



FCIconnect.com

Copyright FCI


TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D +0.25	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15	D09P82C4PA00	D09P82C6PA00
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15	D15P82C4PA00	D15P82C6PA00
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25	D25P82C4PA00	D25P82C6PA00
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25	D37P82C4PA00	D37P82C6PA00
							Gold flash	0.76 μ gold



LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D +0.25	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15	D09P82C4PA00LF	D09P82C6PA00LF
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15	D15P82C4PA00LF	D15P82C6PA00LF
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25	D25P82C4PA00LF	D25P82C6PA00LF
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25	D37P82C4PA00LF	D37P82C6PA00LF
							Gold flash	0.76 μ gold


view shown without plastic pin



Detail of integral plastic pin





PC card drilling dimensions(after plating)
(thickness 1.60 or 2.40±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D—SUB										
ltr	ecn no	dr	date	tolerances unless		otherwise specified			title MALE CONNECTOR DELTA-D EUROSTYLE RIGHT ANGLED PRESS FIT											
G	ELX-I-18050	MP	2014/06/23	angles	linear	.0±.0.1														scale 2:1
						.00±0.1														
				0°±2°		.000±0.1														
				dr	PESSON		1995/10/16			dwg no						sheet 1 of 1		size		
				enr	MITHUN PAUL		2014/06/23			C01—8646—0384						A3				
				chr	ALIAS BABU		2014/06/23													
				appd	BIJU K PAUL		2014/06/23													
sheet index		revision sheet		G	1															
type Product Customer Drawing																				