

Technical Datasheet

Cyanolit® 203 TX



Product Description

With the superglue Cyanolit® series, Panacol-Elosol offers an optimal product range in the field of cyanoacrylates. Cyanolit® adhesives are solvent-free reaction adhesives formulated on the basis of esters of cyanoacrylic acid. They show very good adhesion to many materials and especially to plastics.

Cyanolit® 203 TX is a one part, humidity curing cyanoacrylate adhesive, with extremely good bonding to a wide range of materials including metals, plastics and elastomers. Cyanolit® 203 TX is a high viscosity instant adhesive with gap filling ability. It is designed for clean, fast and automated assembly applications. Cyanolit® 203 TX has met the requirements for USP Class VI and is suitable for use in the assembly of disposable medical devices.

Curing Properties

Curing takes place without heat supply, pressure or additional activators. The classical one-component cyanoacrylates react with moisture, which is absorbed as a moisture film on the material surfaces, in a few seconds.

The curing speed depends on the gap width and the humidity level. A small gap width and a high humidity accelerate the setting process.

After a short time Cyanolit® reaches high strength. The material continues to harden 24 hours after gluing. Only after this time is the optimum media resistance achieved.

The following table describes the setting times on different substrates.

Substrate	Curing time [sec]
PVC	5
PMMA	10
ABS	15
PC	20
NR	5
steel	15

Technical Data

Resin
Appearance
Gap width max [mm]

ethyl-2-cyanoacrylate
transparent
0,3

Technical Datasheet

Cyanolit® 203 TX



Uncured material

Viscosity [mPas] (Brookfield LVT, 25°C, Sp 3, 6rpm) <i>PE-Norm 001</i>	5 000 - 10 000
Viscosity [mPas] (Brookfield LVT, 25°C, Sp 3, 60rpm) <i>PE-Norm 001</i>	1 300 - 1 500
Density [g/cm³] <i>PE-Norm 004</i>	1,1
Flash point [°C] <i>PE-Norm 050</i>	>83

Cured material

Temperature resistance [°C]	-80 - 80
-----------------------------	----------

Transport/Storage/Shelf Life

Trading unit	Transport	Storage	Shelf-life*
Other packages	at room temperature max. 25°C	0°C - 10°C	at delivery min. 6 months max. 12 months

***Store in original, unopened containers!**

Instructions for Use

Surface preparation

The surfaces to be bonded should be free of dust, oil, grease or other dirt in order to obtain an optimal and reproducible bond.

For cleaning we recommend the cleaner IP® Panacol. Substrates with low surface energy (e.g. polyethylene, polypropylene) must be pretreated in order to achieve sufficient adhesion.

Application

Our products are supplied ready to use. Depending on packaging they can be applied by hand directly from the container or semi or fully automatically. If help is required, please contact our application engineering department.

Cyanoacrylate adhesives react very quickly with humidity (20% - 80%) or the moisture film on the materials. It is therefore advisable to wear gloves and goggles when handling larger quantities. Cyanolit® is applied punctiform - one or more drops, depending on the size of the surface, onto one of the joining parts. The second joining part is fixed with slight pressure, whereby the adhesive is distributed into a thin film. Acid surfaces prevent or retard the curing, while basic surfaces (pH > 7) accelerate curing.

The application can take place directly from the tip of the dosing bottle, but also with dosing devices. Since the achievable strength depends on the application quantity, an even dosage must be taken into account.

Technical Datasheet

Cyanolit® 203 TX



Adhesive and substrate may not be cold and must be warmed up to room temperature prior to processing.

After application, bonding of the parts should be done quickly.

For safety information refer to our safety data sheet.

Disclaimer

The product is free of heavy metals, PFOS and Phthalates and is conform to the EU-Directive 2017/2102/EU "RoHS III".

THE VALUES NOTED IN THIS TECHNICAL DATA SHEET ARE TYPICAL PROPERTIES AND ARE NOT MEANT TO BE USED AS PRODUCT SPECIFICATIONS.

The information contained in this data sheet is believed to be accurate and is provided for information only. Panacol makes no representation or warranties of any kind concerning this information. It is the user's responsibility to determine the suitability of this product for any intended use. Panacol does not assume responsibility for test or performance results obtained by the user. The user assumes all risk and liability connected with the use of this product.

The user should adopt such precautions and use guidelines as may be advisable for the protection of property and persons against any hazards that may be involved in this product's handling or use. Panacol specifically disclaims any liability for consequential or incidental damages of any kind arising from the handling or use of this product.

The information contained in this Technical Data Sheet offers no assurance that the product use, application, or process will not infringe on existing patents or licenses of others. Nothing in this Technical Data Sheet transfers or grants license for the use of any patents, trade secrets, intellectual property, or confidential information that is the property of Panacol.

Except as otherwise noted, all trademarks in this document (identified as ®) are the property of Panacol.

Contact

Panacol-Elosol GmbH
Daimlerstr. 8
61449 Steinbach
Germany
Phone.: +49 6171 6202-0
Mail: info@panacol.de
www.panacol.com

Panacol-USA, Inc.
142 Industrial Lane
Torrington CT 06790
USA
Phone: +1 860-738-7449
Mail: info@panacol-usa.com
www.panacol-usa.com

Panacol-Korea Co., Ltd.
#707, Kranz Techno, 388 Dunchon-daero
Junwon-gu, Seongnam
Gyeonggi-do, 13403 KOREA
Phone: +82 31 749 1701
Mail: info@panacol-korea.com
www.panacol-korea.com

Eleco Panacol – EFD
125, av Louis Roche
Z.A. des Basses Noëls
92238 Gennevilliers Cdx FRANCE
Tél.: +33 (0)1 47 92 41 80
Mail: eleco@eleco-panacol.fr
www.eleco-panacol.fr