

APD3224MGC MEGA GREEN


Features

- 3.2x2.4mm SMT LED, 2.4mm THICKNESS.
 - LOW POWER CONSUMPTION.
 - IDEAL FOR BACKLIGHT AND INDICATOR.
 - VARIOUS COLORS AND LENS TYPES AVAILABLE.
 - PACKAGE : 1500PCS / REEL.

Description

The Mega Green source color devices are made with DH InGaAlP on GaAs substrate Light Emitting Diode.

Package Dimensions



Notes:

- NOTES:

 1. All dimensions are in millimeters (inches).
 2. Tolerance is $\pm 0.1(0.004")$ unless otherwise noted.
 3. Specifications are subject to change without notice.

Selection Guide

Part No.	Dice	Lens Type	I _V (mcd) @ 20 mA		Viewing Angle
			Min.	Typ.	
APD3224MGC	MEGA GREEN (InGaAlP)	WATER CLEAR	280	550	20°

Note:

1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at T_A=25°C


Symbol	Parameter	Device	Typ.	Max.	Units	Test Conditions
λ _{peak}	Peak Wavelength	Mega Green	574		nm	I _F =20mA
λ D	Dominate Wavelength	Mega Green	568		nm	I _F =20mA
Δλ 1/2	Spectral Line Half-width	Mega Green	26		nm	I _F =20mA
C	Capacitance	Mega Green	20		pF	V _F =0V;f=1MHz
V _F	Forward Voltage	Mega Green	2.1	2.5	V	I _F =20mA
I _R	Reverse Current	Mega Green		10	uA	V _R = 5V

Absolute Maximum Ratings at T_A=25°C






Parameter	Mega Green	Units
Power dissipation	105	mW
DC Forward Current	30	mA
Peak Forward Current [1]	150	mA
Reverse Voltage	5	V
Operating / Storage Temperature	-40°C To +85°C	

Note:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.




Mega Green APD3224MGC




APD3224MGC SMT Reflow Soldering Instructions

Number of reflow process shall be less than 2 times and cooling process to normal temperature is required between first and second soldering process.



Recommended Soldering Pattern (Units : mm)



Tape Specifications (Units : mm)

