


Dimensions: mm (in.)



■ Mechanical Specifications:

- Primary Voltage: 120VAC 60Hz
- Secondary Voltage: 13.7VAC unloaded, 12VAC @ 500mA loaded
- Insulation Resistance: 100MΩ @ 500VDC
- Dielectric Strength: 500VAC for 1 minute

■ Materials:

- Output Cord: 2 conductors x 22AWG x 1.8m min. Length
- Lamination Core: Silicon Steel EI-41
- Thermal Fuse: M20 type, 250V 2A @ 115°C
- Enclosure: Noryl SE-100J, UL E45587
- Bobbin: Rynite FR-530, UL E69578(M)
- Winding Wire: Polyurethane Enamelled Copper Wire; Ø.14mm (primary), Ø.55mm (secondary)
- Insulating Tape: Polyester
- Impregnation: Insulating Varnish
- Color: Black

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[412-212054](#)