

Duplex Multimode 62.5/125 Fiber Patch Cable (MTRJ/MTRJ), 3M (10-ft.)

MODEL NUMBER: **N312-03M**



Description

Tripp Lite's 3meter multimode duplex fiber optic MTRJ/MTRJ patch cable is manufactured from 62.5/125 zipcord fiber. The cable has MTRJ to MTRJ connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 3meter. Connectors: MTRJ to MTRJ
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Duplex multimode fiber is most commonly used in LAN applications where links are typically 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)

Highlights

- Premium PVC 62.5/125 μ m multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

- Any fiber optic hardware or NIC card requiring Multimode Duplex cable with MT-RJ/SC connectors

Package Includes

- 3-meter Duplex MMF Cable
MTRJ/MTRJ 62.5/125 Fiber

Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Model Type	MTRJ/MTRJ
Network Speed	1Gbps
INPUT	
Cable Length (m)	3
UPC ASSIGNMENT	
Unit Carton UPC#	037332097972
PHYSICAL	
Color	Orange
Style	Fiber Optic
CONNECTIONS	
Connector A	MTRJ
Connector B	MTRJ
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.