

## 74VHC08

### Quad 2-Input AND Gate

#### General Description

The VHC08 is an advanced high speed CMOS 2 Input AND Gate fabricated with silicon gate CMOS technology. It achieves the high-speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation.

The internal circuit is composed of 4 stages including buffer output, which provide high noise immunity and stable output. An input protection circuit insures that 0V to 7V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5V to 3V systems and two supply systems such as battery backup. This circuit prevents device destruction due to mismatched supply and input voltages.

#### Features


- High Speed:  $t_{PD} = 4.3$  ns (typ) at  $T_A = 25^\circ\text{C}$
- High noise immunity:  $V_{NIH} = V_{NIL} = 28\% V_{CC}$  (min)
- Power down protection is provided on all inputs
- Low power dissipation:  $I_{CC} = 2$   $\mu\text{A}$  (Max) @  $T_A = 25^\circ\text{C}$
- Low noise:  $V_{OLP} = 0.8\text{V}$  (max)
- Pin and function compatible with 74HC08

#### Ordering Code:


| Order Number | Package Number | Package Description                                                          |
|--------------|----------------|------------------------------------------------------------------------------|
| 74VHC08M     | M14A           | 14-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-120, 0.150" Narrow |
| 74VHC08SJ    | M14D           | 14-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide                |
| 74VHC08MTC   | MTC14          | 14-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide  |
| 74VHC08N     | N14A           | 14-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide       |

Surface mount packages are also available on Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

#### Logic Symbol



#### Connection Diagram



#### Pin Descriptions

| Pin Names  | Description |
|------------|-------------|
| $A_n, B_n$ | Inputs      |
| $O_n$      | Outputs     |

#### Truth Table

| A | B | O |
|---|---|---|
| L | L | L |
| L | H | L |
| H | L | L |
| H | H | H |

**Absolute Maximum Ratings** (Note 1)

|                                                       |                          |
|-------------------------------------------------------|--------------------------|
| Supply Voltage ( $V_{CC}$ )                           | -0.5V to +7.0V           |
| DC Input Voltage ( $V_{IN}$ )                         | -0.5V to +7.0V           |
| DC Output Voltage ( $V_{OUT}$ )                       | -0.5V to $V_{CC} + 0.5V$ |
| Input Diode Current ( $I_{IK}$ )                      | -20 mA                   |
| Output Diode Current ( $I_{OK}$ )                     | ±20 mA                   |
| DC Output Current ( $I_{OUT}$ )                       | ±25 mA                   |
| DC $V_{CC}$ /GND Current ( $I_{CC}$ )                 | ±50 mA                   |
| Storage Temperature ( $T_{STG}$ )                     | -65°C to +150°C          |
| Lead Temperature ( $T_L$ )<br>(Soldering, 10 seconds) | 260°C                    |

**Recommended Operating Conditions** (Note 2)

|                                         |                   |
|-----------------------------------------|-------------------|
| Supply Voltage ( $V_{CC}$ )             | 2.0V to +5.5V     |
| Input Voltage ( $V_{IN}$ )              | 0V to +5.5V       |
| Output Voltage ( $V_{OUT}$ )            | 0V to $V_{CC}$    |
| Operating Temperature ( $T_{OPR}$ )     | -40°C to +85°C    |
| Input Rise and Fall Time ( $t_r, t_f$ ) |                   |
| $V_{CC} = 3.3V \pm 0.3V$                | 0 ns/V ~ 100 ns/V |
| $V_{CC} = 5.0V \pm 0.5V$                | 0 ns/V ~ 20 ns/V  |

**Note 1:** Absolute Maximum Ratings are values beyond which the device may be damaged or have its useful life impaired. The databook specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. Fairchild does not recommend operation outside databook specifications.

**Note 2:** Unused inputs must be held HIGH or LOW. They may not float.

**DC Electrical Characteristics**

| Symbol   | Parameter                    | $V_{CC}$<br>(V)  | $T_A = 25^\circ\text{C}$ |     |                      | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |                      | Units | Conditions                                                     |
|----------|------------------------------|------------------|--------------------------|-----|----------------------|-------------------------------------------------|----------------------|-------|----------------------------------------------------------------|
|          |                              |                  | Min                      | Typ | Max                  | Min                                             | Max                  |       |                                                                |
| $V_{IH}$ | HIGH Level<br>Input Voltage  | 2.0<br>3.0 - 5.5 | 1.50<br>0.7 $V_{CC}$     |     |                      | 1.50<br>0.7 $V_{CC}$                            |                      | V     |                                                                |
| $V_{IL}$ | LOW Level<br>Input Voltage   | 2.0<br>3.0 - 5.5 |                          |     | 0.50<br>0.3 $V_{CC}$ |                                                 | 0.50<br>0.3 $V_{CC}$ | V     |                                                                |
| $V_{OH}$ | HIGH Level<br>Output Voltage | 2.0              | 1.9                      | 2.0 |                      | 1.9                                             |                      | V     | $V_{IN} = V_{IH}$<br>or $V_{IL}$<br>$I_{OH} = -50 \mu\text{A}$ |
|          |                              | 3.0              | 2.9                      | 3.0 |                      | 2.9                                             |                      |       |                                                                |
|          |                              | 4.5              | 4.4                      | 4.5 |                      | 4.4                                             |                      | V     | $I_{OH} = -4 \text{ mA}$<br>$I_{OH} = -8 \text{ mA}$           |
|          |                              | 3.0              | 2.58                     |     |                      | 2.48                                            |                      |       |                                                                |
| $V_{OL}$ | Low Level<br>Output Voltage  | 2.0              |                          | 0.0 | 0.1                  |                                                 | 0.1                  | V     | $V_{IN} = V_{IH}$<br>or $V_{IL}$<br>$I_{OL} = 50 \mu\text{A}$  |
|          |                              | 3.0              |                          | 0.0 | 0.1                  |                                                 | 0.1                  |       |                                                                |
|          |                              | 4.5              |                          | 0.0 | 0.1                  |                                                 | 0.1                  | V     | $I_{OL} = 4 \text{ mA}$<br>$I_{OL} = 8 \text{ mA}$             |
|          |                              | 3.0              |                          |     | 0.36                 |                                                 | 0.44                 |       |                                                                |
|          |                              | 4.5              |                          |     | 0.36                 |                                                 | 0.44                 |       |                                                                |
| $I_{IN}$ | Input Leakage Current        | 0 - 5.5          |                          |     | ±0.1                 |                                                 | ±1.0                 | μA    | $V_{IN} = 5.5V$ or GND                                         |
| $I_{CC}$ | Quiescent Supply Current     | 5.5              |                          |     | 2.0                  |                                                 | 20.0                 | μA    | $V_{IN} = V_{CC}$ or GND                                       |

**Noise Characteristics**

| Symbol                | Parameter                                | $V_{CC}$<br>(V) | $T_A = 25^\circ\text{C}$ |        | Units | Conditions            |
|-----------------------|------------------------------------------|-----------------|--------------------------|--------|-------|-----------------------|
|                       |                                          |                 | Typ                      | Limits |       |                       |
| $V_{OLP}$<br>(Note 3) | Quiet Output Maximum Dynamic $V_{OL}$    | 5.0             | 0.3                      | 0.8    | V     | $C_L = 50 \text{ pF}$ |
| $V_{OLV}$<br>(Note 3) | Quiet Output Minimum Dynamic $V_{OL}$    | 5.0             | -0.3                     | -0.8   | V     | $C_L = 50 \text{ pF}$ |
| $V_{IHD}$<br>(Note 3) | Minimum HIGH Level Dynamic Input Voltage | 5.0             |                          | 3.5    | V     | $C_L = 50 \text{ pF}$ |
| $V_{ILD}$<br>(Note 3) | Maximum LOW Level Dynamic Input Voltage  | 5.0             |                          | 1.5    | V     | $C_L = 50 \text{ pF}$ |




**Note 3:** Parameter guaranteed by design.

## AC Electrical Characteristics

| Symbol           | Parameter                     | V <sub>CC</sub><br>(V) | T <sub>A</sub> = 25°C |     |      | T <sub>A</sub> = -40°C to +85°C |      | Units | Conditions             |
|------------------|-------------------------------|------------------------|-----------------------|-----|------|---------------------------------|------|-------|------------------------|
|                  |                               |                        | Min                   | Typ | Max  | Min                             | Max  |       |                        |
| t <sub>PHL</sub> | Propagation Delay             | 3.3 ± 0.3              |                       | 6.2 | 8.8  | 1.0                             | 10.5 | ns    | C <sub>L</sub> = 15 pF |
| t <sub>PLH</sub> |                               |                        |                       | 8.7 | 12.3 | 1.0                             | 14.0 |       | C <sub>L</sub> = 50 pF |
|                  |                               | 5.0 ± 0.5              |                       | 4.3 | 5.9  | 1.0                             | 7.0  | ns    | C <sub>L</sub> = 15 pF |
|                  |                               |                        |                       | 5.8 | 7.9  | 1.0                             | 9.0  |       | C <sub>L</sub> = 50 pF |
| C <sub>IN</sub>  | Input Capacitance             |                        |                       | 4   | 10   |                                 | 10   | pF    | V <sub>CC</sub> = Open |
| C <sub>PD</sub>  | Power Dissipation Capacitance |                        |                       | 18  |      |                                 |      | pF    | (Note 4)               |




**Note 4:** C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I<sub>CC</sub> (opr.) = C<sub>PD</sub> \* V<sub>CC</sub> \* f<sub>IN</sub> + I<sub>CC</sub>/4 (per gate).

# Physical Dimensions inches (millimeters) unless otherwise noted







M14A (REV H)

**14-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-120, 0.150" Narrow  
Package Number M14A**



M14D (REV B)

**14-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide  
Package Number M14D**




## NOTES:

- A. CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION AB,  
REF NOTE 6, DATED 7/93
- B. DIMENSIONS ARE IN MILLIMETERS
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH,  
AND TIE BAR EXTRUSIONS

**14-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide  
Package Number MTC14**

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



14-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide  
Package Number N14A

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)