


Technical drawing of a rectangular plate. The drawing includes three dimension lines: a vertical line on the left labeled 'C' indicating the height, a horizontal line at the top labeled 'B REF.' indicating the width, and a vertical line at the bottom labeled 'A' indicating the thickness. The plate is shown in a perspective view with rounded corners on the top and bottom edges.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	MIN. LOOP* TENSILE lbs. (N)	PACKAGE DESCRIPTION	APPROXIMATE WEIGHT lbs/100 TIES (g)
	MIN. in (mm)	MAX. in (mm)						
HLB2S-C	.25 (6.4)	1.6 (41)	.100 (2.5)	7.0 (178)	.750 (19.1)	50 (222)	100 PIECES STACKED 5 ACROSS 20 ROWS HIGH (STAGGERED)	0.49 (223)



- 1) TIES ARE STACK-PACKED (SEE ILLUSTRATION 'A')
- 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
- 3) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR OPTIONAL COLORS.

PANDUIT CORP. TINLEY PARK, ILLINOIS

DWG
A
SIZE

R	1/7/08	ERW		DRAWING RELEASED	27571	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	