

F

E

D

C

B

A

F









E

D

C

B

A




- NOTES:
- 1.MATERIALS: HOUSING-POLYAMIDE, GLASS FIBER FILLED, UL94V-0, COLOR: SEE TABLE.
EAR-POLYAMIDE, GLASS FIBER FILLED, UL94V-0, COLOR: WHITE.
TERMINAL-1. PHOSPHOR BRONZE
2. BRASS
LATCH-BRASS
 - 2.FINISHES: TERMINAL:
GOLD PLATED IN CONTACT AREA (SEE TABLE),
TIN ALLOY IN THE SOLDER AREA;
THICKNESS=150 MICRONCH MINIMUM,
UNDER PLATED: NICKEL(N)
THICKNESS=50 MICRONCH MINIMUM,
LATCH:
TIN PLATED ALL OVER,
THICKNESS=100 MICRONCH MINIMUM,
UNDER PLATED: NICKEL(N)
THICKNESS=50 MICRONCH MINIMUM,
3.RECOMMENDED PCB THICKNESS: 160±0.05MM
4.PRODUCT SPECIFICATION: REFER TO PS-48006-002
5.TEST SUMMARY: REFER TO TS-48006-002
6.PACKAGING: REFER TO PK-48006-002
7.LEAD-FREE AND ROHS COMPLIANCE

RECOMMENDED PCB HOLE LAYOUT
(TOLERANCE ±0.05MM)


48006-1102	15 MICROINCH	PHOSPHOR BRONZE	2.5V	BLACK
48006-2102	15 MICROINCH			BLUE 2945C
48006-5101	GOLD FLASH			YELLOW 115U
48006-4101	GOLD FLASH			LAVENDER 2736U
48006-3101	GOLD FLASH			GREEN 3258U-3268U
48006-2101	GOLD FLASH	BRASS	2.5V	BLUE 2945C
48006-1101	GOLD FLASH			BLACK
48006-2112	15 MICROINCH			BLUE 2945C
48006-1112	15 MICROINCH			BLACK
48006-5111	GOLD FLASH			YELLOW 115U
48006-4111	GOLD FLASH			LAVENDER 2736U
48006-3111	GOLD FLASH			GREEN 3258U-3268U
48006-2111	GOLD FLASH			BLUE 2945C
48006-1111	GOLD FLASH			BLACK
MOLEX P/N	CONTACT PLATING	MATERIAL	POWER SUPPLY	COLOR

L/F FOR 48006 EC NO: SH2005-0376 DRWN: JCHEN12 CHKD: 2005/08/04 APPR: WWSCHANG 2005/08/04	DESCRIPTION	QUALITY SYMBOLS
		▽=0
		▽C=0
		REV

GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
	mm	INCH	DRAWN BY DATE		TITLE 1.27MM PITCH DDR DIMM SINGLE KEY 2.5V 184CKTS (LEAD-FREE VERSION) MOLEX INCORPORATED			
4 PLACES	± ---	± ---	JIANG	2005/04/13				
3 PLACES	± ---	± ---	CHECKED BY	DATE				
2 PLACES	± 0.25	± ---	ERIC KAO	2005/04/13				
1 PLACE	± 0.25	± ---	APPROVED BY	DATE				
ANGULAR ± 3 °			WSCHANG 2005/04/13		MOLEX			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.			SHEET NO.
			SEE TABLE		SD-48006-002			1 OF 2
			SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					



PLUG COMPONENT:DDR 184P FUNC. CARD



NOTE:
SEE JEDEC SPEC MO-206 FOR COMPLETE MODULE
DETAILS 1.27±0.10 THICK ACROSS CONTACT RADS

SEE SHEET 1 EC NO: SH2005-0376 DRWN: JCHEN12 CHKD: 2005/08/04 APPR: WWSCHANG 2005/08/04	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY JIANG	DATE 2005/04/13	TITLE 1.27MM PITCH DDR DIMM SINGLE KEY 2.5V 184CKTS (LEAD-FREE VERSION)			
			4 PLACES	± ---	± ---	CHECKED BY ERIC KAO	DATE 2005/04/13				
			3 PLACES	± ---	± ---	APPROVED BY WSCHANG	DATE 2005/04/13	MOLEX MOLEX INCORPORATED			
			2 PLACES	± 0.25	± ---						
			1 PLACE	± 0.25	± ---	MATERIAL NO.	DOCUMENT NO.	SHEET NO.			
			ANGULAR ± 3 °		SEE TABLE		SD-48006-002	2 OF 2			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			B	REV							