


MECHANICAL DATA
Dimensions in mm (inches)



TO-247

PIN 1 - Base

PIN 2 - Emitter

PIN 3 - Collector.

**NPN
MULTI-EPITAXIAL
POWER
TRANSISTORS**

FEATURES

- LOW $V_{CE(sat)}$
- FAST SWITCHING
- HIGH CURRENT
- HIGH RELIABILITY

APPLICATIONS

- HIGH FREQUENCY AND EFFICIENCY CONVERTERS
- SWITCHING REGULATORS
- MOTOR CONTROLS

Suitable for high current, high speed, low voltage applications.

ABSOLUTE MAXIMUM RATINGS ($T_{case} = 25^{\circ}C$ unless otherwise stated)

		BUW48-247	BUW49-247
V_{CEV}	Collector - Emitter Voltage ($V_{BE} = -1.5V$)	120V	160V
V_{CEO}	Collector - Base Voltage ($I_B = 0$)	60V	80V
V_{EBO}	Emitter - Base Voltage ($I_C = 0$)	7V	7V
I_C	Collector Current	30A	30A
$I_{C(pk)}$	Peak Collector Current ($t_p = 10ms$)	45A	40A
I_B	Base Current	8A	6A
$I_{B(pk)}$	Peak Base Current ($t_p = 10ms$)	12A	10A
P_{tot}	Total Power Dissipation	150W	150W
T_{STG}	Storage Temperature Range	-55 to +175°C	-55 to +175°C
T_J	Maximum Operating Junction Temperature	+175°C	+175°C
$R_{\theta JC}$	Thermal Resistance Junction - Case	1.0°C/W Max.	1.0°C/W Max.

Magnatec Plc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Magnatec is believed to be both accurate and reliable at the time of going to press. However Magnatec assumes no responsibility for any errors or omissions discovered in its use. Magnatec encourages customers to verify that datasheets are current before placing orders.

Magnatec plc. Telephone +44(0)1455 554711. Fax +44(0)1455 558843.

E-mail: sales@magnatec-uk.co.uk Website: <http://www.magnatec-uk.co.uk/>

Prelim. 08/07

ELECTRICAL CHARACTERISTICS ($T_{case} = 25^{\circ}C$ unless otherwise stated)

Parameter	Test Conditions	Min.	Typ.	Max.	Unit
$V_{CE(sus)}$ Collector - Emitter Sustaining Voltage	$I_C = 0.2A$ BUW48	60			V
	$L = 25mH$ BUW49	80			
$V_{(BR)EBO}$ Emitter - Base Breakdown Voltage	$I_C = 0$ $I_E = 50mA$	7			
I_{CEX} Collector Cut-off Current	$V_{CE} = V_{CEX}$			1.0	mA
	$V_{BE} = -1.5V$ $T_J = 125^{\circ}C$			3.0	
I_{EBO} Emitter Cut-off Current	$I_C = 0$ $V_{BE} = -5V$			1.0	
$V_{CE(sat)^*}$ Collector - Emitter Saturation Voltage	$I_C = 20A$ $I_B = 2.0A$ BUW48			0.6	V
	$I_C = 40A$ $I_B = 4.0A$ BUW49			1.4	
	$I_C = 15A$ $I_B = 1.5A$ BUW48			0.5	
	$I_C = 30A$ $I_B = 3.0A$ BUW49			1.2	
$V_{BE(sat)^*}$ Base - Emitter Saturation Voltage	$I_C = 40A$ $I_B = 4.0A$ BUW48			2.1	
	$I_C = 30A$ $I_B = 3.0A$ BUW49			2.0	
f_T Transition Frequency	$f = 15MHz$ $V_{CE} = 15V$ $I_C = 1A$		8.0		MHz

DYNAMIC CHARACTERISTICS BUW48 ($T_{case} = 25^{\circ}C$ unless otherwise stated)

Parameter	Test Conditions	Min.	Typ.	Max.	Unit
t_{on} Turn-On Time	$V_{CC} = 60V$ $I_C = 40A$ $I_{B1} = -I_{B2} = 4A$		1.2	1.5	μs
t_s Storage Time	$V_{CC} = 60V$ $I_C = 40A$ $I_{B1} = -I_{B2} = 4A$ $T_J = 100^{\circ}C$		0.6	1.1	
t_f Fall Time	$V_{CC} = 60V$ $I_C = 40A$		0.17	0.25	
	$I_{B1} = -I_{B2} = 4A$ $T_J = 100^{\circ}C$			0.5	

DYNAMIC CHARACTERISTICS BUW49 ($T_{case} = 25^{\circ}C$ unless otherwise stated)

Parameter	Test Conditions	Min.	Typ.	Max.	Unit
t_{on} Turn-On Time	$V_{CC} = 80V$ $I_C = 30A$ $I_{B1} = -I_{B2} = 4A$		0.8	1.2	μs
t_s Storage Time	$V_{CC} = 80V$ $I_C = 30A$ $I_{B1} = -I_{B2} = 4A$ $T_J = 100^{\circ}C$		0.6	1.1	
t_f Fall Time	$V_{CC} = 80V$ $I_C = 30A$		0.15	0.25	
	$I_{B1} = -I_{B2} = 4A$ $T_J = 100^{\circ}C$			0.5	

* Pulse Test: $t_p = 300\mu s$, $\delta \leq 2\%$

Magnatec Plc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Magnatec is believed to be both accurate and reliable at the time of going to press. However Magnatec assumes no responsibility for any errors or omissions discovered in its use. Magnatec encourages customers to verify that datasheets are current before placing orders.