

Product Data Sheet

A59



Safety Products



Description: Safety helmet with 4 point plastic suspension with forehead comfort band, 4 – point chinstrap anchorage and 3-level height adjustment. The 30mm accessory slots fits most available accessories.

Materials: Shell – HDPE (High Density Polyethylene).
Temp. resistance : -30 °C up to max +50°C
Electrical properties : VDE-tested (1000 V).

Total Weight: 306 gram

Standards: EN397 – DIN VDE 0680

Size : 52 – 62 cm.

Accessories : Nomaz sweatband
Penclip
Faceshields
Weldingshields
Ear defenders
Chinstraps (4-point).

Standards characteristics	EN 397	
Shock absorption		
Form and mass		Spherical M = 5 Kg
Free fall and shock angle		H = 1 m vertical
Maximum force		F maximum 5 kN
Resistance to penetration		
Form and mass		Conical (60° C) M = 3 Kg
Free fall and shock angle		H = 1 m vertical
Number of shocks		1 shock
Requirement		No contact
Flame resistance		Flame 10 s at 5 cm
Requirement		No burn more than 5 s
Retention system strength		
Released force		150 N < F < 250 N
Ventilation area		If ventilation 150 < S < 450 mm ²

End Shelf life: Shell max. 5 years after date first use.

Storage : Temp : min.+5°C and max. +25°C. Avoid direct sunlight.

Packaging: individual in polythene bag.
20 helmets/Cse – LxWxH: 44.5x 31.8x 62.2cm – 08.02kg.

rev. 14-03-2006

**North Safety Products
The Netherlands**
Noordmonsterweg 1
4332 SC Middelburg
The Netherlands

Tel: +31(0)118 656400
Fax: +31(0)118 627535

United Kingdom
The Court Yard
Green Lane, Heywood
Lancashire OL10 2EX
United Kingdom

Tel: +44(0)170 669 3800
Fax: +44(0)170 669 3801

Germany
Bramfelder Chaussee 41
D-22177 Hamburg
Germany

Tel: +49(0)40611775-0
Fax: +49(0)40611775-10

France
505 route de Bouc Bel Air
13080 Luynes
France

Tel: +33(0)442 240264
Fax : +33(0)442 609530

Scandinavia
Verktygsvägen 10
S-55302 Jönköping
Sweden

Tel: +46(0)36377241
Fax: +46(0)36377629