


GP Batteries


Data Sheet

Model No.: GP380AFH


Type	Rechargeable Nickel Metal Hydride Cylindrical Cell	
Nominal Dimension (with Sleeve)	$\Phi = 17.5\text{mm}$ $H = 67.0\text{mm}$	
Applications	Recommended discharge current 380 to 11400mA	
Nominal Voltage	1.2V	
Nominal Capacity	Minimum: 3700mAh Typical: 3800mAh when discharge at 760mA to 1.0V at 20°C	
Charging Condition	380mA for 14 hrs at 20°C	
Fast Charge	1900mA to 3800mA (0.5 to 1C) charge termination control recommended control parameters: - ΔV : 0 - 5mV DT/dt : 0.8°C/min (0.5 to 0.9C) : 0.8 - 1°C/min (1C) TCO : 45 - 50°C Timer : 105% nominal input	
Service Life	>500 cycles (IEC standard)	
Continuous Overcharge	380mA maximum current for 1 year No conspicuous deformation and/or leakage	
Weight	53.5g	
Internal Resistance	Average 18m Ω upon fully charged (Range 13-24m Ω) at 1000Hz	
Max. Charging Voltage	1.5V at 380mA charging	
Ambient Temperature Range	Standard Charging	0 to 45°C
	Fast Charging	10 to 45°C
	Discharging	-20 to 50°C
	Storage	-20 to 35°C




Fast Charge (Charge control required)



Low Rate Discharge



High Rate Discharge



* The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.