





DIALIGHT PART NUMBER	LED COLOR
597-3021-402F; -407F	RED
597-3202-402F; -407F	ORANGE
597-3312-402F; -407F	GREEN
597-3325-402F; -407F	InGaN GREEN
597-3612-402F; -407F	BLUE

RoHS COMPLIANT 597-3XXX-40XF
Part Numbers with the "F" suffix ending are RoHS Compliant.
For example: 597-3021-402F
Reel and bag packaging are marked with "RoHS Compliant"
label or equivalent markings. These parts can be used with
RoHS reflow profile. Parts can be wave soldered, dip soldered
or hand soldered using typical lead-free soldering process
with max 260°C temp. for 5 sec.

OPERATING CHARACTERISTICS AT 25°C AMBIENT										
LED COLOR	LUMINOUS INTENSITY @I _F = 20 mA (10 mA FOR InGaN GREEN & BLUE) (mcd)		FORWARD VOLTAGE @I _F = 20 mA (10 mA FOR InGaN GREEN & BLUE) (V)		REVERSE CURRENT (μA)	DOMINANT WAVELENGTH (nm)			PEAK WAVELENGTH (nm)	VIEWING ANGLE (DEG)
	MIN	MAX	TYP	MAX	MAX	MIN	TYP	MAX	TYP	TYP
RED	150	330	1.9	2.4	100	620	626	632	635	60
ORANGE	150	330	1.9	2.4	100	600	605	609	609	60
GREEN	27	56	2.1	2.5	100	558	561	564	565	60
InGaN GREEN	150	680	3.3	3.8	100	—	525	—	522	50
BLUE	47	220	3.3	3.8	100	—	470	—	465	50

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT	LED COLOR					UNITS
	RED	ORANGE	GREEN	InGaN GREEN	BLUE	
POWER DISSIPATION	78	78	81	84	80	mW
FORWARD CURRENT	30	30	30	20	20	mA
PULSE FORWARD CURRENT (DUTY ≤ 1/20, PULSE WIDTH ≤ 1ms)	100	100	100	48	48	mA
DERATE LINEARLY FROM 75°C (FROM 60°C OR HIGHER FOR InGaN GREEN & BLUE)	1.0	1.0	1.0	0.96	0.96	mA/°C
REVERSE VOLTAGE	5	5	5	5	5	V
STORAGE TEMPERATURE	-40 TO +120			-40 TO +110		°C
OPERATING TEMPERATURE	-40 TO +100					°C



RECOMMENDED SOLDER PAD LAYOUT

NOTES:


1. DIE: InGaN FOR P/Ns 597-3325-40XF & 597-3612-40XF
All InGaP FOR ALL OTHER P/Ns.
2. EPOXY COLOR: WATER CLEAR.
3. DIALIGHT PART NUMBERS: 597-3XXX-40XF.
4. ...-402F SUFFIX FOR 20 PCS ON A SAMPLE STRIP.
5. ...-407F SUFFIX FOR 7" [180mm] DIA. REEL, .315" [8mm] WIDE TAPE,
PACKAGED 2,500 PCS PER REEL, CATHODE TOWARDS SPROCKET.
6. MOISTURE SENSITIVITY LEVEL: 4.
7. THESE COMPONENTS CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE
DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING
ASSEMBLY, HANDLING AND STORAGE IN ACCORDANCE WITH IPC-A-610.



ATTENTION:
OBSERVE PRECAUTIONS FOR
HANDLING ELECTROSTATIC
SENSITIVE DEVICES



LED SCHEMATIC



THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.										
SCALE: 20.000 ALL DIM'S IN: INCHES (MM)					DRAWING NUMBER			REV		
TOLERANCES: UNLESS OTHERWISE SPECIFIED FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.008 ANGLES: ±1° FINISH: FSCM 83330					C-17266			B		
					TITLE			SMT LED, 1206 PKG. W/ LENS RoHS COMPLIANT		
					MATERIAL			-		
					Dialight			1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727		
					SHEET 1 OF 1			FAMILY TABLE:		