

TOSHIBA PHOTOCOUPLER GaAs IRED & PHOTO-THYRISTOR

TLP543J, TLP545J

PROGRAMMABLE CONTROLLERS

AC-OUTPUT MODULE



SOLID STATE RELAY

The TOSHIBA TLP543J consists of a phot-thyristor optically coupled to a gallium arsenide infrared emitting diode in a seven lead plastic DIP package.


The TOSHIBA TLP545J consists of a photo-thyristor optically coupled to a gallium arsenide infrared emitting diode in a six lead plastic DIP package.

- Trigger LED Current : $I_{FT} = 10\text{mA}$ (Max.)
- On-State Current : $I_T(\text{RMS}) = 150\text{mA}$
- Peak Off-State Voltage : $V_{DRM} = V_{RRM} = 600\text{V}$ (Min.)
- Isolation Voltage : $2500V_{\text{rms}}$ (Min.)
- UL Recognized : UL1577, File No. E67349


PIN CONFIGURATIONS (TOP VIEW)



Unit in mm



Weight : 0.53g



Weight : 0.4g

MAXIMUM RATINGS (Ta = 25°C)

		SYMBOL	RATING	UNIT
LED	Forward Current	I_F	70	mA
	Forward Current Derating (Ta $\geq$ 25°C)	$\Delta I_F / ^\circ\text{C}$	-0.7	mA / °C
	Peak Forward Current (Note 1)	I_{FP}	1	A
	Reverse Voltage	V_R	5	V
	Junction Temperature	T_j	125	°C
DETECTOR	Peak Forward Voltage ($R_{GK} = 27\text{k}\Omega$)	V_{DRM}	600	V
	Peak Reverse Voltage ($R_{GK} = 27\text{k}\Omega$)	V_{RRM}		
	On-State Current	$I_T(\text{RMS})$	150	mA
	On-State Current Derating	$\Delta I_T / ^\circ\text{C}$	-2	mA / °C
	Peak One Cycle Surge Current	I_{TSM}	1	A
	Peak Reverse Gate Voltage	V_{GM}	-5	V
	Junction Temperature	T_j	100	°C
Operating Temperature Range		T_{opr}	-30~100	°C
Storage Temperature Range		T_{stg}	-55~125	°C
Lead Soldering Temperature (10s) (Note 2)		T_{sol}	260	°C

(Note 1) Pulse width $\leq 100\mu\text{s}$, $f = 100\text{Hz}$

(Note 2) Soldering portion of lead : up to 2mm from body of the device.

RECOMMENDED OPERATING CONDITIONS

CHARACTERISTIC	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply Voltage	V_{AC}	—	—	250	V _{AC}
Forward Current	I_F	15	20	25	mA
Operating Temperature	T_{opr}	-30	—	85	°C
Gate to Cathode Resistance	R_{GK}	—	10	27	k Ω
Gate to Cathode Capacity	C_{GK}	—	0.01	0.1	μF

ELECTRICAL CHARACTERISTICS (Ta = 25°C)







CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
LED	Forward Voltage	V_F	$I_F = 10\text{mA}$	1.0	1.15	1.3	V
	Reverse Current	I_R	$V_R = 5\text{V}$	—	—	10	μA
	Capacitance	C_T	$V = 0, f = 1\text{MHz}$	—	30	—	pF
DETECTOR	Off-State Current and Reverse Current	I_{DRM} and I_{RRM}	$V_{DRM} = \text{Rating}, R_{GK} = 27\text{k}\Omega$	—	—	5	μA
	On-State Voltage	V_{TM}	$I_{TM} = 100\text{mA}$	—	—	1.3	V
	Holding Current	I_H	$R_{GK} = 27\text{k}\Omega$	—	0.2	—	mA
	Off-State dv / dt	dv / dt	$V_{AK} = \text{Rating}, R_{GK} = 27\text{k}\Omega$	—	10	—	V / μs








COUPLED CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Trigger LED Current	I_{FT}	$V_{AK} = 6\text{V}, R_{GK} = 27\text{k}\Omega$ $R_L = 100\Omega$	—	—	10	mA
Turn-On Time	t_{ON}	$I_F = 50\text{mA}, R_{GK} = 27\text{k}\Omega$	—	10	—	μs
Capacitance (Input to Output)	C_S	$V = 0, f = 1\text{MHz}$	—	0.8	—	pF
Isolation Resistance	R_S	R.H. $\leq 60\%$, $V = 500\text{V}$	5×10^{10}	10^{14}	—	Ω
Isolation Voltage (Note 3)	BV_S	AC, 1 minute, R.H. $\leq 60\%$	2500	—	—	V_{rms}

(Note 3) TLP543J : Device considered a two terminal device : Pins 1, 2, 3 and 4 shorted together and pins 5, 6, 7 and 8 shorted together.

TLP545J : Device considered a two terminal device : Pins 1, 2 and 3 shorted together and pins 4, 5 and 6 shorted together.





RESTRICTIONS ON PRODUCT USE

000707EAA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.