

Compact Keyboard

G81-1800



Actual product may vary from the image shown

Small dimensions and top performance!

This popular 16 inch compact designed PC keyboard is highly sought after for space-saving applications and optimum longevity requirements.

Facts & Features

- FTSC technology (mechanical individual keys with membrane contact switches)
- High-performance and compact 16" PC keyboard
- Space-saving and ergonomic
- Robust and reliable
- High-quality keyboard for professional users
- Codeset 3 support e.g. for Unix systems (PS/2 version)

Technical Data:

Total weight (with packaging)

approx. 1.3 kg (without packaging)

approx. 1.6 kg (with packaging)

Storage Temperature:

-20 °C to 60 °C

Operating temperature:

0 °C to 50 °C

Compatibility

- Designed for MS Windows™ XP
- Windows™ 2000, XPembedded, Vista, Windows 7
- Works with Linux, Mac, UNIX, Sun

Current Consumption:

Typ.16 mA

Interface:

PS/2

Number of buttons:

104 = US layout with Windows™ keys

Agency Approvals / Instructions

- FCC, CE, C-Tick, VDE, cURus

Delivery Volume:

- G81-1800
- Quick Guide
- CDROM (USB version only)

System Requirements

- PS/2: Plugs for Keyboard & Mouse

Dimensions (product):

approx. 405 x 180 x 44 mm (keyboard)

Dimensions (packaging):

approx. 460 x 270 x 50 mm (packaging)

Reliability:

- MTBF > 80.000 hours
- MCBF > 10 bill. operation

Keyboard:

- Key technology FTSC
- Service life, standard key: >50 million key operations
- Operation characteristics: Linear
- Inscription technology: Laser
- Inscription layout: US
- Number of keys: (see table)

Technical Data (continued):

Cable length:
approx. 1.75 m

Packaging unit:

- Number of products in the master packaging 52 keyboards
- Number of master packages per pallet 2

Available Software:

- MS Windows™, 2000, XP, Vista, Windows 7

Guarantee period:

- 2 years

Errors, technical changes and delivery possibilities accepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Order Description

<i>Order Number</i>	<i>Interface</i>	<i>Number of Keys</i>	<i>Color</i>
G81-1800LPMUS-0	PS/2	104	Light grey
G81-1800LPMUS-2	PS/2	104	Black

(possible country/layout versions, others available on request)

Cherry Americas, LLC
11200 88th Avenue
Pleasant Prairie, WI 53158
USA
Phone: 262.942.6508
Internet: www.cherryamericas.com

E-Mail: cep_sales@zf.com

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2016 Cherry Americas, LLC, Rev Date: January 6, 2016

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CHERRY:

[G81-1800LUMUS-2](#) [G81-1800LPAUS-0](#) [G81-1800LUMUS-0](#) [G81-1800LPMUS-0](#) [G81-1800LPMUS-2](#) [G81-1800HQMUS](#) [G81-1800LPMES-0](#) [G81-1800LPMSF-0](#) [G81-1800LPMIT-0](#) [G81-1800LPMDK-0](#) [G81-1800LPMBE-0](#) [G81-1800LPMPO-0](#) [G81-1800HQAUS](#) [G81-1800LPAUS](#) [G81-1800LPMDE-0](#) [G81-1800LPMNO-0](#) [G81-1800LPMEU-0](#) [G81-1800LPMGB-0](#) [G81-1800LPMFR-0](#) [G81-1800LPMCH-0](#)