


PART NUMBER	MATERIAL	HEIGHT "A" +/- .031	IMPRINT AREA "B" +/- .031	VERTICAL REPEAT "C" +/- .031	LABELS PER ROW	STANDARD PKG. QTY.
S075X125TAT	GMT1	1.25 [31.8]	0.38 [9.53]	1.50 [38.1]	5	5000
S075X075VATY	GMV16	0.75 [19.0]	0.25 [6.35]	1.00 [25.4]	5	5000
4 S075X100VATY	GMV16	1.00 [25.4]	0.38 [9.53]	1.25 [31.8]	5	5000
S075X125VATY	GMV16	1.25 [31.8]	0.38 [9.53]	1.50 [38.1]	5	5000
S075X150VATY	GMV16	1.50 [38.1]	0.50 [12.7]	1.75 [44.45]	5	5000



CAD FILENAME/LAYERS		100472JY-DC-C10466/05E	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING		OPTIMUM SELF-LAM. S075X***VATY AND S075X125TAT THERMAL TRANSFER PRINTABLE LABELS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) ± .12 (.XX) ± .062		(.XXX) ± .025 ANGLES ± 3	
DRAWN BY RVU		MAT'L:	
DATE 8-31-06		SEE TABLE	
CHK'D		SCALE NTS	
REV		DRAWING NO. C10466	
DATE		DWG SIZE A	
BY			
CHK			

4	9/6/11	RVU	ADD S075X100VATY ON TABLE.	6503	R				
3	8-31-06	RVU	UPDATE ON ALL STANDARD TOLERANCES AND REMOVE NOTE 1.	5925	R				
2	8-31-06	RVU	ADDED NEW P/N: S075X125TAT.	5021	R				
1	8-31-06	RVU	REVISED TOLERANCES.	4830	R				
0	8-31-06	RVU	DRAWING RELEASE.	4671	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	