


REV.	DATE	DESCRIPTION
NC	05/20/02	INITIAL RELEASE
A	04/11/06	UPDATE DRAWING FORMAT



NOTES;

1. ACCEPTS $\varnothing 0.5 \sim 1.05$ CENTER CONDUCTOR TYPICAL.
2. RETURN LOSS -15db MIN. AT 2 GHz.
3. BRT. TIN (90/100) PL. 100 MIN. THICK
OVER NICKEL PL. 50 MIN.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex						
8						DRAWN	G.R.S.							
7					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	CHECKED		PART DESCRIPTION F R/A PC MOUNT RECEPTACLE (HIGH PERFORMANCE)						
6	INSULATOR	TEFLON	NATURAL	1		ISSUED								
5	CONTACT PIN	BRASS	GOLD	1		SHEET	1 OF 1							
4	INSULATOR	TEFLON	NATURAL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”			PART NO. 222180						
3	CONTACT PIN	BER. COPPER	GOLD	1										
2	INSULATOR	TEFLON	BRT. TIN	1				DWG. NO. 222180.DWG						
1	BODY	BRASS	BRT. TIN	1			REV. A							
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	C:/222/1222180.DWG								