


# SOT23 Surface Mount Voltage Divider

New DIV23 Series

- Replaces IRC SOT23 Series for new designs
- Precision ratio tolerances to  $\pm 0.05\%$
- Superior alternative to matched sets
- Ultra-stable TaNSil® resistors on silicon substrate
- RoHS Compliant and Sn/Pb terminations available



## Electrical Data

Element Resistance Range	10 to 200K $\Omega$
Total Resistance Range	20 to 400K $\Omega$
Absolute Tolerance	To $\pm 0.1\%$
Ratio Tolerance to R1	To $\pm 0.05\%$
Absolute TCR	To $\pm 25\text{ppm}/^\circ\text{C}$
Tracking TCR	To $\pm 2\text{ppm}/^\circ\text{C}$
Element Power Rating @ 70°C	125mW
Package Power Rating @ 70°C	250mW
Rated Operating Voltage (not to exceed $\sqrt{P \times R}$ )	100 Volts
Operating Temperature	-55°C to +125°C
Noise	<-30dB

## Environmental Data

Test Per MIL-PRF-83401	Typical Delta R	Max Delta R
Thermal Shock	$\pm 0.02\%$	$\pm 0.1\%$
Power Conditioning	$\pm 0.03\%$	$\pm 0.1\%$
High Temperature Exposure	$\pm 0.03\%$	$\pm 0.05\%$
Short-time Overload	$\pm 0.02\%$	$\pm 0.05\%$
Low Temperature Storage	$\pm 0.03\%$	$\pm 0.05\%$
Life	$\pm 0.05\%$	$\pm 2.0\%$


## Manufacturing Capability

Element Resistance	Available Absolute Tolerances	Available Ratio Tolerances	Best Absolute TCR	Tracking TCR
10 $\Omega$ - 25 $\Omega$	F G J K	D F G	$\pm 100\text{ppm}/^\circ\text{C}$	$\pm 25\text{ppm}/^\circ\text{C}$
25.1 $\Omega$ - 50 $\Omega$	D F G J K	C D F G	$\pm 50\text{ppm}/^\circ\text{C}$	$\pm 10\text{ppm}/^\circ\text{C}$
51 $\Omega$ - 500 $\Omega$	C D F G J K	B C D F G	$\pm 25\text{ppm}/^\circ\text{C}$	$\pm 2\text{ppm}/^\circ\text{C}$
501 $\Omega$ - 100K $\Omega$	B C D F G J K	A B C D F G	$\pm 25\text{ppm}/^\circ\text{C}$	$\pm 2\text{ppm}/^\circ\text{C}$
101K $\Omega$ - 200K $\Omega$	B C D F G J K	B C D F G	$\pm 25\text{ppm}/^\circ\text{C}$	$\pm 2\text{ppm}/^\circ\text{C}$


### General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.


## Physical Data



## Schematic Data



## Power Derating Data



## Ordering Procedure

**Prefix** ..... **SOT** - **DIV23LF** - **01** - **1002** - **1002** - **F** **B**

**Style** .....  
DIV23 = Divider network with standard Sn/Pb termination  
DIV23LF = Divider network with Pb-free termination

**Absolute TCR Code** .....  
00 =  $\pm 250\text{ppm}/^\circ\text{C}$ ; 01 =  $\pm 100\text{ppm}/^\circ\text{C}$ ;  
02 =  $\pm 50\text{ppm}/^\circ\text{C}$ ; 03 =  $\pm 25\text{ppm}/^\circ\text{C}$

**R1 Resistance Code** .....  
4-Digit Resistance Code  
Ex: 1002 =  $10\text{K}\Omega$ ; 50R1 =  $50.1\Omega$

**R2 Resistance Code** .....  
4-Digit Resistance Code  
Ex: 1002 =  $10\text{K}\Omega$ ; 50R1 =  $50.1\Omega$

**Absolute Tolerance Code** .....  
K =  $\pm 10\%$ ; J =  $\pm 5\%$ ; G =  $\pm 2\%$ ; F =  $\pm 1\%$ ;  
D =  $\pm 0.5\%$ ; C =  $\pm 0.25\%$ ; B =  $\pm 0.1\%$

**Ratio Tolerance Code** .....  
G =  $\pm 2\%$ ; F =  $\pm 1\%$ ; D =  $\pm 0.5\%$ ;  
C =  $\pm 0.25\%$ ; B =  $\pm 0.1\%$ ; A =  $\pm 0.05\%$

**Packaging**  
Standard packaging is tape & reel.

**SOT23 Series Legacy Design Note**  
The SOT-DIV23 place R1 between pins 1 and 3 and R2 between pins 2 and 3.  
The SOT-SOT23 place R1 between pins 2 and 3 and R2 between pins 1 and 3.

For additional information or to discuss your specific requirements,  
please contact our Applications Team using the contact details below.

### General Note

TT electronics reserves the right to make changes in product specification without notice or liability.  
All information is subject to TT electronics' own data and is considered accurate at time of going to print.