

Small Signal Diode



Features

- ✧ Designed for mounting on small surface.
- ✧ Extremely thin/leadless package
- ✧ High mounting capability, strong surge with stand, high reliability.
- ✧ Pb free version and RoHS compliant
- ✧ Green compound (Halogen free) with suffix "G" on packing code and prefix "G" on date code

Mechanical Data

- ✧ Case :0603 standard package, molded plastic
- ✧ Terminal: Gold plated, solderable
per MIL-STD-750, method 2026 guaranteed
- ✧ High temperature soldering guaranteed: 260 °C/10s
- ✧ Polarity : Indicated by cathode band
- ✧ Weight : 0.003 gram (approximately)

Ordering Information

Part No.	Package	Packing
TS4448 RZ	0603	4Kpcs / 7" Reel

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Maximum Ratings

Type Number	Symbol	Value	Units
Power Dissipation	P_D	150	mW
Repetitive Peak Reverse Voltage	V_{RRM}	100	V
Repetitive Peak Forward Current	I_{FRM}	300	mA
Mean Forward Current	I_o	125	mA
Non-Repetitive Peak Forward Surge Current Pulse Width= 1 μ sec Pulse Width= 8.3 msec	I_{FSM}	2.0 1.0	A
Thermal Resistance (Junction to Ambient) (Note 1)	$R_{\theta JA}$	666	°C/W
Junction and Storage Temperature Range	T_J, T_{STG}	-40 to + 125	°C

Electrical Characteristics


Type Number	Symbol	Min	Max	Units
Reverse Breakdown Voltage (Note 2)	$V_{(BR)}$	-	80	V
Forward Voltage $I_F = 5mA$ $I_F = 100mA$	V_F	0.62	0.72 1.00	V
Reverse Leakage Current $V_R = 20V$ $V_R = 80V$	I_R	- -	25 100	nA
Junction Capacitance $V_R = 0.5, f = 1.0MHz$	C_J	-	9.0	pF
Reverse Recovery Time (Note3)	T_{rr}	-	9	ns

Notes:1. Valid provided that electrodes are kept at ambient temperature

Notes:2. Test Condition : $I_R = 100\mu A$

Notes:3. Test Condition : $I_F = I_R = 10mA, R_L = 100\Omega, I_{RR} = 1mA$

0603



Dimensions	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	1.60	1.80	0.063	0.071
B	0.80	1.00	0.031	0.039
C	0.70	0.85	0.027	0.033
D	Typ.	0.45	Typ.	0.018
E	Typ.	0.70	Typ.	0.028

Small Signal Diode

Rating and Sharacteristic Curves

FIG 1 Typical Forward Characteristics




FIG 2 Reverse Current vs Reverse




FIG 3 Admissible Power Dissipation Curve




FIG 4 Typical Junction Capacitance




FIG 5 Forward Resistance vs. Forward Current

