

6 A 2P plugs and extensions and TV plugs



501 27

501 28



501 67

501 68



500 10

Ø4 mm pin
For 2-wire cables (max. Ø9 mm)
For class II appliances

Pack	Cat.Nos	2P - plastic - 6 A
20	501 27	○ Plug - white
10	501 28	○ Extension - white
20	501 39	● Plug - black

Pack	Cat.Nos	2P - rubber - 6 A
20	501 67	● Plug - black
10	501 68	● Extension - black

Pack	Cat.Nos	TV plugs
50	500 09	Ø9.52 mm Male plug
50	500 10	Female plug

16 A 2P+⊥ plugs and extensions French standard




502 16

502 17



502 20

502 21



502 45

502 46



502 52

Pack	Cat.Nos	2P+⊥ - plastic - 16 A
		Automatic cable grip Plastic plug and extension For round cable max. Ø11 mm Ø4.8 mm pin for class I appliances Extension equipped with child protection shutters ○ Straight outlet plug - white ○ Side outlet plug - white ○ Extension - white
		Screw-type cable grip - White ○ Straight outlet plug with extraction handle - Annela - white ○ Extension with extraction handle - Annela - white
		Screw-type cable grip - Grey Plastic plug and extension For round cable max. Ø11 mm Ø4.8 mm pin for class I appliances Extension equipped with child protection shutters Plug and extension equipped with extraction handle ● Plug - grey ● Extension with cover - grey
20	502 15	
20	502 16	
10	502 17	
20	502 20	
10	502 21	
20	502 30	
10	502 31	

Pack	Cat.Nos	2P+⊥ - rubber - 16 A
		Screw-type cable grip Rubber plug and extension 250 V~ For class I appliances Straight outlet plug - black For round cable max. Ø11 mm Extension - black For round cable max. Ø11 mm Side outlet plug with extraction handle - black French, German standard For round cable max. Ø12.5 mm
10	502 45	
10	502 46	
10	502 52	

10/16 A 2P+⊥ plugs and extensions

German standard



502 54



503 63



502 85



503 21



513 64



513 68



513 66



513 69

Pack	Cat.Nos	2 P+⊥ plastic - 10/16 A with cable grip	
		For round cable up to 2.5 mm ² (max Ø11 mm) Pin Ø4.8	
20/ 200	502 53		Straight outlet plug, automatic cable grip
50	502 65		Straight outlet plug, screw type cable grip
20/ 200	502 54		Side outlet plug, automatic cable grip
20	502 66		Side outlet plug, screw type cable grip

Pack	Cat.Nos	Female extension - screw type cable grip	
		For round cable up to 2.5 mm ² (max Ø11 mm) Pin Ø4.8	
10	503 63		White

Pack	Cat.Nos	2 P+⊥ plastic - 10/16 A screw type cable grip	
		For round cable up to 2.5 mm ² (max Ø11 mm) Pin Ø4.8	
		French - German standard	
		White - side outlet	
20	503 03		White - side outlet plug - extra flat
10	502 85		Plug equipped with easy extraction rings

Pack	Cat.Nos	2 P+⊥ - rubber - 10/16 A screw type cable grip	
		For round cable up to 2.5 mm ² (max Ø12.5 mm)	
		Plugs	
40	503 21		IP 44
10	502 52		French-German standard plug White extraction handle
		Extensions	
30	513 64	IP 40 - without cover	
25	513 68	IP 44 - with waterproof cover	
5	513 66	IP 44 - with closed covers	
5	513 69	IP 44 - with inserted plug and closed covers	

international plugs, adaptors and multi-outlets adaptors



Pack Cat.Nos International plugs

Pack	Cat.Nos	International plugs
20	503 26	British standard 13 A - 250 V~  2P+⊥
10	502 82	American standard - 15 A - 125 V~ Straight blade devices USE specification grade UL and CSA listed
20	502 04	2 pole 3 wire grounding plug moulded from high strength thermoplastic 2P - straight outlet
20	515 32	Italian standard - 10 A - 250 V~  2P+⊥ aligned, straight outlet with screw-type cable grip

Travel adaptors

With safety shutters
For connecting a plug to a different standard socket
○ White

10	503 82	German standard to French standard adaptor  2P+E - 16 A output - 3680 W at 230 V (countries: Germany, Spain, Austria, Portugal, Greece, Hungary, etc...) onto a French socket
10	503 83	British standard to French or German standard adaptor  2P+E - 13 A British standard plug to French or German standard socket

Multi - outlet adaptors

10/100	506 55	2P+⊥ German standard multi-outlet adaptors  2 front sockets With child protection
10/100	506 56	 3 front sockets With child protection
5	504 53	 3 lateral sockets - Without child protection
10	906 32	2P+⊥ French standard multi-outlet adaptor  3 lateral sockets With child protection

cord switches and door contact switch 2 A - 250 V~



Pack Cat.Nos Cord switches

Pack	Cat.Nos	Cord switches
20	401 87	Fluorescent Easy connection by cutting the 2 wires Double pole  White spotted
20	401 92	Coloured Easy connection by cutting the 2 wires Double pole  White
20	401 93	Old gold, old gold rocker
20	401 94	Black

Door contact switch

10	401 75	 Normally closed contactor complete with roller actuator Automatically illuminates cupboards upon opening of the door Single pole 2 A - 250 V
----	--------	--

OmniRex, automatic staircase time lag switch and pulse operated latching relay



6998 11



497 83



491 07

Pack	Cat.Nos	OmniRex - Plug-in time switches
1	6998 11	Manuel switch ON - Auto With 2P+ $\frac{1}{2}$ plug and 10/16 A socket base and 16 A socket With child protection Override/manual switch Mains hold accuracy Synchronous motor, 230 V, 50 Hz 1 contact NO 250 V/50 Hz, 16 A~ $\cos \varphi = 1$ OmniRex T - 24-hour programme German standard - With child protection Switching step 15 min Mini switching time 15 min Switching accuracy ± 5 min OmniRex W - 7-day programme German standard - With child protection Switching step 2 hours Mini switching time 2 hours Switching accuracy ± 30 min

		Automatic staircase time-lag switch 230 V - 50 Hz	
		• Switches a lighting circuit during a determined period • Controlled by illuminated push-button 50 mA max • 3 wire - connection • Output : 1 contact • Contact rating 10 A - 250 V~ - $\cos \varphi = 1$	
		Type of delay adjustable	Type
1	497 83	Electronic 0.5 to 10 min	Resettable

		Pulse operated latching relay surface-mounting				
		Single pole 10 A - 250 V~ - 50 Hz Ensures the switching off of fluorescent circuits				
		• 20 tubes 40 W - 1.20 m non-compensated • 40 tubes 40 W - 1.20 m compensated				
		Dimensions: 65 x 48 x 34 mm				
		<table><tr><th>a.c. control current voltage (Volts)</th><th>Current absorbed (Amperes)</th></tr><tr><td>230</td><td>0.03</td></tr></table>	a.c. control current voltage (Volts)	Current absorbed (Amperes)	230	0.03
a.c. control current voltage (Volts)	Current absorbed (Amperes)					
230	0.03					
10	491 07 ⁽¹⁾					

Lexic latching relays (p. 168)

(1) For use with push button (pulse) supply only
 When using 5 or more illuminated push-buttons connect a compensator to the terminals of the latching relay


OmniRex automatic staircase time lag switch and pulse operated latching relay

OmniRex - Technical details

Type	OmniRex T 24 hour programme	OmniRex W 7 day programme
Cat.Nos	6998 11	6998 12
Voltage/Frequency	230 V, 50 Hz	230 V, 50 Hz
Drive	Synchronous	Synchronous
Switching-dial	24 hours	7 days
Running reserve	no	no
Switching step	15 min	2 hours
Min. switching time	15 min	2 hours
Switching accuracy	± 5 min	± 30 min
Switching capacity Resistive 230 V $\cos \varphi = 1$	16 A~	16 A~
Contact	1 NO	1 NO
Protection	IP 20	IP 20

Automatic staircase time-lag switch

3-wire - connection 230 V~ - 50 Hz



Pulse operated latching relay

Connection of a 10 A - 250 V~ - 50 Hz - Single pole

