


LOC	
CE	
DIST	16

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

CAC Customer Layout Rev: D



Fiber Path

A - _____ - E
B - _____ - A

Right Side
Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

[illegible]

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED	
meters			
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

Restricted To:

P/N Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
Q/R	Jeremy Duncan	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
AP/V	Jeremy Duncan				
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex					
SCALE NTS	SIZE A2	DRAWING NO C- 1906056	SHEET 1 of 4		REV A

	A	Rev Per EC#	RELEASE		0/26/2007	-		JF	
P	LTR	REVISION	RECORD		DATE	DIN		AP	

Qty	U of M	Description	Item No.
2	piece	Trace Label	7
4	piece	Eyelet/Shrink tube assembly - White	6
AR	meter	2 fiber, 62.5/125, 2.0mm, Twinzip, Orange, OFNR (Riser)	5
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	4
2	piece	LC Connector Assy, MM	3
2	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

QFN Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
OK Jeremy Duncan		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Jeremy Duncan					
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex					
SCALE NTS		SIZE A2		DRAWING NO C- 1906056	
				SHEET 2 of 4	
				REV A	

THIS DRAWING IS A CONTROLLED DOCUMENT.

Part #	L (meters)	L (feet)	LC-Duplex Secure, Rose		LC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1906056-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	-
4-1906056-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	-
4-1906056-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	-
4-1906056-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	-
4-1906056-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	-
4-1906056-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	-
4-1906056-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	-
5-1906056-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-
5-1906056-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	-
5-1906056-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	-
5-1906056-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	-
5-1906056-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	-
5-1906056-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	-
5-1906056-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	-
5-1906056-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	-
5-1906056-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	-
5-1906056-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	-
6-1906056-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	-
6-1906056-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	-
6-1906056-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	-
6-1906056-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	-
6-1906056-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	-
6-1906056-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	-
6-1906056-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	-
6-1906056-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	-
6-1906056-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	-
6-1906056-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	-
7-1906056-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	-
7-1906056-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	-
7-1906056-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	-
7-1906056-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	-
7-1906056-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	-
7-1906056-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	-
7-1906056-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	-
7-1906056-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	-
7-1906056-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	-
7-1906056-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	-
8-1906056-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	-

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	D/26/2007	-	JF			
P	LTR	REVISION	RECORD	DATE	DIN	AP			

DIMENSIONS;
meters

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-

Restricted To:

WIN Cable Assy Configurator OK Jeremy Duncan APVD Jeremy Duncan		MATERIAL - HEAT TREAT -
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608
SCALE NTS	SIZE A2	DRAWING NO. C- 1906056
		SHEET 3 of 4 REV A


D

C

B

A

Per specification 107-1645-1

[illegible]

-Trace # - Human Readable

Logo

Made in XXX

X-XXXXXXXX-X


-Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1

[illegible]

—Trace # - Human Readable

Logo

Made in XXX

X-XXXXXXXX-X

—Part Number

—Country of Origin

This label is used on all lengths on this drawing.

				meters		0 PLG ± ± 1 PLG ± ± 2 PLG ± ± 3 PLG ± ± 4 PLG ± ±		VARIATION SPECIFICATIONS Jeremy Duncan APID Jeremy Duncan AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
								NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, LC-Duplex Secure to LC-Duplex	
P	LTR	REVISION RECORD	DATE	DN	APID	Restricted To:		SCALE	REV
								NTS	
								SIZE	
								A2	
								DRAWING NO	
								C- 1906056	
								SHEET	
								4 of 4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-1933287-1](#)