


HDSP-315x/316x Series

10 mm and 13 mm Slim Font Seven Segment Displays

AVAGO
TECHNOLOGIES

Data Sheet



Description

The HDSP-31xx Series of displays incorporates a new slim font character design. This slim font features narrow width, specially mitered segments to give a fuller appearance to the illuminated character. Faces of these displays are painted a neutral gray for enhanced on/off contrast.

All devices are available in either common anode or common cathode configuration with right hand decimal point. Low current versions are available in either AlGaAs red or HER.

Features

- Excellent appearance
- Slim font design
- Mitered corners, evenly illuminated segments
- Gray face for optimum on/off contrast
- Choice of colors: DH AlGaAs red, High Efficiency Red (HER), yellow, and green
- Low current available, AlGaAs red and HER choice of character size: 10 mm and 13 mm
- $\pm 50^\circ$ viewing angle
- Characterized for luminous intensity


Devices

AlGaAs Red Low Current HDSP-	HER Std. Current HDSP-	HER Low Current HDSP-	Yellow Std. Current HDSP-	Green Std. Current HDSP-	Description	Package Drawing
315H	315E	315L	N.A.	315G	Common Anode, 10 mm Display	A
316H	316E	316L	316Y	316G	Common Cathode, 10 mm Display	B

Part Numbering System

5082 - XXXX-XXXXXX


HDSP - XXXX-XXXX



Notes:

1. For codes not listed in the figure, refer to the respective datasheet or contact your nearest Avago representative for details.
2. Bin options refer to shippable bins for a part number. Color and Intensity Bins are typically restricted to 1 bin per tube (exceptions may apply). Refer to respective datasheet for specific bin limit information.

HDSP-315x/316x Series



Absolute Maximum Ratings

Description	AlGaAs Red Low Current	HER	HER Low Current	Yellow	Green	Units
Average Power per Segment or DP	37	105	52	105	105	mW
Peak Forward Current per Segment or DP	45	90 ^[2]	45	90 ^[5]	90 ^[7]	mA
DC Forward Current per Segment or DP	15 ^[1]	30 ^[3]	15 ^[4]	30 ^[6]	30 ^[8]	mA
Operating Temperature Range	-20 to 100		-40 to +100			°C
Storage Temperature Range			-40 to +100			°C
Reverse Voltage per Segment or DP			3.0			V
Wavesoldering Temperature for 3 seconds 1.59 mm below body			250			°C

Notes:

1. Derate above 91°C at 0.53 mA/°C.
2. See Figure 9 to establish pulsed conditions.
3. Derate above 53°C at 0.45 mA/°C.
4. Derate above 80°C at 0.38 mA/°C.
5. See Figure 10 to establish pulsed conditions.
6. Derate above 81°C at 0.52 mA/°C.
7. See Figure 11 to establish pulsed conditions.
8. Derate above 39°C at 0.37 mA/°C.

Electrical/Optical Characteristics at $T_A = 25^\circ\text{C}$

AlGaAs Red Low Current

Device Series	Parameter	Symbol	Min.	Typ.	Max.	Units	Test Conditions
HDSP-315/316H	Luminous Intensity/Segment ^[1,2] (Digit Average)	I _V	180	650		μcd	I _F = 1 mA
	Forward Voltage/Segment or DP	V _F		1.8	2.2	V	I _F = 1 mA
	Peak Wavelength	λ _{PEAK}		645		nm	
	Dominant Wavelength ^[3]	λ _d		637		nm	
	Reverse Voltage/Segment or DP ^[4]	V _R	3	15		V	I _R = 100 μA
	Thermal Resistance LED Junction-to-Pin	R _{θJ-PIN}		255		°C/W/Seg	

HER

Device Series	Parameter	Symbol	Min.	Typ.	Max.	Units	Test Conditions
HDSP-315/316E	Luminous Intensity/Segment ^[1,2] (Digit Average)	I _V	450	2600		μcd	I _F = 10 mA
	Forward Voltage/Segment or DP	V _F		1.9	2.5	V	I _F = 10 mA
	Peak Wavelength	λ _{PEAK}		635		nm	
	Dominant Wavelength ^[3]	λ _d		626		nm	
	Reverse Voltage/Segment or DP ^[4]	V _R	3	30		V	I _R = 100 μA
	Thermal Resistance LED Junction-to-Pin	R _{θJ-PIN}		200		°C/W/Seg	

HER Low Current

Device Series		Symbol	Min.	Typ.	Max.	Units	Test Conditions
HDSP-	Parameter						
315/316L	Luminous Intensity/Segment ^[1,2] (Digit Average)	I _V	180	370		μcd	I _F = 2 mA
	Forward Voltage/Segment or DP	V _F		2.1	2.5	V	I _F = 2 mA
	Peak Wavelength	λ _{PEAK}		635		nm	
	Dominant Wavelength ^[3]	λ _d		626		nm	
	Reverse Voltage/Segment or DP ^[4]	V _R	3	30		V	I _R = 100 μA
	Thermal Resistance LED Junction-to-Pin	R _{θJ-PIN}		200		°C/W/Seg	

Yellow

Device Series		Symbol	Min.	Typ.	Max.	Units	Test Conditions
HDSP-	Parameter						
316Y	Luminous Intensity/Segment ^[1,2] (Digit Average)	I _V	450	1800		μcd	I _F = 10 mA
	Forward Voltage/Segment or DP	V _F		2.0	2.5	V	I _F = 10 mA
	Peak Wavelength	λ _{PEAK}		583		nm	
	Dominant Wavelength ^[3]	λ _d		586		nm	
	Reverse Voltage/Segment or DP ^[4]	V _R	3	50		V	I _R = 100 μA
	Thermal Resistance LED Junction-to-Pin	R _{θJ-PIN}		200		°C/W/Seg	

Green

Device Series		Symbol	Min.	Typ.	Max.	Units	Test Conditions
HDSP-	Parameter						
315/316G	Luminous Intensity/Segment ^[1,2] (Digit Average)	I _V	450	5000		μcd	I _F = 10 mA
	Forward Voltage/Segment or DP	V _F		2.1	2.5	V	I _F = 10 mA
	Peak Wavelength	λ _{PEAK}		566		nm	
	Dominant Wavelength ^[3]	λ _d		571		nm	
	Reverse Voltage/Segment or DP ^[4]	V _R	3	50		V	I _R = 100 μA
	Thermal Resistance LED Junction-to-Pin	R _{θJ-PIN}		200		°C/W/Seg	

Notes:

1. Case temperature of device immediately prior to the intensity measurement is 25°C.
2. The digits are categorized for luminous intensity. The intensity category is designated by a letter on the side of the package.
3. The dominant wavelength, λ is derived from the CIE chromaticity diagram and is that single wavelength which defines the color of the device.
4. Typical specification for reference only. Do not exceed absolute maximum ratings.

AlGaAs Low Current




Figure 1. Maximum allowable average or DC current vs. ambient temperature.




Figure 2. Forward current vs. forward voltage.




Figure 3. Relative luminous intensity vs DC forward current.

HER, Yellow, and Green




Figure 4. Maximum tolerable peak current vs. pulse duration – HER.




Figure 5. Maximum tolerable peak current vs. pulse duration – Yellow.




Figure 6. Allowable peak current vs. pulse duration – Green.




Figure 7. Maximum allowable DC current per segment as a function of ambient temperature.




Figure 8. Forward current vs. forward voltage characteristics.




Figure 9. Relative luminous intensity vs. DC forward current.

HER Low Current




Figure 10. Maximum allowable average or DC current vs. ambient temperature.




Figure 11. Forward current vs. forward voltage.




Figure 12. Relative luminous intensity vs. DC forward current.

Intensity Bin Limits (mcd)

HER Low Current, AlGaAs Red Low Current

HDSP-31xL/H		
IV Bin Category	Min.	Max.
E	0.180	0.360
F	0.280	0.560
G	0.450	0.900
H	0.700	1.400
I	1.100	2.200
K	1.800	3.600
L	2.800	5.600
M	4.500	9.000
N	7.000	15.000

Color Categories

Dominant Wavelength (nm)			
Color	Bin	Min.	Max.
Yellow	1	581.50	585.00
	3	584.00	587.50
	2	586.50	590.00
	4	589.00	592.50
Green	2	573.00	577.00
	3	570.00	574.00
	4	567.00	571.00
	5	564.00	568.00

Note:

All categories are established for classification of products. Products may not be available in all categories. Please contact your local Avago representatives for further clarification/information.

HER Std. Current, Green Std. Current, Yellow Std. Current

HDSP-31xE/G/Y		
IV Bin Category	Min.	Max.
G	0.450	0.900
H	0.700	1.400
I	1.100	2.200
K	1.800	3.600
L	2.800	5.600
M	4.500	9.000
N	7.000	15.000

Electrical/Optical

For more information on electrical/optical characteristics, refer to Application Note 1005.

Contrast Enhancement

For information on contrast enhancement, refer to Application Note 1015.

Soldering/Cleaning

Cleaning agents from the ketone family (acetone, methyl ethyl ketone, etc.) and from the chlorinated hydrocarbon family (methylene chloride, trichloroethylene, carbon tetrachloride, etc.) are not recommended for cleaning LED parts. All of these various solvents attack or dissolve the encapsulating epoxies used to form the package of plastic LED parts.

For further information on soldering LEDs, refer to Application Note 1027.

For product information and a complete list of distributors, please go to our web site: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries. Data subject to change. Copyright © 2005-2014 Avago Technologies. All rights reserved. Obsoletes 5989-2640EN
AV02-1769EN - March 26, 2014

