

DB404-B



1-port omni exposed dipole antenna, 450–470 MHz, 360° HPBW, fixed electrical tilt

General Specifications

Antenna Type	Omni
Band	Single band
Color	Silver
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radiator Material	Aluminum
RF Connector Interface	N Male
RF Connector Location	End of flexible lead
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

Dimensions

Length	1524 mm 60 in
--------	-----------------

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	450 – 470 MHz
Polarization	Vertical

Electrical Specifications

Frequency Band, MHz	450–470
Gain, dBi	5.9
Beamwidth, Horizontal, degrees	360
Beamwidth, Vertical, degrees	27

DB404-B

Beam Tilt, degrees	0
VSWR Return loss, dB	1.5 14.0
Input Power per Port, maximum, watts	250

Mechanical Specifications

Wind Speed, maximum	161 km/h 100.041 mph
---------------------	------------------------

Packaging and Weights

Net Weight, without mounting kit	6.4 kg 14.11 lb
----------------------------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
CE	Compliant with the relevant CE product directives
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

DB365-OS	— Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.
----------	---

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
------------------	---