

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91829

SWITCH - BASIC

CATALOG LISTING

V3-1078

CK-L7800

V3-1078

PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE
7

RELEASE NO. PR 10089 REPLACES

CHECK

REVISIONS

04 JUN 84

AK

CHECK

15 APR 81

APR 81

APR 81

APR 81

APR 81

APR 81

APR 81



APR 81

APR 81

APR 81

APR 81

APR 81




NOTES

- 1 - TERMINALS ARE PLATED FOR SOLDERING
- 2 - IN INSPECTION, DO NOT BURN OUT - GOLD CONTACTS
- 3 - IN INSPECTION, DO NOT EXCEED 10 VDC, .1A RESISTIVE LOAD
- 4 - INSPECT SWITCH RESISTANCE PER CONTROL PLAN

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - - 6-14 OZ

RELEASE TRAVEL - - - - - .007 MIN

RELEASE FORCE - - - - - 4 OZ MIN

DIFFERENTIAL TRAVEL - - - .006-.016

OVERTRAVEL .040 MIN

FREE POSITION - - - - - .625 MAX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L22
1A-125 VAC



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. in	TOL. mil/in	DIM. in	TOL. mil/in
NO PLACES	X	1/64	X	0.010
ONE PLACE	X	0.4/64	X	0.38/64
TWO PLACES	X	0.16/64	X	0.12/64
THREE PLACES	X	0.10/64	X	0.08/64
ANGLES				

DESIGN UNITS ☐ METRIC

US CUSTOMARY ☒

WEIGHT .015 LB

FORMTEK

DRAWN

CHECK

REVISIONS

04 JUN 84

AK

CHECK

15 APR 81

APR 81

APR 81

APR 81

APR 81

APR 81

APR 81

APR 81

APR 81

APR 81

APR 81

APR 81