

Surface Mount Miniature Trimmers Single-Turn Cermet Sealed



The TS53 trimming potentiometer has been designed for surface mount applications and offers volumetric efficiency (5 x 5 x 2.7 mm) with high performance and stability.

The TS53 design is suitable for both manual or automatic operation, and can withstand wave, and reflow soldering techniques.

FEATURES


- 0.25 W at 70 °C
- For PCB version see T53Y series
- Wide ohmic range (10 Ω to 1 M Ω)
- Small size for optimum packing density
- Suitable for both manual or automatic operation
- RoHS compliant since data code 0445




RoHS
COMPLIANT

DIMENSIONS in millimeters (± 0.25 mm)

TS53YL




TS53YJ




Cruciform screwdriver slot
Ø 2.5, width 0.5
Deep: 0.55
Max. deep (center): 0.7

RECOMMENDED SOLDERING AREAS

TS53YL



TS53YJ




Tolerances unless otherwise specified ± 0.25 mm

Surface Mount Miniature Trimmers
Single-Turn Cermet Sealed

Vishay Sfernice

ELECTRICAL SPECIFICATIONS

Resistive Element	Cermet
Electrical Travel	$220^\circ \pm 15^\circ$
Resistance Range	10 Ω to 1 M Ω
Standard Series	1 - 2 - 5
Tolerance Standard	$\pm 20\%$
Variation Law	<div>linear</div> <div>CIRCUIT DIAGRAM</div> 

MECHANICAL SPECIFICATIONS

Mechanical Travel	$270^\circ \pm 10^\circ$
Operating Torque (max. Ncm)	1.5
End Stop Torque (max. Ncm)	3.5
Net Weight (max. g)	0.15
Terminals	Pure Sn (e3)

ENVIRONMENTAL SPECIFICATIONS

Temperature Range	- 55 $^\circ\text{C}$ to + 125 $^\circ\text{C}$
Climatic Category	55/125/56
Sealing	Sealed container IP67
MSL Level	4

PERFORMANCE			
TESTS	CONDITIONS	TYPICAL VALUES AND DRIFTS	
		$\frac{\Delta R_T}{R_T}$ (%)	$\frac{\Delta R_{1-2}}{R_{1-2}}$ (%)
Load Life	1000 hours at rated power 90°/30' - ambient temperature + 70 °C	± 2 % Contact resistance variation: $\Delta R < 1 \% R_n$	± 3 %
Climatic Sequence	Phase A dry heat 125 °C Phase B damp heat Phase C cold - 55 °C Phase D damp heat 5 cycles	± 2 %	± 3 %
Long Term Damp Heat	Temperature 40 °C - RH 93 % 56 days	± 2 % Dielectric strength: 1000 V RMS Insulation resistance: > 10 ⁴ MΩ	± 3 %
Thermal Shock	55 °C to + 125 °C - 5 cycles	± 1 %	$\frac{\Delta V_{1-2}}{V_{1-3}} \leq \pm 2 \%$
Rotational Life (Electrical and Mechanical)	100 cycles - rated power	± (3 % + 5 Ω)	
Shock	50 g - 11 ms 3 successive shocks in 3 directions	± 1 %	$\frac{\Delta V_{1-2}}{V_{1-3}} \leq \pm 1 \%$
Vibration	10 - 55 Hz 0.75 mm or 10 g - 6 hours	± 1 %	$\frac{\Delta V_{1-2}}{V_{1-3}} \leq \pm 1 \%$

STANDARD RESISTANCE ELEMENT DATA				
STANDARD RESISTANCE VALUES	LINEAR LAW			TYPICAL TCR - 55 °C + 125 °C
	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH ELEMENT	
Ω	W	V	mA	ppm/°C
10	0.25	1.58	158	± 100
20	↓	2.24	112	
50		3.54	71	
100		5.00	50	
200		7.07	35	
500		11.2	22	
1K		15.8	16	
2K		22.4	11	
5K		35.4	7	
10K		50.0	5	
20K		70.7	3.5	
50K		112	2.2	
100K	0.25	158	1.6	
200K	0.20	200	1.0	
500K	0.08	200	0.4	
1M	0.04	200	0.2	

MARKING

VISHAY trademark, ohmic value, manufacturing date.

The ohmic value is indicated by a 3 figure code, the first two are significant figures, the third one is the multiplier.

Example:

- 100 = 10 Ω
- 101 = 100 Ω
- 102 = 1000 Ω
- 503 = 50 000 Ω

SOLDERING RECOMMENDATIONS

See Application notes

CAUTION

Reflow soldering must be done within 72 h while stored under a max. temperature of 30 °C, 60 % RH after opening the dry pack envelope.

RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the hermetic bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.


After more than 72 h under these conditions, moisture content will be too high for reflow soldering.

In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

- 192 h at 40 °C + 5 °C/- 0 °C and < 5 % RH (dry air/nitrogen) or
- 96 h at 60 °C + 5 °C and < 5 % RH for all device containers (not suitable for reel) or
- 24 h at 125 °C + 5 °C (not suitable for reel)

PACKAGING

On tape and reel of 500 pieces, code R10 (TR500) and 2000 pieces, code R20 (TR2000)



Cover tape panel strength specifications EIA 481 A and CEI 60286-3.

DRYPACK

Devices are packed in moisture barrier bags to prevent the products from moisture absorption during transportation and storage. Each bag contains a desiccant.

SAP ORDERING INFORMATION (Part Number 15 digits)

T	S	5	3	Y	L	5	0	4	M	R	1	0			
MODEL		STYLE		OHMIC VALUE		TOLERANCE		PACKAGING		SPECIAL NUMBER					
		YL YJ		From 10 Ω to 1 MΩ 504 = 500 kΩ		± 20 %		R10 = Reel 500 pieces R20 = Reel 2000 pieces		(if applicable) Given by VISHAY for custom design					

PART NUMBER DESCRIPTION (for information only)

TS53	YL	500K	20 %		TR500	e3
MODEL	STYLE	VALUE	TOLERANCE	SPECIAL	PACKAGING	LEAD (Pb)-FREE



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[TS53YJ200-20%-TR](#) [TS53YL 20 20%TR](#) [TS53YJ 100 20%TR](#) [TS53YJ 10K 20%TR](#) [TS53YJ 1K 20%RB2](#) [TS53YJ](#)
[1K 20%TR](#) [TS53YJ 20K 20%TR](#) [TS53YL 100K 20%TR](#) [TS53YL 10K 20%TR](#) [TS53YL 1K 20%TR](#) [TS53YL 200K](#)
[20%TR](#) [TS53YL 2K 20%TR](#) [TS53YL 50K 20%TR](#) [TS53YJ 100K 10%TR](#) [TS53YJ 1M 20%TR](#) [TS53YJ502MR10](#)
[TS53YL502MR10](#) [TS53YJ203MR10](#) [TS53YL102MR10](#) [TS53YJ101MR10](#) [TS53YJ102MR10](#) [TS53YJ103MR10](#)
[TS53YJ104MR10](#) [TS53YJ105MR10](#) [TS53YJ201MR10](#) [TS53YJ202MR10](#) [TS53YJ204MR10](#) [TS53YJ500MR10](#)
[TS53YJ501MR10](#) [TS53YJ503MR10](#) [TS53YJ504MR10](#) [TS53YL101MR10](#) [TS53YL103MR10](#) [TS53YL104MR10](#)
[TS53YL105MR10](#) [TS53YL200MR10](#) [TS53YL201MR10](#) [TS53YL202MR10](#) [TS53YL203MR10](#) [TS53YL204MR10](#)
[TS53YL500MR10](#) [TS53YL501MR10](#) [TS53YL503MR10](#) [TS53YL504MR10](#) [TS53YL100MR10](#) [TS53YJ205MR10](#)