


ZXMP7A17K

70V P-channel enhancement mode MOSFET

Summary

$V_{DSS}=70V$: $R_{DS(on)}=0.16\Omega$

$I_D=5.7A$




Description

This new generation of trench MOSFETs from Zetex utilizes a unique structure that combines the benefits of low on-resistance with fast switching speed. This makes them ideal for high efficiency, low voltage power management applications.


Features

- Low on-resistance
- Fast switching speed
- Low threshold
- Low gate drive
- DPAK package



Applications

- DC-DC converters
- Power management functions
- Disconnect switches
- Motor control
- Class D audio output stages



Pinout - Top view

Ordering information

Device	Reel size (inches)	Tape width (mm)	Quantity per reel
ZXMP7A17KTC	13	12	4,000

Device marking

ZXMP
7A17

ZXMP7A17K

Absolute maximum ratings

Parameter	Symbol	Limit	Unit
Drain-source voltage	V_{DSS}	-70	V
Gate-source voltage	V_{GS}	± 20	V
Continuous drain current @ $V_{GS}=10V$; $T_A=25^\circ C$ ^(b) @ $V_{GS}=10V$; $T_A=25^\circ C$ ^(b) @ $V_{GS}=10V$; $T_A=25^\circ C$ ^(a)	I_D	-5.7 -4.6 -3.8	A
Pulsed drain current ^(c)	I_{DM}	-17.7	A
Continuous source current (body diode) ^(b)	I_S	-9.2	A
Pulsed source current (body diode) ^(c)	I_{SM}	-17.7	A
Power dissipation at $T_A = 25^\circ C$ ^(a) Linear derating factor	P_D	4.17 33.3	W mW/°C
Power dissipation at $T_A = 25^\circ C$ ^(b) Linear derating factor	P_D	9.25 74	W mW/°C
Power dissipation at $T_A = 25^\circ C$ ^(d) Linear derating factor	P_D	2.11 16.8	W mW/°C
Operating and storage temperature range	T_j, T_{stg}	-55 to +150	°C







Thermal resistance

Parameter	Symbol	Limit	Unit
Junction to ambient ^(a)	$R_{\theta JA}$	30	°C/W
Junction to ambient ^(b)	$R_{\theta JA}$	13.5	°C/W
Junction to ambient ^(c)	$R_{\theta JA}$	59.1	°C/W

NOTES:

- (a) For a device surface mounted on 50mm x 50mm x 1.6mm FR4 PCB with high coverage of single sided 2oz copper, in still air conditions.
- (b) For a device surface mounted on FR4 PCB measured at $t \leq 10$ sec.
- (c) Repetitive rating 50mm x 50mm x 1.6mm FR4 PCB, $D=0.02$ pulse width=300 μs - pulse width limited by maximum junction temperature.
- (d) For a device surface mounted on 25mm x 25mm x 1.6mm FR4 PCB with high coverage of single sided 1oz copper, in still air conditions.

Characteristics



ZXMP7A17K

ELECTRICAL CHARACTERISTICS (at Tamb = 25°C unless otherwise stated)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Static						
Drain-source breakdown voltage	V _{(BR)DSS}	-70			V	I _D = -250μA, V _{GS} =0V
Zero gate voltage drain current	I _{DSS}			-1	μA	V _{DS} = -70V, V _{GS} =0V
Gate-body leakage	I _{GSS}			100	nA	V _{GS} =±20V, V _{DS} =0V
Gate-source threshold voltage	V _{GS(th)}	-1.0			V	I _D = -250μA, V _{DS} =V _{GS}
Static drain-source on-state resistance ^(*)	R _{DS(on)}			0.16	Ω	V _{GS} = -10V, I _D = -2.1A
				0.25	Ω	V _{GS} = -4.5V, I _D = -1.7A
Forward transconductance ^{(*)(‡)}	g _{fs}		4.4		S	V _{DS} = -15V, I _D = -2.1A
Dynamic ^(‡)						
Input capacitance	C _{iss}		635		pF	V _{DS} = -40V, V _{GS} =0V f=1MHz
Output capacitance	C _{Oss}		52		pF	
Reverse transfer capacitance	C _{rss}		42.5		pF	
Switching ^{(†) (‡)}						
Turn-on-delay time	t _{d(on)}		2.5		ns	V _{DD} = -35V, I _D = -1A R _G ≐6.0Ω, V _{GS} = -10V
Rise time	t _r		3.4		ns	
Turn-off delay time	t _{d(off)}		27.9		ns	
Fall time	t _f		8		ns	
Total gate charge	Q _g		9.6		nC	V _{DS} = -35V, V _{GS} = -5V I _D = -2.1A
Total gate charge	Q _g		18		nC	V _{DS} = -35V, V _{GS} = -10V I _D = -2.1A
Gate-source charge	Q _{gs}		1.77		nC	
Gate drain charge	Q _{gd}		3.66		nC	
Source-drain diode						
Diode forward voltage ^(*)	V _{SD}		-0.85	-0.95	V	T _j =25°C, I _S = -2.0A, V _{GS} =0V
Reverse recovery time ^(‡)	t _{rr}		29.8		ns	T _j =25°C, I _S = -2.1A, di/dt=100A/μs
Reverse recovery charge ^(‡)	Q _{rr}		38.5		nC	







NOTES:

(*) Measured under pulsed conditions. Pulse width $\leq 300\mu s$; duty cycle $\leq 2\%$.

(†) Switching characteristics are independent of operating junction temperature.


(‡) For design aid only, not subject to production testing.

Typical characteristics




ZXMP7A17K

Typical characteristics



Capacitance v Drain-Source Voltage




Gate-Source Voltage v Gate Charge

ZXMP7A17K

Intentionally left blank

ZXMP7A17K

Package outline - DPAK



DIM	Inches		Millimeters		DIM	Inches		Millimeters	
	Min	Max	Min	Max		Min	Max	Min	Max
A	0.086	0.094	2.18	2.39	e	0.090 BSC		2.29 BSC	
A1	-	0.005	-	0.127	H	0.370	0.410	9.40	10.41
b	0.020	0.035	0.508	0.89	L	0.055	0.070	1.40	1.78
b2	0.030	0.045	0.762	1.14	L1	0.108 REF		2.74 REF	
b3	0.205	0.215	5.21	5.46	L2	0.020 BSC		0.508 BSC	
c	0.018	0.024	0.457	0.61	L3	0.035	0.065	0.89	1.65
c2	0.018	0.023	0.457	0.584	L4	0.025	0.040	0.635	1.016
D	0.213	0.245	5.41	6.22	L5	0.045	0.060	1.14	1.52
D1	0.205	-	5.21	-	Θ1°	0°	10°	0°	10°
E	0.250	0.265	6.35	6.73	Θ°	0°	15°	0°	15°
E1	0.170	-	4.32	-	-	-	-	-	-

Note: Controlling dimensions are in inches. Approximate dimensions are provided in millimeters

Europe	Americas	Asia Pacific	Corporate Headquarters
Zetex GmbH Streitfeldstraße 19 D-81673 München Germany	Zetex Inc 700 Veterans Memorial Highway Hauppauge, NY 11788 USA	Zetex (Asia Ltd) 3701-04 Metroplaza Tower 1 Hing Fong Road, Kwai Fong Hong Kong	Zetex Semiconductors plc Zetex Technology Park, Chadderton Oldham, OL9 9LL United Kingdom
Telefon: (49) 89 45 49 49 0 Fax: (49) 89 45 49 49 49 europe.sales@zetex.com	Telephone: (1) 631 360 2222 Fax: (1) 631 360 8222 usa.sales@zetex.com	Telephone: (852) 26100 611 Fax: (852) 24250 494 asia.sales@zetex.com	Telephone: (44) 161 622 4444 Fax: (44) 161 622 4446 hq@zetex.com

For international sales offices visit www.zetex.com/offices

Zetex products are distributed worldwide. For details, see www.zetex.com/salesnetwork

This publication is issued to provide outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contact or be regarded as a representation relating to the products or services concerned. The company reserves the right to alter without notice the specification, design, price or conditions of supply of any product or service.