


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		Y	REVISED PER ECO-12-011709	26JUN2012	RW	SY

D

C

B

A



- 1. .000050 MIN THK NICKEL UNDERPLATE OVER ENTIRE CONTACT.
- 2. .000150 MIN BRIGHT TIN/LEAD OVER ENTIRE CONTACT.
- 3. .000100 MIN THK BRIGHT TIN/LEAD IN ZONE 1.
- 4. GOLD FLASH IN LOCALIZED GOLD PLATE AREA.
- 5. .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 6. .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 7. TO BE APPLIED PER AMP APPLICATION SPEC 114-16015.
- 8. RECOMMENDED HOLE SIZE IS .031-.035 DIA.
- 9. FOR SOLDERABILITY SEE AMP PRODUCT SPEC 108-9024.
- 10. .000150 MIN TIN-LEAD IN ZONE 2.
- 11. AREA TO BE UNPLATED (-9 ONLY).
- 12. GOLD FLASH IN ZONE 1. .000150 MIN TIN IN ZONE 3.
- 13. GOLD FLASH IN ZONE 1.
- 14. GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL IN THIS AREA.

D


C

88997

B

A

	161314	1-88997-4
	151314	1-88997-3
	191214	1-88997-2
OBSOLETE	1011	88997-9
	136	88997-5
	135	88997-4
SUPERSEDED BY 88997-5	134	88997-3
	129	88997-2
	FINISH	PART NO



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B. MCMASTER 10MAR04		TE Connectivity			
DIMENSIONS: INCHES			CHK S. BOLASH 10MAR04					
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 10MAR04		NAME CONTACT, SOLDER TAB, FFC, .100 ϕ	
			0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-9024			
			MATERIAL PH. BRONZE .010 THK		APPLICATION SPEC 114-16015			
SEE TABLE			WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C=88997	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 10:1			SHEET 1 of 1		REV Y