




THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND ITS SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE. SINCE THE USER SHALL MAKE THE FINAL DECISION ON THE DESIGN, THE USER ASSUMES ALL LIABILITY FOR THE DESIGN, CONSTRUCTION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

DATE	REV	REVISION RECORD	APP	DR	CK
8-08	09	NC	ECO	31056	RCW BS TK

SK10759



NOTES:

1. MATERIALS AND FINISHES:

INSULATOR: GLASS FILLED POLYESTER PER MIL-M-24519 UL 94V-0, BLUE COLOR.
CONTACTS: PRECISION MACHINED COPPER ALLOY WITH BERYLLIUM COPPER CLIP,
0.000050 [1.27µ] GOLD OVER NICKEL PLATE.

SHELLS: STAINLESS STEEL, PASSIVATE.

2. ELECTRICAL CHARACTERISTICS:

CONTACT CURRENT RATING: 7.5 AMPERES NOMINAL.
INITIAL CONTACT RESISTANCE: 0.008 OHMS MAXIMUM.
INSULATOR RESISTANCE: 5 G OHMS.
WORKING VOLTAGE: 300 V r.m.s.

3. TEMPERATURE RANGE: -55°C TO +125°C.

4. DIMENSIONS ARE IN INCHES [MILLIMETERS].

		POSITRONIC INDUSTRIES INC.		FSCM 28198	
		www.connectpositronic.com			
DECIMAL TOL.		CBM SERIES	SCALE	DRAWN BY	
± 0.015 [0.38]			N.T.S.	B SHELLBY	
ANGULAR TOL.				APPROVED BY	
± 5°				R WILLIAMS	
DATE		DRAWING NUMBER		REV.	
8-05-09		SK10759		NC	
		CBM7W2S2000S			