






WAFER: 15% GLASS FILLED POLYESTER
TO UL 94V-0.
COLOUR: BLACK.

PINS: (0.650)/.0255 SQ.
BRASS WIRE.
PLATED AS PER
SHEETS 2 TO 6.



NOTES
2. RECOMMENDED PCB THICKNESS: 1.6MM
3. PRODUCT SPECIFICATION: PS-99020-0001



REVISE PIN DIM
EC NO: S2012-0325
DRWN:SKANG
CHKD:ATSEE
APPR:MLONG
REV
M2

QUALITY SYMBOLS
F A = 0
F B = 0
F C = 0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± 0.05 ± .002
1 PLACE ± --- ± ---
ANGULAR ± ---°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS


DIMENSION STYLE
MM ONLY
DRAWN BY DB DATE 16/07/87
CHECKED BY DB DATE 1987/07/16
APPROVED BY DB DATE 1987/07/16
MATERIAL NO.
SEE TABLE
SIZE A3
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SCALE NTS
DESIGN UNITS METRIC
THIRD ANGLE PROJECTION
C-GRID III
DUAL ROW RIGHT
ANGLE HEADER
MOLEX INCORPORATED
SDA-90122
SHEET NO. 1 OF 6

CKT SIZE	DIM. " A "		DIM. " B " ^(+0.20 -0.35 +0.008 -0.014)		CKT SIZE	DIM. " A "		DIM. " B " ^(±0.20 ±.008)	
2X 1	_____		(2.54)	.100	2X21	(50.80)	2.000	(53.34)	2.100
2X 2	(2.54)	.100	(5.08)	.200	2X22	(53.34)	2.100	(55.88)	2.200
2X 3	(5.08)	.200	(7.62)	.300	2X23	(55.88)	2.200	(58.42)	2.300
2X 4	(7.62)	.300	(10.16)	.400	2X24	(58.42)	2.300	(60.96)	2.400
2X 5	(10.16)	.400	(12.70)	.500	2X25	(60.96)	2.400	(63.50)	2.500
2X 6	(12.70)	.500	(15.24)	.600	2X26	(63.50)	2.500	(66.04)	2.600
2X 7	(15.24)	.600	(17.78)	.700	2X27	(66.04)	2.600	(68.58)	2.700
2X 8	(17.78)	.700	(20.32)	.800	2X28	(68.58)	2.700	(71.12)	2.800
2X 9	(20.32)	.800	(22.86)	.900	2X29	(71.12)	2.800	(73.66)	2.900
2X10	(22.86)	.900	(25.40)	1.000	2X30	(73.66)	2.900	(76.20)	3.000
2X11	(25.40)	1.000	(27.94)	1.100	2X31	(76.20)	3.000	(78.74)	3.100
2X12	(27.94)	1.100	(30.48)	1.200	2X32	(78.74)	3.100	(81.28)	3.200
2X13	(30.48)	1.200	(33.02)	1.300	2X33	(81.28)	3.200	(83.82)	3.300
2X14	(33.02)	1.300	(35.56)	1.400	2X34	(83.82)	3.300	(86.36)	3.400
2X15	(35.56)	1.400	(38.10)	1.500	2X35	(86.36)	3.400	(88.90)	3.500
2X16	(38.10)	1.500	(40.64)	1.600	2X36	(88.90)	3.500	(91.44)	3.600
2X17	(40.64)	1.600	(43.18)	1.700	2X37	(91.44)	3.600	(93.98)	3.700
2X18	(43.18)	1.700	(45.72)	1.800	2X38	(93.98)	3.700	(96.52)	3.800
2X19	(45.72)	1.800	(48.26)	1.900	2X39	(96.52)	3.800	(99.06)	3.900
2X20	(48.26)	1.900	(50.80)	2.000	2X40	(99.06)	3.900	(101.60)	4.000

NOTES

1. FOR ASSY NUMBERS WITH FINISH OPTIONS
AND DIM'S C & D SEE SHEETS 2 TO 6.



	10	9	8	7	6	5	4	3	2	1	
F		CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.		CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.	F
		2 X 1	90122-0041	90122-0681	90122-0841		2 X 1	90122-0081	90122-0721	90122-0881	
		2 X 2	▲ -0042	▲ -0682	▲ -0842		2 X 2	▲ -0082	▲ -0722	▲ -0882	
		2 X 3	-0043	-0683	-0843		2 X 3	-0083	-0723	-0883	
		2 X 4	-0044	-0684	-0844		2 X 4	-0084	-0724	-0884	
		2 X 5	-0045	-0685	-0845		2 X 5	-0085	-0725	-0885	
		2 X 6	-0046	-0686	-0846		2 X 6	-0086	-0726	-0886	
		2 X 7	-0047	-0687	-0847		2 X 7	-0087	-0727	-0887	
		2 X 8	-0048	-0688	-0848		2 X 8	-0088	-0728	-0888	
		2 X 9	-0049	-0689	-0849		2 X 9	-0089	-0729	-0889	
		2 X 10	-0050	-0690	-0850		2 X 10	-0090	-0730	-0890	
		2 X 11	-0051	-0691	-0851		2 X 11	-0091	-0731	-0891	
		2 X 12	-0052	-0692	-0852		2 X 12	-0092	-0732	-0892	
		2 X 13	-0053	-0693	-0853		2 X 13	-0093	-0733	-0893	
		2 X 14	-0054	-0694	-0854		2 X 14	-0094	-0734	-0894	
		2 X 15	-0055	-0695	-0855		2 X 15	-0095	-0735	-0895	
		2 X 16	-0056	-0696	-0856		2 X 16	-0096	-0736	-0896	
		2 X 17	-0057	-0697	-0857		2 X 17	-0097	-0737	-0897	
		2 X 18	-0058	-0698	-0858		2 X 18	-0098	-0738	-0898	
		2 X 19	-0059	-0699	-0859		2 X 19	-0099	-0739	-0899	
		2 X 20	-0060	-0700	-0860		2 X 20	-0100	-0740	-0900	
		2 X 21	-0061	-0701	-0861		2 X 21	-0101	-0741	-0901	
		2 X 22	-0062	-0702	-0862		2 X 22	-0102	-0742	-0902	
		2 X 23	-0063	-0703	-0863		2 X 23	-0103	-0743	-0903	
		2 X 24	-0064	-0704	-0864		2 X 24	-0104	-0744	-0904	
		2 X 25	-0065	-0705	-0865		2 X 25	-0105	-0745	-0905	
		2 X 26	-0066	-0706	-0866		2 X 26	-0106	-0746	-0906	
		2 X 27	-0067	-0707	-0867		2 X 27	-0107	-0747	-0907	
		2 X 28	-0068	-0708	-0868		2 X 28	-0108	-0748	-0908	
		2 X 29	-0069	-0709	-0869		2 X 29	-0109	-0749	-0909	
		2 X 30	-0070	-0710	-0870		2 X 30	-0110	-0750	-0910	
		2 X 31	-0071	-0711	-0871		2 X 31	-0111	-0751	-0911	
		2 X 32	-0072	-0712	-0872		2 X 32	-0112	-0752	-0912	
		2 X 33	-0073	-0713	-0873		2 X 33	-0113	-0753	-0913	
		2 X 34	-0074	-0714	-0874		2 X 34	-0114	-0754	-0914	
		2 X 35	-0075	-0715	-0875		2 X 35	-0115	-0755	-0915	
		2 X 36	-0076	-0716	-0876		2 X 36	-0116	-0756	-0916	
		2 X 37	-0077	-0717	-0877		2 X 37	-0117	-0757	-0917	
		2 X 38	-0078	-0718	-0878		2 X 38	-0118	-0758	-0918	
		2 X 39	▼ -0079	▼ -0719	▼ -0879		2 X 39	▼ -0119	▼ -0759	▼ -0919	
		2 X 40	90122-0080	90122-0720	90122-0880		2 X 40	90122-0120	90122-0760	90122-0920	
E		DIM C (± 0.20) $\pm .008$ (5.75) .226					DIM C (± 0.20) $\pm .008$ (5.75) .226				E
D		DIM D (± 0.25) $\pm .010$ (2.90) .114					DIM D (± 0.25) $\pm .010$ (4.50) .177				D
C											C
B											B

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325 2011/10/21 DRWN:SKANG CHKD:ATSEE 2011/10/31 APPR:MLONG 2011/10/31			DESCRIPTION	QUALITY SYMBOLS FA=0 FE=0 FP=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		mm			INCH	DRAWN BY DATE		TITLE C-GRID III DUAL ROW RIGHT ANGLE HEADER				
4 PLACES		± ---			± ---	DB 16/07/87						
3 PLACES		± ---			± ---	CHECKED BY DATE						
2 PLACES		± 0.05			± .002	DB 1987/07/16		MOLEX INCORPORATED				
1 PLACE		± ---			± ---	APPROVED BY DATE						
						DB 1987/07/16						
		ANGULAR ± ---°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SDA-90122		3 OF 6				
M2		REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

	10		9	8	7	6	5	4	3	2	1																													
F	CIRCUIT SIZE 2 X 1 2 X 2 2 X 3 2 X 4 2 X 5 2 X 6 2 X 7 2 X 8 2 X 9 2 X 10 2 X 11 2 X 12 2 X 13 2 X 14 2 X 15 2 X 16 2 X 17 2 X 18 2 X 19 2 X 20 2 X 21 2 X 22 2 X 23 2 X 24 2 X 25 2 X 26 2 X 27 2 X 28 2 X 29 2 X 30 2 X 31 2 X 32 2 X 33 2 X 34 2 X 35 2 X 36 2 X 37 2 X 38 2 X 39 2 X 40 DIM C (±0.20) ±.008 (6.75) .266 DIM D (±0.25) ±.010 (4.50) .177	CIRCUIT SIZE	PLATING TYPE A PART NO.	PLATING TYPE E PART NO.	PLATING TYPE F PART NO.								F																											
90122-0161		90122-0801	90122-0961																																					
▲ -0162		▲ -0802	▲ -0962																																					
-0163		-0803	-0963																																					
-0164		-0804	-0964																																					
-0165		-0805	-0965																																					
-0166		-0806	-0966																																					
-0167		-0807	-0967																																					
-0168		-0808	-0968																																					
-0169		-0809	-0969																																					
-0170		-0810	-0970																																					
-0171		-0811	-0971																																					
-0172		-0812	-0972																																					
-0173		-0813	-0973																																					
-0174		-0814	-0974																																					
-0175		-0815	-0975																																					
-0176		-0816	-0976																																					
-0177		-0817	-0977																																					
-0178		-0818	-0978																																					
-0179		-0819	-0979																																					
-0180		-0820	-0980																																					
-0181		-0821	-0981																																					
-0182		-0822	-0982																																					
-0183		-0823	-0983																																					
-0184		-0824	-0984																																					
-0185		-0825	-0985																																					
-0186		-0826	-0986																																					
-0187		-0827	-0987																																					
-0188		-0828	-0988																																					
-0189		-0829	-0989																																					
-0190		-0830	-0990																																					
-0191		-0831	-0991																																					
-0192		-0832	-0992																																					
-0193		-0833	-0993																																					
-0194		-0834	-0994																																					
-0195		-0835	-0995																																					
-0196		-0836	-0996																																					
-0197		-0837	-0997																																					
-0198		-0838	-0998																																					
▼ -0199		▼ -0839	▼ -0999																																					
90122-0200	90122-0840	90122-1000																																						
NOTES: FOR PLATING VARIATIONS SEE ENG.STD. SDES-99000-0003.																																								
A	REVISE PIN DIM EC NO: S2012-0325 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2011/10/21 2011/10/31 2011/10/31	DESCRIPTION M2 REV	QUALITY SYMBOLS F A =0 F G =0 F P =0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.05</td><td>± .002</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr><tr><td colspan="3">ANGULAR ± ---°</td></tr></table> DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.05	± .002	1 PLACE	± ---	± ---	ANGULAR ± ---°			DIMENSION STYLE MM ONLY <table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>DB</td><td>16/07/87</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>DB</td><td>1987/07/16</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>DB</td><td>1987/07/16</td></tr></table> MATERIAL NO. SEE TABLE SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	DRAWN BY	DATE	DB	16/07/87	CHECKED BY	DATE	DB	1987/07/16	APPROVED BY	DATE	DB	1987/07/16	SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION C-GRID III DUAL ROW RIGHT ANGLE HEADER	MOLEX MOLEX INCORPORATED DOCUMENT NO. SDA-90122 SHEET NO. 4 OF 6	A
	mm	INCH																																						
4 PLACES	± ---	± ---																																						
3 PLACES	± ---	± ---																																						
2 PLACES	± 0.05	± .002																																						
1 PLACE	± ---	± ---																																						
ANGULAR ± ---°																																								
DRAWN BY	DATE																																							
DB	16/07/87																																							
CHECKED BY	DATE																																							
DB	1987/07/16																																							
APPROVED BY	DATE																																							
DB	1987/07/16																																							
tb_frame_A3_P_AM_T Rev. F 2009/06/18	9	8	7	6	5	4	3	2	1																															

	10		9		8		7		6		5		4		3		2		1				
F			CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.			CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.	F
			2 X 1		90122-0281		90122-0441		90122-0601		90122-1081			2 X 1		90122-0201		90122-0361		90122-0521		90122-1001	
			2 X 2		▲ -0282		▲ -0442		▲ -0602		▲ -1082			2 X 2		▲ -0202		▲ -0362		▲ -0522		▲ -1002	
			2 X 3		-0283		-0443		-0603		-1083			2 X 3		-0203		-0363		-0523		-1003	
			2 X 4		-0284		-0444		-0604		-1084			2 X 4		-0204		-0364		-0524		-1004	
			2 X 5		-0285		-0445		-0605		-1085			2 X 5		-0205		-0365		-0525		-1005	
			2 X 6		-0286		-0446		-0606		-1086			2 X 6		-0206		-0366		-0526		-1006	
			2 X 7		-0287		-0447		-0607		-1087			2 X 7		-0207		-0367		-0527		-1007	
			2 X 8		-0288		-0448		-0608		-1088			2 X 8		-0208		-0368		-0528		-1008	
			2 X 9		-0289		-0449		-0609		-1089			2 X 9		-0209		-0369		-0529		-1009	
			2 X 10		-0290		-0450		-0610		-1090			2 X 10		-0210		-0370		-0530		-1010	
			2 X 11		-0291		-0451		-0611		-1091			2 X 11		-0211		-0371		-0531		-1011	
			2 X 12		-0292		-0452		-0612		-1092			2 X 12		-0212		-0372		-0532		-1012	
			2 X 13		-0293		-0453		-0613		-1093			2 X 13		-0213		-0373		-0533		-1013	
			2 X 14		-0294		-0454		-0614		-1094			2 X 14		-0214		-0374		-0534		-1014	
			2 X 15		-0295		-0455		-0615		-1095			2 X 15		-0215		-0375		-0535		-1015	
			2 X 16		-0296		-0456		-0616		-1096			2 X 16		-0216		-0376		-0536		-1016	
			2 X 17		-0297		-0457		-0617		-1097			2 X 17		-0217		-0377		-0537		-1017	
			2 X 18		-0298		-0458		-0618		-1098			2 X 18		-0218		-0378		-0538		-1018	
			2 X 19		-0299		-0459		-0619		-1099			2 X 19		-0219		-0379		-0539		-1019	
			2 X 20		-0300		-0460		-0620		-1100			2 X 20		-0220		-0380		-0540		-1020	
			2 X 21		-0301		-0461		-0621		-1101			2 X 21		-0221		-0381		-0541		-1021	
			2 X 22		-0302		-0462		-0622		-1102			2 X 22		-0222		-0382		-0542		-1022	
			2 X 23		-0303		-0463		-0623		-1103			2 X 23		-0223		-0383		-0543		-1023	
			2 X 24		-0304		-0464		-0624		-1104			2 X 24		-0224		-0384		-0544		-1024	
			2 X 25		-0305		-0465		-0625		-1105			2 X 25		-0225		-0385		-0545		-1025	
			2 X 26		-0306		-0466		-0626		-1106			2 X 26		-0226		-0386		-0546		-1026	
			2 X 27		-0307		-0467		-0627		-1107			2 X 27		-0227		-0387		-0547		-1027	
			2 X 28		-0308		-0468		-0628		-1108			2 X 28		-0228		-0388		-0548		-1028	
			2 X 29		-0309		-0469		-0629		-1109			2 X 29		-0229		-0389		-0549		-1029	
			2 X 30		-0310		-0470		-0630		-1110			2 X 30		-0230		-0390		-0550		-1030	
			2 X 31		-0311		-0471		-0631		-1111			2 X 31		-0231		-0391		-0551		-1031	
			2 X 32		-0312		-0472		-0632		-1112			2 X 32		-0232		-0392		-0552		-1032	
			2 X 33		-0313		-0473		-0633		-1113			2 X 33		-0233		-0393		-0553		-1033	
			2 X 34		-0314		-0474		-0634		-1114			2 X 34		-0234		-0394		-0554		-1034	
			2 X 35		-0315		-0475		-0635		-1115			2 X 35		-0235		-0395		-0555		-1035	
			2 X 36		-0316		-0476		-0636		-1116			2 X 36		-0236		-0396		-0556		-1036	
			2 X 37		-0317		-0477		-0637		-1117			2 X 37		-0237		-0397		-0557		-1037	
			2 X 38		-0318		-0478		-0638		-1118			2 X 38		-0238		-0398		-0558		-1038	
			2 X 39		▼ -0319		▼ -0479		▼ -0639		▼ -1119			2 X 39		▼ -0239		▼ -0399		▼ -0559		▼ -1039	
			2 X 40		90122-0320		90122-0480		90122-0640		90122-1120			2 X 40		90122-0240		90122-0400		90122-0560		90122-1040	

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM		EC NO: S2012-0325		2011/10/21 DRWN:SKANG		2011/10/31 CHKD:ATSEE		2011/10/31 APPR:MLONG		DESCRIPTION	REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION			
															MM ONLY		NTS	METRIC				
													4 PLACES	± ---	± ---	DRAWN BY		DATE	TITLE C-GRID III DUAL ROW RIGHT ANGLE HEADER  MOLEX INCORPORATED			
													3 PLACES	± ---	± ---	CHECKED BY		DATE				
													2 PLACES	± 0.05	± .002	DB		1987/07/16				
													1 PLACE	± ---	± ---	APPROVED BY		DATE				
													ANGULAR		± ---°	DB		1987/07/16				
												DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
														SEE TABLE		SDA-90122		5 OF 6				
M2														SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

	10	9	8	7	6	5	4	3	2	1			
F		CIRCUIT SIZE	PLATING TYPE B PART NO.	PLATING TYPE C PART NO.	PLATING TYPE D PART NO.	PLATING TYPE G PART NO.		CIRCUIT SIZE	PLATING TYPE B PART NO.	PLATING TYPE C PART NO.	PLATING TYPE D PART NO.	PLATING TYPE G PART NO.	F
		2 X 1	90122-0241	90122-0401	90122-0561	90122-1041		2 X 1	90122-0321	90122-0481	90122-0641	90122-1121	
		2 X 2	▲ -0242	▲ -0402	▲ -0562	▲ -1042		2 X 2	▲ -0322	▲ -0482	▲ -0642	▲ -1122	
		2 X 3	-0243	-0403	-0563	-1043		2 X 3	-0323	-0483	-0643	-1123	
		2 X 4	-0244	-0404	-0564	-1044		2 X 4	-0324	-0484	-0644	-1124	
		2 X 5	-0245	-0405	-0565	-1045		2 X 5	-0325	-0485	-0645	-1125	
		2 X 6	-0246	-0406	-0566	-1046		2 X 6	-0326	-0486	-0646	-1126	
		2 X 7	-0247	-0407	-0567	-1047		2 X 7	-0327	-0487	-0647	-1127	
		2 X 8	-0248	-0408	-0568	-1048		2 X 8	-0328	-0488	-0648	-1128	
		2 X 9	-0249	-0409	-0569	-1049		2 X 9	-0329	-0489	-0649	-1129	
		2 X 10	-0250	-0410	-0570	-1050		2 X 10	-0330	-0490	-0650	-1130	
		2 X 11	-0251	-0411	-0571	-1051		2 X 11	-0331	-0491	-0651	-1131	
		2 X 12	-0252	-0412	-0572	-1052		2 X 12	-0332	-0492	-0652	-1132	
		2 X 13	-0253	-0413	-0573	-1053		2 X 13	-0333	-0493	-0653	-1133	
		2 X 14	-0254	-0414	-0574	-1054		2 X 14	-0334	-0494	-0654	-1134	
		2 X 15	-0255	-0415	-0575	-1055		2 X 15	-0335	-0495	-0655	-1135	
		2 X 16	-0256	-0416	-0576	-1056		2 X 16	-0336	-0496	-0656	-1136	
		2 X 17	-0257	-0417	-0577	-1057		2 X 17	-0337	-0497	-0657	-1137	
		2 X 18	-0258	-0418	-0578	-1058		2 X 18	-0338	-0498	-0658	-1138	
		2 X 19	-0259	-0419	-0579	-1059		2 X 19	-0339	-0499	-0659	-1139	
		2 X 20	-0260	-0420	-0580	-1060		2 X 20	-0340	-0500	-0660	-1140	
		2 X 21	-0261	-0421	-0581	-1061		2 X 21	-0341	-0501	-0661	-1141	
		2 X 22	-0262	-0422	-0582	-1062		2 X 22	-0342	-0502	-0662	-1142	
		2 X 23	-0263	-0423	-0583	-1063		2 X 23	-0343	-0503	-0663	-1143	
		2 X 24	-0264	-0424	-0584	-1064		2 X 24	-0344	-0504	-0664	-1144	
		2 X 25	-0265	-0425	-0585	-1065		2 X 25	-0345	-0505	-0665	-1145	
		2 X 26	-0266	-0426	-0586	-1066		2 X 26	-0346	-0506	-0666	-1146	
		2 X 27	-0267	-0427	-0587	-1067		2 X 27	-0347	-0507	-0667	-1147	
		2 X 28	-0268	-0428	-0588	-1068		2 X 28	-0348	-0508	-0668	-1148	
		2 X 29	-0269	-0429	-0589	-1069		2 X 29	-0349	-0509	-0669	-1149	
		2 X 30	-0270	-0430	-0590	-1070		2 X 30	-0350	-0510	-0670	-1150	
		2 X 31	-0271	-0431	-0591	-1071		2 X 31	-0351	-0511	-0671	-1151	
		2 X 32	-0272	-0432	-0592	-1072		2 X 32	-0352	-0512	-0672	-1152	
		2 X 33	-0273	-0433	-0593	-1073		2 X 33	-0353	-0513	-0673	-1153	
		2 X 34	-0274	-0434	-0594	-1074		2 X 34	-0354	-0514	-0674	-1154	
		2 X 35	-0275	-0435	-0595	-1075		2 X 35	-0355	-0515	-0675	-1155	
		2 X 36	-0276	-0436	-0596	-1076		2 X 36	-0356	-0516	-0676	-1156	
		2 X 37	-0277	-0437	-0597	-1077		2 X 37	-0357	-0517	-0677	-1157	
		2 X 38	-0278	-0438	-0598	-1078		2 X 38	-0358	-0518	-0678	-1158	
		2 X 39	▼ -0279	▼ -0439	▼ -0599	▼ -1079		2 X 39	▼ -0359	▼ -0519	▼ -0679	▼ -1159	
		2 X 40	90122-0280	90122-0440	90122-0600	90122-1080		2 X 40	90122-0360	90122-0520	90122-0680	90122-1160	
E													E
D													D
C													C
B													B

DIM
C (± 0.20)
 $\pm .008$
(5.75)
.226

DIM
D (± 0.25)
 $\pm .010$
(4.50)
.177

DIM
C (± 0.20)
 $\pm .008$
(6.75)
.266

DIM
D (± 0.25)
 $\pm .010$
(4.50)
.177

NOTES:
FOR PLATING VARIATIONS SEE
ENG.STD. SDES-99000-0003.

REVISE PIN DIM EC NO: S2012-0325 DRWN:SKANG CHKD:ATSEE APPR:MLONG 2011/10/31 2011/10/31	QUALITY SYMBOLS $F_A=0$ $F_B=0$ $F_P=0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY DB	DATE 16/07/87	TITLE	
		4 PLACES	± ---	± ---	CHECKED BY DB	DATE 1987/07/16	C-GRID III DUAL ROW RIGHT ANGLE HEADER MOLEX INCORPORATED	
		3 PLACES	± ---	± ---	APPROVED BY DB	DATE 1987/07/16		
		2 PLACES	± 0.05	± .002	MATERIAL NO.	DOCUMENT NO.		
1 PLACE	± ---	± ---	SEE TABLE		SDA-90122		SHEET NO. 6 OF 6	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						