


Samtec

QSTRIP®

(0.635 mm) .025"



6QCD-026-06.00-STL-TTR-3

HIGH-SPEED COAX CABLE ASSEMBLIES

SPECIFICATIONS

For complete specifications see www.samtec.com?SQCD or see www.samtec.com?6QCD

Cable:

38 AWG coax micro ribbon

Signal Routing:

50 Ω Single-Ended

Overall Length:

(152 mm) 6" to

(1 m) 40" standard

Cable Flexing Life:

>40,000 cycles

Cable Bending Radius:

<2.5 mm

Plating:

Au over 50 μ" (1.27 μm) Ni

Propagation Delay:

4.79 nsec/meter

Operating Temp Range:

-40 °C to +105 °C

RoHS Compliant:

Yes

SQCD Mates with:
QTS, QSS

6QCD Mates with:
QMS, QFS

RUGGEDIZED
BY SAMTEC

Socket or
Terminal

Surface
Mount

EYE®
SPEED
CABLE

38 AWG
micro ribbon
coax cable

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



APPLICATIONS



Processing conditions will affect mated height.

ALSO AVAILABLE (MOV Required)


- Other pin counts
- Other terminations

Notes:

Cable lengths longer than 40.00" (1 meter) are not supported with S.I. test data.

Design your High-Speed Cable with Samtec's High-Speed Cable Solutionator® at www.samtec.com/hdr

This Series is non-standard, non-returnable.




Due to technical progress, all designs, specifications and components are subject to change without notice.


WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.




SQCD-025-06.00-TTR-STR-1



6QCD-052-06.00-STL-TBR-3-B


SQCD, 6QCD SERIES




Choice of end options

Choice of socket or terminal

SCREW MOUNT APPLICATIONS (-F, -S, -B)



SO-0318-04-01-02



Screw Mount end options

END NO. 1

END NO. 2

WIRING OPTION

SCREW DOWN END OPTION


Specify
END ASSEMBLIES
from chart

—1
= Pin 1 to Pin 1
—2
= Pin 1 to Pin 2
—3
= Pin 1 to Second Last Pin
—4
= Pin 1 to Last Pin

Leave blank for no Screw Option

—F
= End No. 1
—S
= End No. 2
—B
= Both Ends

END	SURFACE MOUNT
TTR	Terminal, Top, Notch Right
TTL	Terminal, Top, Notch Left
TBR	Terminal, Bottom, Notch Right
TBL	Terminal, Bottom, Notch Left
STR	Socket, Top, Notch Right
STL	Socket, Top, Notch Left
SBR	Socket, Bottom, Notch Right
SBL	Socket, Bottom, Notch Left



SURFACE MOUNT (-XTX & -XBX)
SCREW DOWN OPTIONS

SERIES	NO. OF POSITIONS	A	B
SQCD	—025	(40.10) 1.579	(34.00) 1.339
	—050	(60.10) 2.366	(54.00) 2.126
	—075	(80.10) 3.154	(74.00) 2.913
6QCD	—026	(45.47) 1.790	(39.50) 1.555
	—052	(66.80) 2.630	(61.00) 2.402

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.