



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1262	A	RELEASED	HO	8/21/01	JWM	8/21/02	DJC	8/21/02
1885	B	UPDATED TO ROHS COMPLIANCE	EO	02/03/06	HO	2/6/06	HO	2/6/06

Dimensions	A	B	C	D	E	F	G	H	I	J	K
Min.	8.5	7.74	6.09	0.40	—	2.41	4.82	0.71	0.73	12.7	42°
Max.	9.39	8.5	6.6	0.53	0.88	2.66	5.33	0.86	1.02	—	48°



Absolute Maximum Ratings:

- Collector-Base Voltage, $V_{CBO} = 60V$
- Collector-Emitter Voltage, $V_{CEO} = 40V$
- Emitter-Base Voltage, $V_{EBO} = 5V$
- Continuous Collector Current, $I_C = 0.7A$
- Total Device Dissipation ($T_A = +25^\circ C$), $P_D = 800mW$
Derate above $25^\circ C = 4.6mW/^\circ C$
- Total Device Dissipation ($T_C = +25^\circ C$), $P_D = 5W$
Derate above $25^\circ C = 28.6mW/^\circ C$
- Operating Junction Temperature Range, $T_J = -65^\circ$ to $+200^\circ C$
- Storage Temperature Range, $T_{stg} = -65^\circ$ to $+200^\circ C$
- Thermal Resistance, Junction-to-Case, $R_{thJC} = 35^\circ C/W$
- Lead Temperature (Duration Soldering, $\frac{1}{16}$ " from case, 60sec Max.), $T_L = 300^\circ C$

A silicon NPN transistor in a TO-39 type case designed primarily for amplifier and switching applications. This device features high breakdown voltage, low leakage current, low capacity, and beta useful over an extremely wide current range.

Electrical Characteristics: ($T_A = +25^\circ C$ Unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF Characteristics						
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 0.1mA, I_B = 0$	40	—	—	V
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = 100\mu A, I_E = 0$	60	—	—	V
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = 100\mu A, I_C = 0$	5	—	—	V
Emitter Cut-Off Current	I_{EBO}	$V_{BE} = 4V, I_C = 0$	—	—	0.25	μA

ON Characteristics, Note 1

DC Current Gain	h_{FE}	$V_{CE} = 10V, I_C = 150mA$	50	—	250	—
		$V_{CE} = 2.5V, I_C = 150mA$	40	—	—	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 150mA, I_B = 15mA$	—	—	1.4	V
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = 150mA, I_B = 15mA$	—	—	1.7	V

Small-Signal Characteristics

Current Gain-Bandwidth Product	f_T	$V_{CE} = 10V, I_C = 50mA, f = 20MHz$	100	—	—	MHz
Output Capacitance	C_{obo}	$V_{CB} = 10V, I_E = 0, f = 1MHz$	—	—	12	pF
Input Capacitance	C_{ibo}	$V_{BE} = 500mV, I_C = 0, f = 1MHz$	—	—	80	pF

Note 1. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 1\%$.

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

HISHAM ODISH

CHECKED BY:

JEFF MCVICKER

APPROVED BY:

DANIEL CAREY

DATE:

8/21/02

DATE:

8/21/02

DATE:

8/21/02

DRAWING TITLE:

Amplifier Transistor, TO-39, NPN, Silicon

SIZE

A

DWG. NO.

2N3053

ELECTRONIC FILE

35C0698.DWG

REV

B

SCALE:

NTS

U.O.M.: Millimeters

SHEET: 1 OF 1