




## Features

- SMD Single-Turn / Cermet / Industrial Open Frame
- Cross slot rotor designs suitable for automatic adjustment equipment
- Supplied in 12 mm embossed tape, compatible with automatic pick-and-place assembly equipment
- Recommended for reflow solder processing only
- RoHS compliant\* - see [processing information](#) on lead free surface mount trimmers
- For trimmer applications/processing guidelines, [click here](#)

## 3364 - 4 mm Square Trimpot® Trimming Potentiometer

### Electrical Characteristics

Standard Resistance Range  
.....100 ohms to 1 megohm  
(see standard resistance table)  
Resistance Tolerance .....  $\pm 25\%$  std.  
End Resistance  
    <1K.....20 ohms max.  
    >1K.....2 %  
Contact Resistance Variation  
(Voltage Divider) ..... 5 % max.  
Resolution ..... Infinite  
Adjustment Angle .....  $260^\circ \pm 20^\circ$

### Environmental Characteristics

Power Rating (50 volts max.)  
    70 °C ..... 0.2 watt  
Temperature Range ... -40 °C to +100 °C  
Temperature Coefficient ...  $\pm 250$  ppm/°C  
Humidity ..... 500 hours (5 %  $\Delta$ TR)  
Load Life.....500 hours  
    0.2 watt @ 70 °C (5 %  $\Delta$ TR)  
Rotational Life ..... 20 cycles (15%  $\Delta$ TR)

### Physical Characteristics

Torque.....20 to 200 g-cm  
Mechanical Angle ..... Continuous  
Marking..... Resistance code,  
    manufacturer's full part number  
    and date code on packaging  
Terminals ..... Solder coated  
Standard Packaging... 1000 pcs./7 " reel  
Adjustment Tool..... H-90

Aqueous cleaning not recommended.  
Reflow solder processing recommended

### How To Order




**3364 X - 1 - 103 E**

Model \_\_\_\_\_  
Style \_\_\_\_\_  
Orientation of parts in tape:  
    Styles W,A  
    Terminals toward sprocket holes  
    Styles X,B  
    Terminals away from sprocket  
    holes  
Standard Product \_\_\_\_\_  
Resistance Code \_\_\_\_\_  
Embossed Tape Designator \_\_\_\_\_  
    E = 1000 pcs./7 " reel (-1 standard)


Consult factory for other available options.

### Product Dimensions

Common Dimensions  
3364W, X  
3-Terminal






#### SUGGESTED PWB LAYOUT





DIMENSIONS:  $\frac{\text{MM}}{\text{(INCHES)}}$   
TOLERANCES:  $\pm \frac{0.25}{(.010)}$  EXCEPT WHERE NOTED

3364A, B  
3-Terminal



#### SUGGESTED PWB LAYOUT



\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.



Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

# 3364 - 4 mm Square Trimpot® Trimming Potentiometer

**BOURNS®**

## Packaging Specifications



Conforms with EIA specification RS-481.

DIMENSIONS:  $\frac{\text{MM}}{(\text{INCHES})}$

## Standard Resistance Table

| Resistance (Ohms) | Resistance Code | Part Marking |
|-------------------|-----------------|--------------|
| <b>100</b>        | <b>101</b>      | <b>12</b>    |
| <b>200</b>        | <b>201</b>      | <b>22</b>    |
| <b>500</b>        | <b>501</b>      | <b>52</b>    |
| <b>1,000</b>      | <b>102</b>      | <b>13</b>    |
| <b>2,000</b>      | <b>202</b>      | <b>23</b>    |
| <b>5,000</b>      | <b>502</b>      | <b>53</b>    |
| <b>10,000</b>     | <b>103</b>      | <b>14</b>    |
| <b>20,000</b>     | <b>203</b>      | <b>24</b>    |
| <b>50,000</b>     | <b>503</b>      | <b>54</b>    |
| <b>100,000</b>    | <b>104</b>      | <b>15</b>    |
| 200,000           | 204             | 25           |
| 500,000           | 504             | 55           |
| 1,000,000         | 105             | 16           |

Popular distribution resistance values listed in boldface.

REV. 04/14

"Trimpot" is a registered trademark of Bourns, Inc.  
Specifications are subject to change without notice.  
Users should verify actual device performance in their specific applications.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.