

# SN74AUP1G17 Low-Power Single Schmitt-Trigger Buffer

## 1 Features

- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance Tested Per JESD 22
  - 2000-V Human-Body Model (A114-B, Class II)
  - 1000-V Charged-Device Model (C101)
- Available in the Texas Instruments NanoStar™ Package
- Low Static-Power Consumption ( $I_{CC} = 0.9 \mu A$  Maximum)
- Low Dynamic-Power Consumption ( $C_{pd} = 4.4$  pF Typical at 3.3 V)
- Low Input Capacitance ( $C_i = 1.5$  pF Typical)
- Low Noise – Overshoot and Undershoot <10% of  $V_{CC}$
- $I_{off}$  Supports Partial-Power-Down Mode Operation
- Includes Schmitt-Trigger Inputs
- Wide Operating  $V_{CC}$  Range of 0.8 V to 3.6 V
- Optimized for 3.3-V Operation
- 3.6-V I/O Tolerant to Support Mixed-Mode Signal Operation
- $t_{pd} = 5.1$  ns Maximum at 3.3 V
- Suitable for Point-to-Point Applications

## 2 Applications

- Grid Infrastructure
- PC & Notebooks
- Tablets
- Factory Automation & Control
- Gaming
- Server

## 3 Description

The AUP family of devices is TI's premier solution to the industry's low-power needs in battery-powered portable applications. This family ensures a very low static- and dynamic-power consumption across the entire  $V_{CC}$  range of 0.8 V to 3.6 V, resulting in increased battery life. This product also maintains excellent signal integrity (see [AUP – The Lowest-Power Family](#) and [Excellent Signal Integrity](#)).

This device functions as an independent gate with Schmitt-trigger inputs, which allows for slow input transition and better switching-noise immunity at the input.

NanoStar™ package technology is a major breakthrough in IC packaging concepts, using the die as the package.


This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs when the device is powered down. This inhibits current backflow into the device which prevents damage to the device.

### Device Information<sup>(1)</sup>

| PART NUMBER    | PACKAGE     | BODY SIZE (NOM)   |
|----------------|-------------|-------------------|
| SN74AUP1G17DBV | SOT-23 (5)  | 1.60 mm × 2.90 mm |
| SN74AUP1G17DCK | SC70 (5)    | 1.25 mm × 2.00 mm |
| SN74AUP1G17DRL | SOT-5X3 (5) | 1.60 mm × 1.20 mm |
| SN74AUP1G17DRY | SON (6)     | 1.00 mm × 1.45 mm |
| SN74AUP1G17DSF | SON (6)     | 1.00 mm × 1.00 mm |
| SN74AUP1G17YFP | DSBGA (4)   | 0.76 mm × 0.76 mm |
| SN74AUP1G17YZP | DSBGA (5)   | 0.89 mm × 1.39 mm |
| SN74AUP1G17DPW | X2SON (5)   | 0.80 mm × 0.80 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

**Logic Diagram (Positive Logic)**  
(DBV, DCK, DPW, DRL, DRT, DRY, and YZP Packages)



**Logic Diagram (Positive Logic)**  
(YFP Package)



## Table of Contents


|                                                                        |           |                                                                  |           |
|------------------------------------------------------------------------|-----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                                                | <b>1</b>  | <b>8 Detailed Description</b> .....                              | <b>12</b> |
| <b>2 Applications</b> .....                                            | <b>1</b>  | 8.1 Overview .....                                               | 12        |
| <b>3 Description</b> .....                                             | <b>1</b>  | 8.2 Functional Block Diagrams .....                              | 12        |
| <b>4 Revision History</b> .....                                        | <b>2</b>  | 8.3 Feature Description .....                                    | 12        |
| <b>5 Pin Configuration and Functions</b> .....                         | <b>3</b>  | 8.4 Device Functional Modes .....                                | 13        |
| <b>6 Specifications</b> .....                                          | <b>4</b>  | <b>9 Application and Implementation</b> .....                    | <b>14</b> |
| 6.1 Absolute Maximum Ratings .....                                     | 4         | 9.1 Application Information .....                                | 14        |
| 6.2 ESD Ratings .....                                                  | 4         | 9.2 Typical Application .....                                    | 14        |
| 6.3 Recommended Operating Conditions .....                             | 4         | <b>10 Power Supply Recommendations</b> .....                     | <b>16</b> |
| 6.4 Thermal Information .....                                          | 5         | <b>11 Layout</b> .....                                           | <b>16</b> |
| 6.5 Electrical Characteristics .....                                   | 5         | 11.1 Layout Guidelines .....                                     | 16        |
| 6.6 Switching Characteristics: $C_L = 5$ pF .....                      | 7         | 11.2 Layout Example .....                                        | 16        |
| 6.7 Switching Characteristics: $C_L = 10$ pF .....                     | 8         | <b>12 Device and Documentation Support</b> .....                 | <b>17</b> |
| 6.8 Switching Characteristics: $C_L = 15$ pF .....                     | 8         | 12.1 Documentation Support .....                                 | 17        |
| 6.9 Switching Characteristics: $C_L = 30$ pF .....                     | 9         | 12.2 Receiving Notification of Documentation Updates .....       | 17        |
| 6.10 Operating Characteristics .....                                   | 9         | 12.3 Community Resources .....                                   | 17        |
| 6.11 Typical Characteristics .....                                     | 9         | 12.4 Trademarks .....                                            | 17        |
| <b>7 Parameter Measurement Information</b> .....                       | <b>10</b> | 12.5 Electrostatic Discharge Caution .....                       | 17        |
| 7.1 Propagation Delays, Setup and Hold Times, and Pulse Duration ..... | 10        | 12.6 Glossary .....                                              | 17        |
| 7.2 Enable and Disable Times .....                                     | 11        | <b>13 Mechanical, Packaging, and Orderable Information</b> ..... | <b>17</b> |

## 4 Revision History







NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision I (March 2010) to Revision J                                                                                                                                                                                                                                                                                                                                                                                                                                                          | Page |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| <ul style="list-style-type: none"> <li>Added <i>Applications</i>, <i>Device Information</i> table, <i>Pin Configuration and Functions</i> section, <i>ESD Ratings</i> table, <i>Thermal Information</i> table, <i>Feature Description</i> section, <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section .....</li> </ul> | 1    |
| <ul style="list-style-type: none"> <li>Deleted <i>Ordering Information</i> table, see <i>Mechanical, Packaging, and Orderable Information</i> at the end of the data sheet .....</li> </ul>                                                                                                                                                                                                                                                                                                                 | 1    |


## 5 Pin Configuration and Functions



N.C. – No internal connection.



See mechanical drawings for dimensions.



DNU – Do not use

### Pin Functions

| NAME            | PIN                |          |     |     | I/O | DESCRIPTION     |
|-----------------|--------------------|----------|-----|-----|-----|-----------------|
|                 | DBV, DCK, DRL, DPW | DRY, DSF | YFP | YZP |     |                 |
| A               | 2                  | 2        | A1  | B1  | I   | Input           |
| DNU             | —                  | —        | —   | A1  | —   | Do not use      |
| GND             | 3                  | 3        | B1  | C1  | —   | Ground          |
| N.C.            | 1                  | 1<br>5   | —   | —   | —   | No connection   |
| V <sub>CC</sub> | 5                  | 6        | A2  | A2  | —   | Positive supply |
| Y               | 4                  | 4        | B2  | C2  | O   | Output          |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                  |                                                                                             |                    | MIN  | MAX                   | UNIT |
|------------------|---------------------------------------------------------------------------------------------|--------------------|------|-----------------------|------|
| V <sub>CC</sub>  | Supply voltage                                                                              |                    | −0.5 | 4.6                   | V    |
| V <sub>I</sub>   | Input voltage <sup>(2)</sup>                                                                |                    | −0.5 | 4.6                   | V    |
| V <sub>O</sub>   | Voltage range applied to any output in the high-impedance or power-off state <sup>(2)</sup> |                    | −0.5 | 4.6                   | V    |
| V <sub>O</sub>   | Output voltage range in the high or low state <sup>(2)</sup>                                |                    | −0.5 | V <sub>CC</sub> + 0.5 | V    |
| I <sub>IK</sub>  | Input clamp current                                                                         | V <sub>I</sub> < 0 | −50  |                       | mA   |
| I <sub>OK</sub>  | Output clamp current                                                                        | V <sub>O</sub> < 0 | −50  |                       | mA   |
| I <sub>O</sub>   | Continuous output current                                                                   |                    | ±20  |                       | mA   |
|                  | Continuous current through V <sub>CC</sub> or GND                                           |                    | ±50  |                       | mA   |
| T <sub>j</sub>   | Junction temperature                                                                        |                    | 150  |                       | °C   |
| T <sub>stg</sub> | Storage temperature                                                                         |                    | −65  | 150                   | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.

### 6.2 ESD Ratings

|                    |                         | VALUE                                                                          | UNIT |
|--------------------|-------------------------|--------------------------------------------------------------------------------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | 2000 |
|                    |                         | Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | 1000 |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

See<sup>(1)</sup>

|                                |                                | MIN                      | MAX             | UNIT |
|--------------------------------|--------------------------------|--------------------------|-----------------|------|
| V <sub>CC</sub>                | Supply voltage                 | 0.8                      | 3.6             | V    |
| V <sub>I</sub>                 | Input voltage                  | 0                        | 3.6             | V    |
| V <sub>O</sub>                 | Output voltage                 | 0                        | V <sub>CC</sub> | V    |
| I <sub>OH</sub> <sup>(2)</sup> | High-level output current      | V <sub>CC</sub> = 0.8 V  | –20             | μA   |
|                                |                                | V <sub>CC</sub> = 1.1 V  | –1.1            | mA   |
|                                |                                | V <sub>CC</sub> = 1.4 V  | –1.7            |      |
|                                |                                | V <sub>CC</sub> = 1.65 V | –1.9            |      |
|                                |                                | V <sub>CC</sub> = 2.3 V  | –3.1            |      |
|                                |                                | V <sub>CC</sub> = 3 V    | –4              |      |
| I <sub>OL</sub> <sup>(2)</sup> | Low-level output current       | V <sub>CC</sub> = 0.8 V  | 20              | μA   |
|                                |                                | V <sub>CC</sub> = 1.1 V  | 1.1             | mA   |
|                                |                                | V <sub>CC</sub> = 1.4 V  | 1.7             |      |
|                                |                                | V <sub>CC</sub> = 1.65 V | 1.9             |      |
|                                |                                | V <sub>CC</sub> = 2.3 V  | 3.1             |      |
|                                |                                | V <sub>CC</sub> = 3 V    | 4               |      |
| T <sub>A</sub>                 | Operating free-air temperature | –40                      | 85              | °C   |

- (1) All unused inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. See [Implications of Slow or Floating CMOS Inputs](#).
- (2) Defined by the signal-integrity requirements and design-goal priorities

## 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup>                                     | SN74AUP1G17     |               |                  |                |              |              |                |                | UNIT |
|-------------------------------------------------------------------|-----------------|---------------|------------------|----------------|--------------|--------------|----------------|----------------|------|
|                                                                   | DBV<br>(SOT-23) | DCK<br>(SC70) | DRL<br>(SOT-5X3) | DPW<br>(X2SON) | DRY<br>(SON) | DSF<br>(SON) | YFP<br>(DSBGA) | YZP<br>(DSBGA) |      |
|                                                                   | 5 PINS          | 5 PINS        | 5 PINS           | 5 PINS         | 6 PINS       | 6 PINS       | 4 PINS         | 5 PINS         |      |
| $R_{\theta JA}$ Junction-to-ambient thermal resistance            | 267.2           | 284.1         | 294.7            | 489.2          | 347.8        | 386.2        | 179.3          | 146.2          | °C/W |
| $R_{\theta JC(top)}$ Junction-to-case (top) thermal resistance    | 191.9           | 208.5         | 132.5            | 226.3          | 237.7        | 192.9        | 2.8            | 1.4            | °C/W |
| $R_{\theta JB}$ Junction-to-board thermal resistance              | 101.1           | 103.1         | 143.6            | 352.9          | 210.6        | 242.2        | 58.3           | 39.3           | °C/W |
| $\Psi_{JT}$ Junction-to-top characterization parameter            | 83.0            | 76.6          | 14.5             | 38.2           | 64.4         | 28.9         | 1.1            | 0.7            | °C/W |
| $\Psi_{JB}$ Junction-to-board characterization parameter          | 100.8           | 102.3         | 144.1            | 352.1          | 210.6        | 241.9        | 58.6           | 39.8           | °C/W |
| $R_{\theta JC(bot)}$ Junction-to-case (bottom) thermal resistance | N/A             | N/A           | N/A              | 150.8          | N/A          | N/A          | N/A            | N/A            | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 6.5 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

| PARAMETER                                                | TEST CONDITIONS                                 | $V_{CC}$ | MIN  | TYP | MAX  | UNIT |
|----------------------------------------------------------|-------------------------------------------------|----------|------|-----|------|------|
| $V_{T+}$<br>Positive-going<br>input threshold<br>voltage | $T_A = 25^\circ\text{C}$                        | 0.8 V    | 0.3  |     | 0.6  | V    |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.3  |     | 0.6  |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 1.1 V    | 0.53 |     | 0.9  |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.53 |     | 0.9  |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 1.4 V    | 0.74 |     | 1.11 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.74 |     | 1.11 |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 1.65 V   | 0.91 |     | 1.29 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.91 |     | 1.29 |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 2.3 V    | 1.37 |     | 1.77 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 1.37 |     | 1.77 |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 3 V      | 1.88 |     | 2.29 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 1.88 |     | 2.29 |      |
| $V_{T-}$<br>Negative-going<br>input threshold<br>voltage | $T_A = 25^\circ\text{C}$                        | 0.8 V    | 0.1  |     | 0.6  | V    |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.1  |     | 0.6  |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 1.1 V    | 0.26 |     | 0.65 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.26 |     | 0.65 |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 1.4 V    | 0.39 |     | 0.75 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.39 |     | 0.75 |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 1.65 V   | 0.47 |     | 0.84 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.47 |     | 0.84 |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 2.3 V    | 0.69 |     | 1.04 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.69 |     | 1.04 |      |
|                                                          | $T_A = 25^\circ\text{C}$                        | 3 V      | 0.88 |     | 1.24 |      |
|                                                          | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |          | 0.88 |     | 1.24 |      |

## Electrical Characteristics (continued)

over operating free-air temperature range (unless otherwise noted)

| PARAMETER                                                          | TEST CONDITIONS                 |                                 | V <sub>CC</sub> | MIN                    | TYP | MAX  | UNIT |
|--------------------------------------------------------------------|---------------------------------|---------------------------------|-----------------|------------------------|-----|------|------|
| $\Delta V_T$<br>Hysteresis<br>(V <sub>T+</sub> – V <sub>T–</sub> ) | T <sub>A</sub> = 25°C           |                                 | 0.8 V           | 0.07                   |     | 0.5  | V    |
|                                                                    | T <sub>A</sub> = –40°C to +85°C |                                 |                 | 0.07                   |     | 0.5  |      |
|                                                                    | T <sub>A</sub> = 25°C           |                                 | 1.1 V           | 0.08                   |     | 0.46 |      |
|                                                                    | T <sub>A</sub> = –40°C to +85°C |                                 |                 | 0.08                   |     | 0.46 |      |
|                                                                    | T <sub>A</sub> = 25°C           |                                 | 1.4 V           | 0.18                   |     | 0.56 |      |
|                                                                    | T <sub>A</sub> = –40°C to +85°C |                                 |                 | 0.18                   |     | 0.56 |      |
|                                                                    | T <sub>A</sub> = 25°C           |                                 | 1.65 V          | 0.27                   |     | 0.66 |      |
|                                                                    | T <sub>A</sub> = –40°C to +85°C |                                 |                 | 0.27                   |     | 0.66 |      |
|                                                                    | T <sub>A</sub> = 25°C           |                                 | 2.3 V           | 0.53                   |     | 0.92 |      |
|                                                                    | T <sub>A</sub> = –40°C to +85°C |                                 |                 | 0.53                   |     | 0.92 |      |
|                                                                    | T <sub>A</sub> = 25°C           |                                 | 3 V             | 0.79                   |     | 1.31 |      |
|                                                                    | T <sub>A</sub> = –40°C to +85°C |                                 |                 | 0.79                   |     | 1.31 |      |
| V <sub>OH</sub>                                                    | I <sub>OH</sub> = –20 μA        | T <sub>A</sub> = 25°C           | 0.8 V to 3.6 V  | V <sub>CC</sub> – 0.1  |     |      | V    |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | V <sub>CC</sub> – 0.1  |     |      |      |
|                                                                    | I <sub>OH</sub> = –1.1 mA       | T <sub>A</sub> = 25°C           | 1.1 V           | 0.75 × V <sub>CC</sub> |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.7 × V <sub>CC</sub>  |     |      |      |
|                                                                    | I <sub>OH</sub> = –1.7 mA       | T <sub>A</sub> = 25°C           | 1.4 V           | 1.11                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 1.03                   |     |      |      |
|                                                                    | I <sub>OH</sub> = –1.9 mA       | T <sub>A</sub> = 25°C           | 1.65 V          | 1.32                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 1.3                    |     |      |      |
|                                                                    | I <sub>OH</sub> = –2.3 mA       | T <sub>A</sub> = 25°C           | 2.3 V           | 2.05                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 1.97                   |     |      |      |
|                                                                    | I <sub>OH</sub> = –3.1 mA       | T <sub>A</sub> = 25°C           | 2.3 V           | 1.9                    |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 1.85                   |     |      |      |
|                                                                    | I <sub>OH</sub> = –2.7 mA       | T <sub>A</sub> = 25°C           | 3 V             | 2.72                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 2.67                   |     |      |      |
|                                                                    | I <sub>OH</sub> = –4 mA         | T <sub>A</sub> = 25°C           | 3 V             | 2.6                    |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 2.55                   |     |      |      |
| V <sub>OL</sub>                                                    | I <sub>OL</sub> = 20 μA         | T <sub>A</sub> = 25°C           | 0.8 V to 3.6 V  | 0.1                    |     |      | V    |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.1                    |     |      |      |
|                                                                    | I <sub>OL</sub> = 1.1 mA        | T <sub>A</sub> = 25°C           | 1.1 V           | 0.3 × V <sub>CC</sub>  |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.3 × V <sub>CC</sub>  |     |      |      |
|                                                                    | I <sub>OL</sub> = 1.7 mA        | T <sub>A</sub> = 25°C           | 1.4 V           | 0.31                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.37                   |     |      |      |
|                                                                    | I <sub>OL</sub> = 1.9 mA        | T <sub>A</sub> = 25°C           | 1.65 V          | 0.31                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.35                   |     |      |      |
|                                                                    | I <sub>OL</sub> = 2.3 mA        | T <sub>A</sub> = 25°C           | 2.3 V           | 0.31                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.33                   |     |      |      |
|                                                                    | I <sub>OL</sub> = 3.1 mA        | T <sub>A</sub> = 25°C           | 2.3 V           | 0.44                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.45                   |     |      |      |
|                                                                    | I <sub>OL</sub> = 2.7 mA        | T <sub>A</sub> = 25°C           | 3 V             | 0.31                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.33                   |     |      |      |
|                                                                    | I <sub>OL</sub> = 4 mA          | T <sub>A</sub> = 25°C           | 3 V             | 0.44                   |     |      |      |
|                                                                    |                                 | T <sub>A</sub> = –40°C to +85°C |                 | 0.45                   |     |      |      |

## Electrical Characteristics (continued)

over operating free-air temperature range (unless otherwise noted)

| PARAMETER               | TEST CONDITIONS                                                           |                                 | V <sub>CC</sub> | MIN | TYP | MAX | UNIT |
|-------------------------|---------------------------------------------------------------------------|---------------------------------|-----------------|-----|-----|-----|------|
| I <sub>I</sub> A inputs | V <sub>I</sub> = GND to 3.6 V                                             | T <sub>A</sub> = 25°C           | 0 V to 3.6 V    | 0.1 |     |     | μA   |
|                         |                                                                           | T <sub>A</sub> = −40°C to +85°C |                 | 0.5 |     |     |      |
| I <sub>off</sub>        | V <sub>I</sub> or V <sub>O</sub> = 0 V to 3.6 V                           | T <sub>A</sub> = 25°C           | 0 V             | 0.2 |     |     | μA   |
|                         |                                                                           | T <sub>A</sub> = −40°C to +85°C |                 | 0.6 |     |     |      |
| ΔI <sub>off</sub>       | V <sub>I</sub> or V <sub>O</sub> = 0 V to 3.6 V                           | T <sub>A</sub> = 25°C           | 0 V to 0.2 V    | 0.2 |     |     | μA   |
|                         |                                                                           | T <sub>A</sub> = −40°C to +85°C |                 | 0.6 |     |     |      |
| I <sub>CC</sub>         | V <sub>I</sub> = GND or (V <sub>CC</sub> to 3.6 V),<br>I <sub>O</sub> = 0 | T <sub>A</sub> = 25°C           | 0.8 V to 3.6 V  | 0.5 |     |     | μA   |
|                         |                                                                           | T <sub>A</sub> = −40°C to +85°C |                 | 0.9 |     |     |      |
| ΔI <sub>CC</sub>        | V <sub>I</sub> = V <sub>CC</sub> 0.6 V, I <sub>O</sub> = 0                | T <sub>A</sub> = 25°C           | 3.3 V           | 40  |     |     | μA   |
|                         |                                                                           | T <sub>A</sub> = −40°C to +85°C |                 | 50  |     |     |      |
| C <sub>i</sub>          | V <sub>I</sub> = V <sub>CC</sub> or GND                                   | 0 V                             |                 | 1.5 |     |     | pF   |
|                         |                                                                           | 3.6 V                           |                 | 1.5 |     |     |      |
| C <sub>O</sub>          | V <sub>O</sub> = GND                                                      |                                 | 0 V             | 2.5 |     |     | pF   |

## 6.6 Switching Characteristics: C<sub>L</sub> = 5 pF

over recommended operating free-air temperature range, C<sub>L</sub> = 5 pF (unless otherwise noted) (see [Figure 3](#) and [Figure 4](#))

| PARAMETER       | FROM<br>(INPUT) | TO<br>(OUTPUT) | TEST CONDITIONS                  |                                 | MIN  | TYP | MAX  | UNIT |
|-----------------|-----------------|----------------|----------------------------------|---------------------------------|------|-----|------|------|
| t <sub>pd</sub> | A               | Y              | V <sub>CC</sub> = 0.8 V          | T <sub>A</sub> = 25°C           | 22.7 |     |      | ns   |
|                 |                 |                | V <sub>CC</sub> = 1.2 V ± 0.1 V  | T <sub>A</sub> = 25°C           | 6.3  | 8   | 12.8 |      |
|                 |                 |                |                                  | T <sub>A</sub> = –40°C to +85°C | 3.9  |     | 14.6 |      |
|                 |                 |                | V <sub>CC</sub> = 1.5 V ± 0.1 V  | T <sub>A</sub> = 25°C           | 4.6  | 5.8 | 8.4  |      |
|                 |                 |                |                                  | T <sub>A</sub> = –40°C to +85°C | 2.8  |     | 10   |      |
|                 |                 |                | V <sub>CC</sub> = 1.8 V ± 0.15 V | T <sub>A</sub> = 25°C           | 3.9  | 4.8 | 7.2  |      |
|                 |                 |                |                                  | T <sub>A</sub> = –40°C to +85°C | 2.4  |     | 8.1  |      |
|                 |                 |                | V <sub>CC</sub> = 2.5 V ± 0.2 V  | T <sub>A</sub> = 25°C           | 3.1  | 3.6 | 5.1  |      |
|                 |                 |                |                                  | T <sub>A</sub> = –40°C to +85°C | 2    |     | 6.1  |      |
|                 |                 |                | V <sub>CC</sub> = 3.3 V ± 0.3 V  | T <sub>A</sub> = 25°C           | 2.7  | 3   | 4.4  |      |
|                 |                 |                |                                  | T <sub>A</sub> = –40°C to +85°C | 1.9  |     | 5.1  |      |

## 6.7 Switching Characteristics: $C_L = 10$ pF

over recommended operating free-air temperature range,  $C_L = 10$  pF (unless otherwise noted) (see [Figure 3](#) and [Figure 4](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | TEST CONDITIONS               |                                                  | MIN | TYP  | MAX  | UNIT |
|-----------|-----------------|----------------|-------------------------------|--------------------------------------------------|-----|------|------|------|
| $t_{pd}$  | A               | Y              | $V_{CC} = 0.8$ V              | $T_A = 25^\circ\text{C}$                         |     | 25.1 |      | ns   |
|           |                 |                | $V_{CC} = 1.2$ V $\pm$ 0.1 V  | $T_A = 25^\circ\text{C}$                         | 7.1 | 9.1  | 13.8 |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 4.7 |      | 15.6 |      |
|           |                 |                | $V_{CC} = 1.5$ V $\pm$ 0.1 V  | $T_A = 25^\circ\text{C}$                         | 5.2 | 6.5  | 9.4  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 3.4 |      | 11   |      |
|           |                 |                | $V_{CC} = 1.8$ V $\pm$ 0.15 V | $T_A = 25^\circ\text{C}$                         | 4.5 | 5.4  | 8    |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 2.9 |      | 9    |      |
|           |                 |                | $V_{CC} = 2.5$ V $\pm$ 0.2 V  | $T_A = 25^\circ\text{C}$                         | 3.5 | 4.2  | 5.7  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 2.4 |      | 6.8  |      |
|           |                 |                | $V_{CC} = 3.3$ V $\pm$ 0.3 V  | $T_A = 25^\circ\text{C}$                         | 3.1 | 3.5  | 4.9  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 2.2 |      | 5.7  |      |

## 6.8 Switching Characteristics: $C_L = 15$ pF

over recommended operating free-air temperature range,  $C_L = 15$  pF (unless otherwise noted) (see [Figure 3](#) and [Figure 4](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | TEST CONDITIONS               |                                                  | MIN | TYP  | MAX  | UNIT |
|-----------|-----------------|----------------|-------------------------------|--------------------------------------------------|-----|------|------|------|
| $t_{pd}$  | A               | Y              | $V_{CC} = 0.8$ V              | $T_A = 25^\circ\text{C}$                         |     | 27.6 |      | ns   |
|           |                 |                | $V_{CC} = 1.2$ V $\pm$ 0.1 V  | $T_A = 25^\circ\text{C}$                         | 7.8 | 10.1 | 14.8 |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 5.3 |      | 16.7 |      |
|           |                 |                | $V_{CC} = 1.5$ V $\pm$ 0.1 V  | $T_A = 25^\circ\text{C}$                         | 5.8 | 7.4  | 10.3 |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 3.9 |      | 12   |      |
|           |                 |                | $V_{CC} = 1.8$ V $\pm$ 0.15 V | $T_A = 25^\circ\text{C}$                         | 5   | 6.1  | 8.8  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 3.4 |      | 10   |      |
|           |                 |                | $V_{CC} = 2.5$ V $\pm$ 0.2 V  | $T_A = 25^\circ\text{C}$                         | 4   | 4.7  | 6.4  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 2.8 |      | 7.5  |      |
|           |                 |                | $V_{CC} = 3.3$ V $\pm$ 0.3 V  | $T_A = 25^\circ\text{C}$                         | 3.5 | 4.1  | 5.4  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 2.6 |      | 6.2  |      |

## 6.9 Switching Characteristics: $C_L = 30$ pF

over recommended operating free-air temperature range,  $C_L = 30$  pF (unless otherwise noted) (see Figure 3 and Figure 4)


| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | TEST CONDITIONS               |                                                  | MIN | TYP  | MAX  | UNIT |
|-----------|-----------------|----------------|-------------------------------|--------------------------------------------------|-----|------|------|------|
| $t_{pd}$  | A               | Y              | $V_{CC} = 0.8$ V              | $T_A = 25^\circ\text{C}$                         |     | 35.1 |      | ns   |
|           |                 |                | $V_{CC} = 1.2$ V $\pm$ 0.1 V  | $T_A = 25^\circ\text{C}$                         | 10  | 13.1 | 18.1 |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 7.5 |      | 19.8 |      |
|           |                 |                | $V_{CC} = 1.5$ V $\pm$ 0.1 V  | $T_A = 25^\circ\text{C}$                         | 7.4 | 9.6  | 12.9 |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 5.6 |      | 14.9 |      |
|           |                 |                | $V_{CC} = 1.8$ V $\pm$ 0.15 V | $T_A = 25^\circ\text{C}$                         | 6.4 | 7.9  | 11   |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 4.8 |      | 12.4 |      |
|           |                 |                | $V_{CC} = 2.5$ V $\pm$ 0.2 V  | $T_A = 25^\circ\text{C}$                         | 5.2 | 6.1  | 7.9  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 4   |      | 9.3  |      |
|           |                 |                | $V_{CC} = 3.3$ V $\pm$ 0.3 V  | $T_A = 25^\circ\text{C}$                         | 4.6 | 5.3  | 6.7  |      |
|           |                 |                |                               | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$ | 3.6 |      | 7.7  |      |

## 6.10 Operating Characteristics

$T_A = 25^\circ\text{C}$


| PARAMETER                              | TEST CONDITIONS | $V_{CC}$           | TYP | UNIT |
|----------------------------------------|-----------------|--------------------|-----|------|
| $C_{pd}$ Power dissipation capacitance | $f = 10$ MHz    | 0.8 V              | 4   | pF   |
|                                        |                 | 1.2 V $\pm$ 0.1 V  | 4   |      |
|                                        |                 | 1.5 V $\pm$ 0.1 V  | 4   |      |
|                                        |                 | 1.8 V $\pm$ 0.15 V | 4   |      |
|                                        |                 | 2.5 V $\pm$ 0.2 V  | 4.2 |      |
|                                        |                 | 3.3 V $\pm$ 0.3 V  | 4.4 |      |

## 6.11 Typical Characteristics



## 7 Parameter Measurement Information


### 7.1 Propagation Delays, Setup and Hold Times, and Pulse Duration




- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_r/t_f = 3 \text{ ns}$ .
  - C. The outputs are measured one at a time, with one transition per measurement.
  - D.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
  - E. All parameters and waveforms are not applicable to all devices.

**Figure 3. Load Circuit And Voltage Waveforms**

## 7.2 Enable and Disable Times



|       | $V_{CC} = 0.8\text{ V}$ | $V_{CC} = 1.2\text{ V}$<br>$\pm 0.1\text{ V}$ | $V_{CC} = 1.5\text{ V}$<br>$\pm 0.1\text{ V}$ | $V_{CC} = 1.8\text{ V}$<br>$\pm 0.15\text{ V}$ | $V_{CC} = 2.5\text{ V}$<br>$\pm 0.2\text{ V}$ | $V_{CC} = 3.3\text{ V}$<br>$\pm 0.3\text{ V}$ |
|-------|-------------------------|-----------------------------------------------|-----------------------------------------------|------------------------------------------------|-----------------------------------------------|-----------------------------------------------|
| $C_L$ | 5, 10, 15, 30 pF        | 5, 10, 15, 30 pF                              | 5, 10, 15, 30 pF                              | 5, 10, 15, 30 pF                               | 5, 10, 15, 30 pF                              | 5, 10, 15, 30 pF                              |
| $V_M$ | $V_{CC}/2$              | $V_{CC}/2$                                    | $V_{CC}/2$                                    | $V_{CC}/2$                                     | $V_{CC}/2$                                    | $V_{CC}/2$                                    |
| $V_I$ | $V_{CC}$                | $V_{CC}$                                      | $V_{CC}$                                      | $V_{CC}$                                       | $V_{CC}$                                      | $V_{CC}$                                      |
| $V_D$ | 0.1 V                   | 0.1 V                                         | 0.1 V                                         | 0.15 V                                         | 0.15 V                                        | 0.3 V                                         |



- NOTES: A.  $C_L$  includes probe and jig capacitance.  
 B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.  
 C. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10\text{ MHz}$ ,  $Z_O = 50\text{ }\Omega$ ,  $t_r/t_f = 3\text{ ns}$ .  
 D. The outputs are measured one at a time, with one transition per measurement.  
 E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .  
 F.  $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .  
 G. All parameters and waveforms are not applicable to all devices.

**Figure 4. Load Circuit And Voltage Waveforms**

## 8 Detailed Description

### 8.1 Overview

This device functions as an independent gate with Schmitt-trigger inputs, which allows for slow input transition and better switching-noise immunity at the input.

The AUP family is TI's premier solution to the industry's low power needs in battery-powered portable applications. This family assures a very low static and dynamic power consumption across the entire VCC range of 0.8 V to 3.6 V, resulting in an increased battery life.

This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs when the device is powered down. This inhibits current backflow into the device which prevents damage to the device and excess power consumption.

### 8.2 Functional Block Diagrams



**Figure 5. Logic Diagram (Positive Logic)**  
(DBV, DCK, DPW, DRL, DRT, DRY, and YZP Packages)



**Figure 6. Logic Diagram (Positive Logic)**  
(YFP Package)

### 8.3 Feature Description

#### 8.3.1 Balanced High-Drive CMOS Push-Pull Outputs

A balanced output allows the device to sink and source similar currents. The high drive capability of this device creates fast edges into light loads so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important for the power output of the device to be limited to avoid thermal runaway and damage due to over-current. The electrical and thermal limits defined in the [Absolute Maximum Ratings](#) table must be followed at all times.

#### 8.3.2 Standard CMOS Inputs

Standard CMOS inputs are high impedance and are typically modelled as a resistor in parallel with the input capacitance given in the [Electrical Characteristics](#) table. The worst case resistance is calculated with the maximum input voltage, given in the [Absolute Maximum Ratings](#) table, and the maximum input leakage current, given in the [Electrical Characteristics](#) table, using ohm's law ( $R = V \div I$ ).

Signals applied to the inputs need to have fast edge rates, as defined by  $\Delta t/\Delta v$  in [Recommended Operating Conditions](#) table to avoid excessive currents and oscillations. If a slow or noisy input signal is required, a device with a Schmitt-trigger input should be used to condition the input signal prior to the standard CMOS input.

## Feature Description (continued)

### 8.3.3 Clamp Diodes

The inputs and outputs to this device have negative clamping diodes.

#### CAUTION

Voltages beyond the values specified in the [Absolute Maximum Ratings](#) table can cause damage to the device. The input negative-voltage and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.




Figure 7. Electrical Placement of Clamping Diodes for Each Input and Output

### 8.3.4 Partial Power Down ( $I_{off}$ )

The inputs and outputs for this device enter a high impedance state when the supply voltage is 0 V. The maximum leakage into or out of any input or output pin on the device is specified by  $I_{off}$  in the [Electrical Characteristics](#) table.

### 8.3.5 Over-Voltage Tolerant Inputs

Input signals to this device can be driven above the supply voltage so long as they remain below the maximum input voltage value specified in the [Absolute Maximum Ratings](#) table.

## 8.4 Device Functional Modes

Table 1 lists the functional modes of the SN74AUP1G17 device.

Table 1. Function Table

| INPUT<br>A | OUTPUT<br>Y |
|------------|-------------|
| H          | H           |
| L          | L           |

## 9 Application and Implementation


### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### 9.1 Application Information

There are many situations in which a device needs to be initialized or held off for a short time at system turn-on. This application of the SN74AUP1G17 utilizes the delay created in an RC circuit to hold a line low for a short time when the system is first started, then maintains the line high while the system operates. The SN74AUP1G17 is ideal for this application because it must be tied directly to the primary supply for correct operation and is designed to draw minimal supply current during operation.

### 9.2 Typical Application



**Figure 8. Turn-On Pulse Generator (Normally High Output)**

#### 9.2.1 Design Requirements


This device uses CMOS technology and has balanced output drive. Take care to avoid bus contention because it can drive currents that would exceed maximum limits. The drive strength also creates fast edges into light loads, so routing and load conditions should be considered to prevent ringing.

#### 9.2.2 Detailed Design Procedure

1. Recommended Input Conditions:
  - For specified high and low levels, see ( $V_{T+}$  and  $V_{T-}$ ) in the [Electrical Characteristics](#) table.
  - Inputs are overvoltage tolerant allowing them to go as high as ( $V_I$  max) in the [Absolute Maximum Ratings](#) table at any valid  $V_{CC}$ .
2. Recommended Output Conditions:
  - Load currents should not exceed ( $I_O$  max) per output and should not exceed (continuous current through  $V_{CC}$  or GND) total current for the part. These limits are located in the [Absolute Maximum Ratings](#) table.

## Typical Application (continued)

### 9.2.3 Application Curve



**Figure 9. Simulated Output Response to Supply Turn-On**

## 10 Power Supply Recommendations

The power supply can be any voltage between the min and max supply voltage rating located in the [Recommended Operating Conditions](#) table.

Each  $V_{CC}$  pin should have a good bypass capacitor to prevent power disturbance. It is ok to parallel multiple bypass caps to reject different frequencies of noise. 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor must be installed as close to the power pin as possible for best results.


## 11 Layout

### 11.1 Layout Guidelines


Even low data rate digital signals can contain high-frequency signal components due to fast edge rates. When a printed-circuit board (PCB) trace turns a corner at a 90° angle, a reflection can occur. A reflection occurs primarily because of the change of width of the trace. At the apex of the turn, the trace width increases to 1.414 times the width. This increase upsets the transmission-line characteristics, especially the distributed capacitance and self-inductance of the trace which results in the reflection. Not all PCB traces can be straight and therefore some traces must turn corners. [Figure 10](#) shows progressively better techniques of rounding corners. Only the last example (BEST) maintains constant trace width and minimizes reflections.

An example layout is given in [Figure 11](#) for the DPW (X2SON-5) package. This example layout includes a 0402 (metric) capacitor and uses the measurements found in the example board layout appended to this end of this datasheet. A via of diameter 0.1 mm (3.973 mil) is placed directly in the center of the device. This via can be used to trace out the center pin connection through another board layer, or it can be left out of the layout

### 11.2 Layout Example



**Figure 10. Trace Example**



**Figure 11. Example Layout With DPW (X2SON-5) Package**

## 12 Device and Documentation Support

### 12.1 Documentation Support

#### 12.1.1 Related Documentation

For related documentation see the following:

- [Designing and Manufacturing with TI's X2SON Packages](#)
- [Implications of Slow or Floating CMOS Inputs](#)
- [How to Select Little Logic](#)
- [Introduction to Logic](#)
- [Semiconductor Packing Material Electrostatic Discharge \(ESD\) Protection](#)

### 12.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 12.3 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

**TI E2E™ Online Community** *TI's Engineer-to-Engineer (E2E) Community*. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

### 12.4 Trademarks

NanoStar, E2E are trademarks of Texas Instruments.  
All other trademarks are the property of their respective owners.

### 12.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 12.6 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number             | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)      |
|-----------------------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------|
| <a href="#">SN74AUP1G17DBVR</a>   | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU   SN   NIPDAU                 | Level-1-260C-UNLIM                | -40 to 85    | (H175, H17F, H17K, H17R) |
| SN74AUP1G17DBVR.B                 | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (H175, H17F, H17K, H17R) |
| <a href="#">SN74AUP1G17DBVRG4</a> | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | H17F                     |
| SN74AUP1G17DBVRG4.B               | Active        | Production           | SOT-23 (DBV)   5  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | H17F                     |
| <a href="#">SN74AUP1G17DBVT</a>   | Active        | Production           | SOT-23 (DBV)   5  | 250   SMALL T&R       | Yes         | NIPDAU   SN   NIPDAU                 | Level-1-260C-UNLIM                | -40 to 85    | (H175, H17F, H17K, H17R) |
| SN74AUP1G17DBVT.B                 | Active        | Production           | SOT-23 (DBV)   5  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (H175, H17F, H17K, H17R) |
| <a href="#">SN74AUP1G17DCKR</a>   | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU   SN   NIPDAU                 | Level-1-260C-UNLIM                | -40 to 85    | (H75, H7F, H7K, H7R)     |
| SN74AUP1G17DCKR.B                 | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | (H75, H7F, H7K, H7R)     |
| <a href="#">SN74AUP1G17DCKRG4</a> | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -40 to 85    | (H75, H7F, H7K, H7R)     |
| SN74AUP1G17DCKRG4.B               | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (H75, H7F, H7K, H7R)     |
| <a href="#">SN74AUP1G17DCKT</a>   | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -40 to 85    | (H75, H7F, H7K, H7R)     |
| SN74AUP1G17DCKT.B                 | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (H75, H7F, H7K, H7R)     |
| <a href="#">SN74AUP1G17DPWR</a>   | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU   NIPDAU                      | Level-1-260C-UNLIM                | -40 to 85    | (C, C3)                  |
| SN74AUP1G17DPWR.B                 | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | (C, C3)                  |
| SN74AUP1G17DPWRG4                 | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | C                        |
| SN74AUP1G17DPWRG4.B               | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | C                        |
| <a href="#">SN74AUP1G17DRLR</a>   | Active        | Production           | SOT-5X3 (DRL)   5 | 4000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 85    | (H77, H7R)               |
| SN74AUP1G17DRLR.B                 | Active        | Production           | SOT-5X3 (DRL)   5 | 4000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | (H77, H7R)               |
| <a href="#">SN74AUP1G17DRYR</a>   | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 85    | H7                       |
| SN74AUP1G17DRYR.B                 | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | H7                       |
| <a href="#">SN74AUP1G17DSFR</a>   | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 85    | H7                       |
| SN74AUP1G17DSFR.B                 | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 85    | H7                       |

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">SN74AUP1G17YFPR</a> | Active        | Production           | DSBGA (YFP)   4 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -            | H7<br>(2, N)        |
| SN74AUP1G17YFPR.B               | Active        | Production           | DSBGA (YFP)   4 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | H7<br>(2, N)        |
| <a href="#">SN74AUP1G17YZPR</a> | Active        | Production           | DSBGA (YZP)   5 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | H7N                 |
| SN74AUP1G17YZPR.B               | Active        | Production           | DSBGA (YZP)   5 | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | H7N                 |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF SN74AUP1G17 :**

- Enhanced Product : [SN74AUP1G17-EP](#)

NOTE: Qualified Version Definitions:

- Enhanced Product - Supports Defense, Aerospace and Medical Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AUP1G17DBVR   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DBVR   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DBVRG4 | SOT-23       | DBV             | 5    | 3000 | 178.0              | 9.0                | 3.23    | 3.17    | 1.37    | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DCKR   | SC70         | DCK             | 5    | 3000 | 180.0              | 8.4                | 2.3     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DCKRG4 | SC70         | DCK             | 5    | 3000 | 178.0              | 9.0                | 2.4     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DCKRG4 | SC70         | DCK             | 5    | 3000 | 178.0              | 9.2                | 2.4     | 2.4     | 1.22    | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DCKRG4 | SC70         | DCK             | 5    | 3000 | 180.0              | 8.4                | 2.47    | 2.3     | 1.25    | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DCKT   | SC70         | DCK             | 5    | 250  | 178.0              | 9.0                | 2.4     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DPWR   | X2SON        | DPW             | 5    | 3000 | 180.0              | 8.4                | 0.91    | 0.91    | 0.5     | 2.0     | 8.0    | Q3            |
| SN74AUP1G17DPWRG4 | X2SON        | DPW             | 5    | 3000 | 180.0              | 8.4                | 0.91    | 0.91    | 0.5     | 2.0     | 8.0    | Q3            |
| SN74AUP1G17DRLR   | SOT-5X3      | DRL             | 5    | 4000 | 180.0              | 8.4                | 1.98    | 1.78    | 0.69    | 4.0     | 8.0    | Q3            |
| SN74AUP1G17DRYR   | SON          | DRY             | 6    | 5000 | 180.0              | 9.5                | 1.15    | 1.6     | 0.75    | 4.0     | 8.0    | Q1            |
| SN74AUP1G17DSFR   | SON          | DSF             | 6    | 5000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.63    | 4.0     | 8.0    | Q2            |
| SN74AUP1G17DSFR   | SON          | DSF             | 6    | 5000 | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |

---

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AUP1G17YFPR | DSBGA        | YFP             | 4    | 3000 | 178.0              | 9.2                | 0.89    | 0.89    | 0.58    | 4.0     | 8.0    | Q1            |
| SN74AUP1G17YZPR | DSBGA        | YZP             | 5    | 3000 | 178.0              | 9.2                | 1.02    | 1.52    | 0.63    | 4.0     | 8.0    | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AUP1G17DBVR   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G17DBVR   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G17DBVRG4 | SOT-23       | DBV             | 5    | 3000 | 180.0       | 180.0      | 18.0        |
| SN74AUP1G17DBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| SN74AUP1G17DBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| SN74AUP1G17DCKR   | SC70         | DCK             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G17DCKRG4 | SC70         | DCK             | 5    | 3000 | 180.0       | 180.0      | 18.0        |
| SN74AUP1G17DCKRG4 | SC70         | DCK             | 5    | 3000 | 180.0       | 180.0      | 18.0        |
| SN74AUP1G17DCKRG4 | SC70         | DCK             | 5    | 3000 | 202.0       | 201.0      | 28.0        |
| SN74AUP1G17DCKT   | SC70         | DCK             | 5    | 250  | 180.0       | 180.0      | 18.0        |
| SN74AUP1G17DPWR   | X2SON        | DPW             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G17DPWRG4 | X2SON        | DPW             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| SN74AUP1G17DRLR   | SOT-5X3      | DRL             | 5    | 4000 | 202.0       | 201.0      | 28.0        |
| SN74AUP1G17DRYR   | SON          | DRY             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74AUP1G17DSFR   | SON          | DSF             | 6    | 5000 | 202.0       | 201.0      | 28.0        |
| SN74AUP1G17DSFR   | SON          | DSF             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74AUP1G17YFPR   | DSBGA        | YFP             | 4    | 3000 | 220.0       | 220.0      | 35.0        |
| SN74AUP1G17YZPR   | DSBGA        | YZP             | 5    | 3000 | 220.0       | 220.0      | 35.0        |



## SOT-23 - 1.45 mm max height

## SMALL OUTLINE TRANSISTOR



1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-178.
4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
5. Support pin may differ or may not be present.

# EXAMPLE BOARD LAYOUT

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4214839/K 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## GENERIC PACKAGE VIEW

**DRY 6**

**USON - 0.6 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4207181/G




# EXAMPLE BOARD LAYOUT


DRY0006A

USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



**LAND PATTERN EXAMPLE**  
1:1 RATIO WITH PKG SOLDER PADS  
EXPOSED METAL SHOWN  
SCALE:40X



**SOLDER MASK DETAILS**

4222894/A 01/2018

NOTES: (continued)


3. For more information, see QFN/SON PCB application report in literature No. SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).

## EXAMPLE STENCIL DESIGN

DRY0006A

USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.075 - 0.1 mm THICK STENCIL  
SCALE:40X

4222894/A 01/2018

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.




**X2SON - 0.4 mm max height**

# EXAMPLE BOARD LAYOUT


DSF0006A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:40X



SOLDER MASK DETAILS

4220597/B 06/2022

NOTES: (continued)


4. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).

## EXAMPLE STENCIL DESIGN

DSF0006A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD




SOLDER PASTE EXAMPLE  
BASED ON 0.09 mm THICK STENCIL

PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:40X

4220597/B 06/2022

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.


DRL0005A



## PACKAGE OUTLINE

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



4220753/E 11/2024

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-293 Variation UAAD-1

# EXAMPLE BOARD LAYOUT


DRL0005A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



LAND PATTERN EXAMPLE  
SCALE:30X



SOLDERMASK DETAILS

4220753/E 11/2024

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DRL0005A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:30X

4220753/E 11/2024

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## GENERIC PACKAGE VIEW

**DPW 5**




**X2SON - 0.4 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4211218-3/D



4223102/D 03/2022


## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The size and shape of this feature may vary.

**DPW0005A**

**X2SON - 0.4 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
SOLDER MASK DEFINED  
SCALE:60X

4223102/D 03/2022

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, refer to QFN/SON PCB application note in literature No. SLUA271 ([www.ti.com/lit/slua271](http://www.ti.com/lit/slua271)).

# EXAMPLE STENCIL DESIGN

DPW0005A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD





SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL

EXPOSED PAD 3  
92% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:100X

4223102/D 03/2022

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



4228233/D 09/2023


## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The size and shape of this feature may vary.

**DPW0005B**

**X2SON - 0.4 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
SOLDER MASK DEFINED  
SCALE:60X

4228233/D 09/2023

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, refer to QFN/SON PCB application note in literature No. SLUA271 ([www.ti.com/lit/slua271](http://www.ti.com/lit/slua271)).

## EXAMPLE STENCIL DESIGN

DPW0005B

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL

EXPOSED PAD 5  
92% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:60X

4228233/D 09/2023

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



YZP0005



# PACKAGE OUTLINE

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



D: Max = 1.418 mm, Min = 1.358 mm  
E: Max = 0.918 mm, Min = 0.858 mm

4219492/A 05/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


YZP0005

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE  
SCALE:40X



SOLDER MASK DETAILS  
NOT TO SCALE

4219492/A 05/2017

NOTES: (continued)


- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

## EXAMPLE STENCIL DESIGN

YZP0005

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:40X

4219492/A 05/2017

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.




YFP0004



# PACKAGE OUTLINE

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY




D: Max = 0.79 mm, Min = 0.73 mm

E: Max = 0.79 mm, Min = 0.73 mm


4223507/A 01/2017

## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:50X



SOLDER MASK DETAILS  
NOT TO SCALE

4223507/A 01/2017

NOTES: (continued)


- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

## EXAMPLE STENCIL DESIGN

YFP0004

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:50X

4223507/A 01/2017

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.



### SOT - 1.1 max height

Technical drawing of a mechanical part showing three views: front, side, and top.

**Front View:**

- Overall dimensions: 2.4 (width) x 2.15 (height).
- Feature locations: 1.4, 1.1, 1.3, 1.3.
- Hole diameters: 0.15, 0.1.
- Feature 'NOTE 4' is indicated.
- Feature 'PIN 1 INDEX AREA' is indicated with a hatched area.
- Feature control frames:  $\phi$  0.1 M, C A B, and 0.1 C.


**Side View:**

- Width: 1.1 MAX.
- Height: 0.1.
- Feature control frame: 0.1 C.


**Top View:**

- Width: 0.46 TYP.
- Height: 0.22 TYP.
- Feature control frame: 0.1 C.

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC MO-203.
4. Support pin may differ or may not be present.
5. Lead width does not comply with JEDEC.
6. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:18X




SOLDER MASK DETAILS

4214834/G 11/2024

NOTES: (continued)

7. Publication IPC-7351 may have alternate designs.
8. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE  
 BASED ON 0.125 THICK STENCIL  
 SCALE:18X

4214834/G 11/2024

NOTES: (continued)

9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
10. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated