

General Specifications

Electrical Capacity (Resistive Load)

Power Level: 6A @ 125V AC & 3A @ 250V AC or 6A @ 30V DC

Other Ratings

Contact Resistance:

10 milliohms maximum for solder lug & screw terminal models
30 milliohms maximum for wire lead terminal models

Insulation Resistance:

200 megohms minimum @ 500V DC

Dielectric Strength:

1,500V AC minimum for 1 minute minimum

Mechanical Life:

30,000 operations minimum

Electrical Life:

15,000 operations minimum

Contact Timing:

Break before make

Total Travel:

Alternate Action .177" (4.5mm); Momentary Action .110" (2.8mm)

Materials & Finishes

Plunger:

Brass with nickel plating

Bushing & Outer Case:

Fiberglass reinforced polyamide (UL94V-0 outer case)

Inner Case:

Melamine

Inner Sealing Ring:

Silicone rubber

Outer Sealing Ring:

Natural rubber

Movable Contactor:

Copper with silver plating

Movable Contacts:

Silver alloy with silver plating

Stationary Contacts:

Silver alloy with silver plating

Terminals:

Brass with silver plating for screw lug models;

brass with tin plating for solder lug & wire lead models

Wire Lead Covers:

Heat resistant polyvinyl chloride (Leads are AWG 16.)

Environmental Data

Operating Temp Range:

-30°C through +70°C (-22°F through +158°F)

Humidity:

90 ~ 95% humidity for 96 hours @ 40°C (104°F)

Vibration:

10 ~ 55Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range & returning in 1 minute; 3 right angled directions for 2 hours

Shock:

50G (490m/s²) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)

Installation

Mounting Torque:

1.5Nm (13 lb•in)

Soldering Time & Temp:

Manual Soldering: See Profile A in Supplement section.

Standards & Certifications

Flammability Standards:

UL94V-0 outer case

Wiring Material Standards:

UL AWM 1015 Recognized at Flammability VW-1;

Temperature Range -20°C ~ +105°C; Maximum Load 600V; AWG 16

CSA TEW 105 Certified at Temperature Range -20°C ~ +105° C;

Maximum Load 600V

Distinctive Characteristics

Single unit construction of the bushing and case gives added protection from environmental elements.


Specially designed contact mechanism for breaking light welds.

Minimal contact bounce is achieved with specially designed interlocked switching mechanism.


Outer housing of heat resistant resin meets UL 94V-0 flammability standard and provides high arc and tracking resistance.

Solder lug and screw terminal models meet IP67 of IEC60529 Standards at front panel (dust tight and water protected for temporary immersion). Behind panel standard is IP60 (dust tight but not water protected).

Wire lead models conform fully to IP67 of IEC60529 Standards at front and behind panel (dust tight and water protected for temporary immersion). These models are epoxy sealed at the switch base and covered by an outer case for further protection from dust and water (not operable under water).



Actual Size



TYPICAL SWITCH ORDERING EXAMPLE

WB	1	2	S	D	A
Poles	Circuits	Terminals	Caps	Cap Colors	
1 SPDT	2 ON ON	S Solder Lug *	D .520" (13.2mm) Dia.	A Black	
5	ON (ON)	T Screw Lug	E .748" (19.0mm) Dia.	B White	
() = Momentary		L Wire Lead		C Red	
				* D Amber	
				* E Yellow	
				F Green	
				* G Blue	
				* H Gray	

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

WB12S-DA



Black .520" (13.2mm)
Diameter Cap

SPDT
ON-ON Circuit

Solder Lug Terminals

* Wire harness & cable assemblies
offered only in Americas

POLES & CIRCUITS

		Actuator Position () = Momentary		Connected Terminals		Throw & Schematics	
Pole	Model	Normal Flat	Down	Normal Flat	Down	Note: Terminal numbers are not actually on wire lead models.	
SP	WB12	ON	ON	1-1b	1-1a	SPDT	1a • 1 (COM) 1b
SP	WB15	ON	(ON)	1-1b	1-1a		

STANDARD WIRE COLOR SCHEME

Wire leads are covered with heat resistant vinyl in accordance to UL 1015 and CSA TEW 105 Standards for Appliance Wiring Material (AWM).





Terminal Numbers & Wire Colors			
Models	1a	1	1b
WB12L, WB15L	White	Black	Red

TYPICAL SWITCH DIMENSIONS

Solder Lug







WB15S-DA






Panel Thickness
.157" (4.0mm)

TYPICAL SWITCH DIMENSIONS



Panel Thickness .157" (4.0mm)

WB12T-DA



Panel Thickness .157" (4.0mm)



WB12L-DA

Toggles

Rockers

Pushbuttons

Illuminated PB

Programmable

Keylocks

Rotaries

Slides

Tactiles

Tilt

Touch


Indicators

Accessories

Supplement


Page

D AT414
.520" (13.2mm) Diameter

Colors Available:
A B C D E F G H

Material: PBT Finish: Glossy

E AT412
.748" (19.0mm) Diameter


Colors Available:
A B C F

Material: Polystyrene Finish: Glossy


Cap Color Codes: **A** Black **B** White **C** Red **D** Amber **E** Yellow **F** Green **G** Blue **H** Gray

STANDARD HARDWARE



AT503M
Hex Face Nut

Material:
Brass with
chrome plating1 supplied
with each
switch

AT508
Internal Tooth Lockwasher

Material:
Steel with
zinc/chromate1 supplied
with each
switch

AT401P
O-ring

Material:
Nitrile
butadiene
rubber1 supplied
with each
switch

Notes
