



PANEL CUTOUT
MAX. PANEL THICKNESS
14.0mm [.55]



4 O O 5

GREEN (FORWARD)



GREEN (REVERSE)

▲ DPDT ON-(ON)
CONTACT CONFIGURATION





SWITCH FUNCTION

POS. 1	POS. 2
ON	(ON)
1-3, 4-6	1-2, 4-5

(ON) = MOMENTARY

NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 1A 24VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 M Ω MIN.
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
- OPERATING TEMP.: -20°C to 55°C
- ▲ DENOTES CRITICAL PARAMETER.
- HARDWARE SUPPLIED: O-RING AND HEXNUT
- INGRESS RATING: IP40
- 2011/95/EC (ROHS) COMPLIANT
- LAMP VOLTAGE: 12V



E-SWITCH®

E	22887	UPDATED RATING TO 1A 24VDC	6/19/17	MJR
D	22108	UPDATE TO NEW TERMINAL HOUSING	12/28/15	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV3H2H0NN-334

SCALE 3:2

DATE 1/30/2012

DR BMA

DWG 52-PV3H2H0NN334

REV E