

C-C-D-103-01

$\frac{.126}{3.25} \text{ MIN.}$

Technical drawing of a stud. The drawing shows a side view of a cylindrical component with a central hole. The hole is labeled "STUD". The outer diameter is labeled "W". The total length is labeled "L". The distance from the top of the stud to the center of the hole is labeled "C". The minimum thickness of the material at the top is labeled "MIN.".

"UL" LISTING #E32244
"CSA" LISTING #18689

WIRE SIZE: 12-10 AWG
40-60 MM²

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES
C-1102-	$\frac{.415}{10.41}$	$\frac{.305}{7.75}$	$\frac{.784}{19.91}$	08
C-1105-	$\frac{.320}{8.13}$	$\frac{.305}{7.75}$	$\frac{.784}{19.91}$	06

DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE: NTS	DATE	TITLE:
FRACTION	DEC.	ANG.	DRWN. BY: JJ	10-16-84	SPADE TONGUE TERMINAL KRIMPITE 100-SERIES
±	±	±	CHKD. BY: GZ	10-23-84	
			APPRD. BY:		

DWG. NO.	A	CUSTOMER DWG.
----------	---	---------------

