

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0908140014

Status:

Active

Overview:

Picoflex®

Description:

1.27mm (.050") Pitch Picoflex® PF-50 Header, Vertical, Low Profile, Surface Mount, 14 Circuits, Glow Wire Compatible

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0011 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Application Tooling Part Link

Comments

Overview

Product Name

PCB Headers

90814

Wire-to-Board

690081070

Low Profile SMT

Picoflex®

Picoflex®

Physical

Breakaway

Circuits (Loaded)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness Recommended (in)

PCB Thickness Recommended (mm)

Packaging Type

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Plating min: Mating (µin)

Plating min: Mating (µm)

Plating min: Termination (µin)

Plating min: Termination (µm)

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

14

Natural

30

No

94V-0

Yes

No

None

Yes

Brass

Tin

High Temperature Thermoplastic

1

Vertical

Yes

Yes

0.062 In

1.60 mm

Tube

0.050 In

1.27 mm

120

3

120

3

Yes

Yes

No

No

N/A


-40°C to +105°C

Surface Mount

Electrical

Current - Maximum

1.2A



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

90814Series

Mates With

90327 IDT Connector

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool (Plastic) for 90327 Connector, 4-26 Circuit

0690081070

UL
Voltage - Maximum

E29179
250V

Material Info

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-99020-0011
SDA-90814

This document was generated on 01/06/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION