


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F004 * Effective: 12/21/08 * DCP No: 680					
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
948	A	RELEASED		HYD	4/24/01	JC	6/1/01	DJC	6/1/01



SPC Type No.	Volts (V)	Watts (W)	MOD (mm)	LCL (mm)	MOL (mm)	Base (mm)	Base Type	ØPin (mm)	Filament	Lumens	Color Temperature °K	Avrage Life (Hours)
ESY	120	150	13.5	32	50	15	G6.35	0.95 ~ 1.05	CC-6	3300	3075	200
FCS	24			30					44	13	CBAR6	4500
BRL	12	50	11.5		15	CC-6					1400	
EHJ	24	250	13.5	33	55	CBAR6			8000	3200		
EVD	36	400	19	36	60				14500			
FCR	12	100	11.5	30	44.5	13	GY6.35	1.2 ~ 1.3	2900		3250	

SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
HISHAM ODISH	4/24/01
CHECKED BY:	DATE:
JOHN COLE	6/1/01
APPROVED BY:	DATE:
DANIEL CAREY	6/1/01

DRAWING TITLE:

PROJECTOR LAMPS

SIZE DWG. NO.

A

TA-325

ELECTRONIC FILE

TA-325.DWG

REV

A

SCALE: NTS

U.O.M.: MILLIMETERS

SHEET: 1 OF 1