

Model #: TRAVELERC8

Protect It! Surge Suppressor - TRAVELERC8 In-Line Surge Suppressor



Highlights

- 120V/240V compatible
- Tel/modem protection with built-in splitter
- 2 LEDs
- \$100,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's Traveler In-Line surge suppressor features a high 1130 joule rating to handle even the strongest surges (820 joule rating at 240V AC). In-line design, over current protection and 120/240V compatibility make this surge suppressor ideal for notebook computers and PDAs. Integrated phone line protection allows you to safeguard tel/modem and AC connections with a single unit. "Protected" and "Over Current" LEDs let you instantly know whether your wall jacks have potentially damaging signals. Lifetime warranty with \$100,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

CONNECTORS: interfaces with C8 (2 conductor laptop type) cabling

ELECTRICAL: 120V and 240V AC, 50/60Hz

FORMAT: In-line design that puts surge protection between your notebook computer or PDAs' power adapter and the power cord leading to the wall outlet

SUPPRESSION: AC: 150V RMS Clamping/1130 joules (120V AC) or 820 joules (240V AC)/330V UL1449 let-through rating

Applications

- Ideal for notebook computers, PDAs or other electronics requiring AC and tel/modem safeguarding

Package Includes

- TRAVELERC8 surge suppressor
- 6-ft. phone cord
- Instruction manual with warranty information

Features

- In-line design places AC line surge protection between your notebook computer or PDAs' power adapter and the power cord leading to the wall outlet
- 120/240V compatibility operates on voltage worldwide, automatically switching between 120V or 240V AC power
- Surge suppression rating: 1130 joules (100-120V)/820 joules (220-240V)
- Includes two 2-prong (C8) connectors
- Built-in LEDs confirm suppressor "protection present" (green) and "overcurrent detection" (red) status

- Tel/modem RJ11 jacks provide complete surge protection for modem, fax or telephone connections. Built-in splitter (1 in/2 out) allows simultaneous connection and protection of two devices on a single line
- Single small push-button switch activates overcurrent detection circuit
- \$100,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only) covers connected equipment
- Lifetime product warranty

Specifications

OVERVIEW	
Intended Application	Home/Office, Travel
SYSTEM OVERVIEW	
Voltage compatibility	Supports worldwide voltages of 120 or 240 V AC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Outlet quantity / type	2 (C8) 2-prong connectors
INPUT	
Recommended Electrical Service	120V (110-125V), 230V (220-250V)
Input connection type	Two 2-prong (C8) connectors
Input cord length (ft.)	In-line
LEDS ALARMS & SWITCHES	
Switches	Single small push-button switch activates over-current detection circuit
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "over-current detection" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1130 joules (100-120V) / 820 joules (220-240V)
AC suppression response time	< 1 ns
Clamping voltage (RMS)	150V
UL1499 let through rating	330V - UL Verified
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	

Unit Dimensions (HWD/in)	1.75 x 4.25 x 1
Unit Dimensions (HWD/cm)	4.4 x 10.8 x 2.5
Shipping Dimensions (HWD/in)	9 x 7 x 1.2
Shipping Dimensions (HWD/cm)	22.9 x 17.8 x 3
Unit weight (lbs)	0.2
Unit weight (kg)	0.1
Material of construction	Plastic
Style	InLine
Form factors supported	In-line
SPECIAL FEATURES	
Appearance	Ultra-compact portable in-line protector in an attractive, all black lightweight enclosure
Additional Information	Phone line protection circuits includes a switch to activate over-current detection circuit able to detect digital phone lines that could potentially damage standard dialup modems. Simply connect the protector to an active phone jack and press the button. If RED LED illuminates, the jack wired for digital or other profile that may not be compatible with standard dialup modems
WARRANTY	
Standard warranty period	Lifetime
Connected equipment insurance (USA, Canada, Puerto Rico)	\$100,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2639.