

DO NOT
SCALE FROM
THIS PRINT

LBS-1XX-X-X-S


POSITION SPECIFICATION
-01 THRU -36
"A" = No. of POS. x .100

— ROW SPECIFICATION
USE LBS-36-S

LEAD STYLE SPECIFICATION
(SEE TABLE 1)

— PLATING SPECIFICATION

-T: MATTE TIN CONTACT AND TAIL
-F: 3µ" FLASH GOLD IN CONTACT AREA, MATTE TIN ON TAIL
-H: 30µ" HEAVY GOLD IN CONTACT AREA, 3µ" ON TAIL



NOTES:

1. MIN. PUSHOUT FORCE: 2 lbs.
2. MAX. ALLOWABLE BOW AFTER ASSEMBLY: .003 [.08] in./in.
3. MAX. VARIATION BETWEEN ANY TWO PINS TO BE .010 [.25] MAX.
4.  REPRESENTS A CRITICAL DIMENSION.
5. MAX CUT FLASH: .005 [.13]

TABLE 1

STYLE	"B"	"C"	TERMINAL	COMMENTS
A	.210 [5.33]	.125 [3.18]	T-1M7-01-X	FOR USE WITH STANDARD "SS" SOCKET STRIP
B	.335 [8.51]	.125 [3.18]	T-1M7-02-X	
C	.585 [14.86]	.125 [3.18]	T-1M7-03-X	
D	.835 [21.21]	.125 [3.18]	T-1M7-04-X	

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS	ANGLES
.XX: $\pm .01$ [.3]	2°
.XXX: $\pm .005$ [.13]	
.XXXX: $\pm .0020$ [.051]	

PROPRIETARY NOTE

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: ZYTEL HTNFR52G30BL
CONTACT OR TERMINAL:

MAX FLASH ALLOWED: .002
MAX GATE VESTIGE: .002

F:\DWG\SW\Exisprod\Assembly\100\LBS-1XX-X-X-S.SLDDRW

SHEET SCALE: 3:1

DESCRIPTION:

DESCRIPTION
DWG. NO.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:	LBS ASSEMBLY
--------------	--------------

DWG. NO. **LBS-1XX-X-X-S**

BY: T.WERNE	08/27/02	SHEET 1 OF 1
-------------	----------	--------------