




Dual N-Channel 30-V (D-S) MOSFET with Schottky Diode

PRODUCT SUMMARY		
V_{DS} (V)	$r_{DS(on)}$ (Ω)	I_D (A)
30	0.022 @ $V_{GS} = 10$ V	7.5
	0.030 @ $V_{GS} = 4.5$ V	6.5


SCHOTTKY PRODUCT SUMMARY		
V_{DS} (V)	V_{SD} (V) Diode Forward Voltage	I_F (A)
30	0.50 V @ 1.0 A	2.0

LITTLE FOOT PLUS™




Top View

Ordering Information: Si4834DY
Si4834DY-T1 (with Tape and Reel)



N-Channel MOSFET



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)				
Parameter		Symbol	10 secs	Steady State
Drain-Source Voltage		V_{DS}	30	
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 150^\circ\text{C}$) ^a	$T_A = 25^\circ\text{C}$	I_D	7.5	5.7
	$T_A = 70^\circ\text{C}$		6.0	4.6
Pulsed Drain Current		I_{DM}	30	
Continuous Source Current (Diode Conduction) ^a		I_S	1.7	0.9
Maximum Power Dissipation ^a	$T_A = 25^\circ\text{C}$	P_D	2.0	1.1
	$T_A = 70^\circ\text{C}$		1.3	0.7
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 150	

THERMAL RESISTANCE RATINGS							
Parameter		Symbol	MOSFET		Schottky		Unit
			Typ	Max	Typ	Max	
Maximum Junction-to-Ambient ^a	$t \leq 10$ sec	R_{thJA}	52	62.5	53	62.5	$^\circ\text{C/W}$
	Steady-State		93	110	93	110	
Maximum Junction-to-Foot (Drain)	Steady-State	R_{thJC}	35	40	35	40	

Notes

a. Surface Mounted on 1" x 1" FR4 Board.

MOSFET SPECIFICATIONS (T _J = 25° C UNLESS OTHERWISE NOTED).							
Parameter	Symbol	Test Condition		Min	Typ ^a	Max	Unit
Static							
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA		0.8			V
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V				± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 24 V, V _{GS} = 0 V	Ch-1			100	μA
			Ch-2			1	
		V _{DS} = 24 V, V _{GS} = 0 V, T _J = 85°C	Ch-1			2000	
			Ch-2			15	
On-State Drain Current ^b	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V		20			A
Drain-Source On-State Resistance ^b	r _{DS(on)}	V _{GS} = 10 V, I _D = 7.5 A			0.018	0.022	Ω
		V _{GS} = 4.5 V, I _D = 6.5 A			0.024	0.030	
Forward Transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 7.5 A			22		S
Diode Forward Voltage ^b	V _{SD}	I _S = 1 A, V _{GS} = 0 V	Ch-1		0.47	0.5	V
			Ch-2		0.8	1.2	
Dynamic ^a							
Total Gate Charge	Q _g	V _{DS} = 15 V, V _{GS} = 10 V, I _D = 7.5 A			13	20	nC
Gate-Source Charge	Q _{gs}				2		
Gate-Drain Charge	Q _{gd}				2.7		
Gate Resistance	R _g			0.5	1.9	3.2	Ω
Turn-On Delay Time	t _{d(on)}	V _{DD} = 15 V, R _L = 15 Ω I _D ≅ 1 A, V _{GEN} = 10 V, R _G = 6 Ω			8	16	ns
Rise Time	t _r				10	20	
Turn-Off Delay Time	t _{d(off)}				21	40	
Fall Time	t _f				10	20	
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 1.7 A, di/dt = 100 A/μs	Ch-1		32	70	
			Ch-2		40	80	

Notes

- a. Guaranteed by design, not subject to production testing.
b. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.


SCHOTTKY SPECIFICATIONS ($T_J = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Forward Voltage Drop	V_F	$I_F = 1.0\ \text{A}$		0.47	0.50	V
		$I_F = 1.0\ \text{A}$, $T_J = 125^\circ\text{C}$		0.36	0.42	
Maximum Reverse Leakage Current	I_{rm}	$V_r = 30\ \text{V}$		0.004	0.100	mA
		$V_r = 30\ \text{V}$, $T_J = 100^\circ\text{C}$		0.7	10	
		$V_r = -30\ \text{V}$, $T_J = 125^\circ\text{C}$		3.0	20	
Junction Capacitance	C_T	$V_r = 10\ \text{V}$		50		pF




TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

MOSFET


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Capacitance



Gate Charge








On-Resistance vs. Junction Temperature






TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED) **MOSFET**








TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

MOSFET



TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)

SCHOTTKY





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[SI4834DY-E3](#) [SI4834DY](#) [SI4834DY-T1](#) [SI4834DY-T1-E3](#)