


Specifications

- **Certifications*:** UL, CSA, VDE
- **Dielectric Strength:** 1,000V (minimum)
- **Insulation Resistance:** 100 Megohms (minimum)
- **Base Material:** Nylon
- **Actuator Material:** Nylon

* Due to ongoing technological advances, consult factory for certification specifics.



RGSC		C	70	1	-	R	-	B	-	B	-	0	
SERIES		CIRCUIT ¹		RATING ²			ACTUATOR STYLE			BASE COLOR ³			
RGSC	STANDARD BASE	A	OFF-NONE-ON SINGLE POLE	20	15A 250VAC 20A 125VAC	P	PADDLE	B	BLACK				
RGSB	METAL BRACKET	B	ON-NONE-ON SINGLE POLE	21	15A 250 VAC 20A 125VAC	R	ROCKER	W	WHITE				
RGSE	EUROPEAN BASE	C	OFF-NONE-ON DOUBLE POLE	57	10A 250VAC 3/4HP 15A 125VAC 3/4HP 6A 277VAC 3/4HP	ACTUATOR COLOR ³			ROCKER FACE IMPRINTED LEGEND ⁴				
		D	ON-NONE-ON DOUBLE POLE	70	15A 250VAC 20A 125VAC 3/4HP 125-250VAC 16(6)A 250VAC T85	B	BLACK	0 NO LEGEND					
		E	POLE 1 ON-NONE-ON POLE 2 OFF-NONE-ON	71	15A 250VAC 20A 125VAC 16(6)A 250VAC T85	W	WHITE	A OFF-ON (VERTICAL)					
		F	POLE 1 ON-NONE-OFF POLE 2 OFF-NONE-ON	TERMINATION			D O-I (HORIZONTAL)						
				0	SOLDER LUG				E O-I (VERTICAL)				
				1	.250TAB (QC)				F ON-OFF (VERTICAL)				
				5	WIRE LEAD				G ON-OFF (HORIZONTAL)				

4 White is standard with dark actuators; black is standard with light actuators.