


3φ Round Narrow Viewing Angle LEDs


SEL2015 Series

Part Number	Emitting Color		Lens Color	Forward Voltage		Luminous Intensity		Peak Wavelength		Dominant Wavelength		Spectrum Half Bandwidth		Chip Material	
				VF	Conditions IF (mA)	Iv	Conditions IF (mA)	λP	Conditions IF (mA)	λd	Conditions IF (mA)	Δλ	Conditions IF (mA)		
				(V)		(mcd)		(nm)		(nm)		(nm)			
			TYP	MAX		TYP		TYP		TYP		TYP			
SEL2215R	Red		Diffused red	1.9	2.5	10	38	20	630	10	620	10	35	10	GaAsP
SEL2215S	Red		Transparent red	1.9	2.5	10	45	20	630	10	620	10	35	10	GaAsP
SEL2815A	Amber		Transparent orange	1.9	2.5	10	80	20	610	10	605	10	35	10	GaAsP
SEL2815D	Amber		Diffused orange	1.9	2.5	10	60	20	610	10	605	10	35	10	GaAsP
SEL2915A	Orange		Transparent orange	1.9	2.5	10	81	20	587	10	590	10	33	10	GaAsP
SEL2915D	Orange		Diffused orange	1.9	2.5	10	53	20	587	10	590	10	33	10	GaAsP
SEL2715K	Yellow		Transparent yellow	2.0	2.5	10	130	20	570	10	571	10	30	10	GaP
SEL2715Y	Yellow		Diffused yellow	2.0	2.5	10	110	20	570	10	571	10	30	10	GaP
SEL2415E	Green		Transparent green	2.0	2.5	10	110	20	560	10	567	10	20	10	GaP
SEL2415G	Green		Diffused green	2.0	2.5	10	72	20	560	10	567	10	20	10	GaP
SEL2515C	Pure green		Water clear	2.0	2.5	10	52	20	555	10	559	10	20	10	GaP
SELU2215R-S	Ultrahigh luminosity	Red	Diffused red	2.0	2.5	20	380	20	632	20	624	20	20	20	AlGaInP

Directional Characteristics (representative example)



External Dimensions (Unit: mm)



5-1 Visible Light LEDs

Absolute Maximum Ratings

●Visible Light Unicolor Lamp

Parameter	Unit	Ratings					Conditions
		GaP	GaAsP	GaAlAs	AlGaInP	InGaN	
P _D	mW	75				120	
I _F	mA	30					
ΔI _F	mA/°C	-0.45					25°C or higher
I _{FP}	mA	100				70	f=1kHz, tw≤100μs
V _R	V	3			5		
T _{op}	°C	-30 to +85				-30 to +80	
T _{stg}	°C	-30 to +100					

●Visible Light Bicolor Lamp

Parameter	Unit	Ratings					Conditions
		GaP	GaAsP	GaAlAs	AlGaInP	InGaN	
P _D	mW	75				120	Same conditions for simultaneous lighting
I _F	mA	30					
ΔI _F	mA/°C	-0.45					25°C or higher
I _{FP}	mA	100					f=1kHz, tw≤100μs
V _R	V	4			5		
T _{op}	°C	-30 to +85					
T _{stg}	°C	-30 to +100					

●Visible Light Unicolor Surface Mount LEDs

Parameter	Unit	Ratings					Conditions
		GaP	GaAsP	GaAlAs	AlGaInP	InGaN	
I _F	mA	30				20	
ΔI _F	mA/°C	-0.45				-0.27	25°C or higher
I _{FP}	mA	100 ^{*1}				70 ^{*2}	f=1kHz, tw≤100μs
V _R	V	3			5		
T _{op}	°C	-30 to +85				-30 to +80	
T _{stg}	°C	-30 to +100					

*1: 70mA for SEC1005/1007 Series

*2: 50mA for SEC1005/1007 Series

●Visible Light Bicolor Surface Mount LEDs

Parameter	Unit	Ratings	Conditions
		SEC2002/2004	
PD	mW	75	
		(Same conditions for simultaneous lighting)	
IF	mA	30	
ΔIF	mA/°C	−0.45	25°C or higher
IFP	mA	70	f=1kHz, tw≤100μs
VR	V	4	
Top	°C	−30 to +85	
Tstg	°C	−30 to +100	

●Visible Light Three Element Surface Mount LEDs

Parameter	Unit	Ratings		Conditions
		SECT3M02C-S		
		Red	Green/Blue	
Pd	mW	75	120	When one chip lights up (same as green/blue for simultaneous lighting)
IF	mA	30		
ΔIF	mA/°C	−0.45		25°C or higher
IFP	mA	70	50	f=1kHz, tw≤100μs
VR	V	5		
Top	°C	−30 to +80		
Tsta	°C	−30 to +100		