

Model 6084

Metal Wrist Strap with Clip and Cord, ESD



Features

- For users who prefer a metal wrist strap with adjustability.
- Featuring a flexible band that will not pinch or pull hair.
- Supplied with adjustable links to assure a secure and comfortable fit.
- A standard 4mm snap stud allows attachment to resistive coil cord and alligator clip (provided).

Specifications

Wrist Strap:

Strap Material: Stainless Steel non-rusting per MIL-STD 202 Mthd. 101

Color: Blue

Elasticity: Expansion – 1.5:1

Weight: ~33 grams

Resistance: Band Interior – <150 Ohms

Snap: Post 4mm

Ground Cord:

Length: 6 feet, extended

Resistor: 1 megohm

Color: Black

Snap: 4mm

Standards

MIL-STD 1686, MIL-HDBK-263, and EIA 625.

Ordering Information

Model: 6084

Packaging: Metal Strap, Ground Cord, Alligator Clip, and Instruction Sheet per bag.

USA: Sales: 800-490-2361

Technical Support: technicalsupport@pomonatest.com

Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ (.51 mm), .xxx = $\pm .005$ (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.