

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

88641 Multi-Conductor - Single-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

24 AWG stranded (7x32) TC conductors, plenum, FEP insulation, twisted pair, overall Beldfoil shield (100% coverage), 24 AWG stranded TC drain wire, FEP jacket

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	24	7x32	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
FEP - Fluorinated Ethylene Propylene	0.1524

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
FEP - Fluorinated Ethylene Propylene	0.3556

Overall Cable

Overall Nominal Diameter: 2.692 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 13.394 Kg/Km

Max. Recommended Pulling Tension: 71.171 N

Min. Bend Radius/Minor Axis: 31.750 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/UL Specification: CMP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

88641 Multi-Conductor - Single-Pair Cable

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Plenum Number:	82641
Non-Plenum Number:	8641

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/m)
0.5577

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
101.711

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
193.579

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
79.0721

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
55.777

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
88641 002100	30 MT	1.089 KG	RED		2#24 FEP FS FEP
88641 0021000	305 MT	4.990 KG	RED	C	2#24 FEP FS FEP
88641 002500	152 MT	2.722 KG	RED	C	2#24 FEP FS FEP

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 09-04-2012

© 2014 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.