




	10	9	8	7	6	5	4	3	2	1						
F											F					
E											E					
D											D					
C	REFLOWED MATTE TIN 0.00090/(.000035) MIN. (PREPLATE) (FINISH IS BRIGHT IN APPEARANCE, THICKNESS AS APPLIED PRIOR TO REFLOW)	PHOSPHOR BRONZE	(0.9) .035	(4.5) .177	(3.6) .142	(0.6) .024	(2.7) .106	(2.3) .091	Ø (3.1) .122 MAX.	# 16	39-00-0084 ↑ -0083	5558 PBT3L ↑ PBT3	LOOSE CHAIN			
			(0.6) .024	(2.3) .091	(2.3) .091	(0.4) .016	(1.65) .065	(1.8) .071	Ø (0.9-1.8) .035-.071	#22-28	-0068 -0067	PBT2L PBT2	LOOSE CHAIN			
			(0.9) .035	(4.5) .177	(3.6) .142	(0.5) .020	(2.3) .091	(1.9) .075	Ø (1.3-3.1) .051-.122	# 18-24	-0062 -0061	PBTL PBT	LOOSE CHAIN			
B	REFLOWED MATTE TIN 0.00090/(.000035) MIN OVER COPPER 0.00050/(.000020) MIN. (PREPLATE) (FINISH IS BRIGHT IN APPEARANCE, THICKNESS AS APPLIED PRIOR TO REFLOW)	BRASS	(0.9) .035	(4.5) .177	(3.6) .142	(0.6) .024	(2.7) .106	(2.3) .091	Ø (3.1) .122 MAX.	# 16	-0082 -0081	T3L T3	LOOSE CHAIN			
			(0.6) .024	(2.3) .091	(2.3) .091	(0.4) .016	(1.65) .065	(1.8) .071	Ø (0.9-1.8) .035-.071	#22-28	-0049 -0048	T2L T2	LOOSE CHAIN			
			(0.9) .035	(4.5) .177	(3.6) .142	(0.5) .020	(2.3) .091	(1.9) .075	Ø (1.3-3.1) .051-.122	# 18-24	↓ -0041	↓ TL	LOOSE CHAIN			
	PLATING	MATERIAL	F	E	D	C	B	A	INS. RANGE	WIRE RANGE	EDP NO.	ENG. NO.	FORM			
A			SEE SHEET 1 EC NO: UCP2017-1893 DRAWN:CSIAFTER 2017/02/28 CHKD:JBELL 2017/03/14 APPR:FSMITH 2017/07/31		DESCRIPTION REV	L1	QUALITY SYMBOLS FA=0 FC=0 FP=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .010 2 PLACES ± .25 ± .010 1 PLACE ± .25 ± --- ANGULAR ± 3 °		DIMENSION STYLE MM/IN DRAWN BY DATE H.HIRAMOTO 1991/03/12 CHECKED BY DATE S.KUNISHI 1998/07/07 APPROVED BY DATE FSMITH 2010/04/09 MATERIAL NO.		SCALE DESIGN UNITS METRIC THIRD ANGLE PROJECTION		TITLE MINI-FIT JR OVERALL TIN MALE CRIMP TERMINAL MOLEX INCORPORATED SD-5558**** THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 2 OF 2
	tb_frame_B_P_ME_T Rev. F 2009/06/18	9	8	7	6	5	4	3	2	1						