



STGW30NB60HD

N-CHANNEL 30A - 600V TO-247
PowerMESH™ IGBT

TYPE	V _{CES}	V _{CE(sat)}	I _C
STGW30NB60HD	600 V	< 2.8 V	30 A



- HIGH INPUT IMPEDANCE (VOLTAGE DRIVEN)
- LOW ON-VOLTAGE DROP (V_{CESAT})
- LOW GATE CHARGE
- HIGH CURRENT CAPABILITY
- VERY HIGH FREQUENCY OPERATION
- OFF LOSSES INCLUDE TAIL CURRENT
- CO-PACKAGE WITH TURBOSWITCH™ ANTIPARALLEL DIODE

DESCRIPTION

Using the latest high voltage technology based on a patented strip layout, STMicroelectronics has designed an advanced family of IGBTs, the PowerMESH™ IGBTs, with outstanding performances. The suffix "H" identifies a family optimized to achieve very low switching times for high frequency applications (<120kHz).

APPLICATIONS

- HIGH FREQUENCY MOTOR CONTROLS
- WELDING EQUIPMENTS
- SMPS AND PFC IN BOTH HARD SWITCH AND RESONANT TOPOLOGIES



ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
V _{CES}	Collector-Emitter Voltage (V _{GS} = 0)	600	V
V _{ECR}	Emitter-Collector Voltage	20	V
V _{GE}	Gate-Emitter Voltage	± 20	V
I _C	Collector Current (continuous) at T _c = 25 °C	60	A
I _C	Collector Current (continuous) at T _c = 100 °C	30	A
I _{CM} (•)	Collector Current (pulsed)	240	A
P _{tot}	Total Dissipation at T _c = 25 °C	190	W
	Derating Factor	1.52	W/°C
T _{stg}	Storage Temperature	-65 to 150	°C
T _j	Max. Operating Junction Temperature	150	°C

(•) Pulse width limited by safe operating area

STGW30NB60HD

THERMAL DATA

R _{thj-case}	Thermal Resistance Junction-case	Max	0.66	°C/W
R _{thj-amb}	Thermal Resistance Junction-ambient	Max	30	°C/W
R _{thc-h}	Thermal Resistance Case-heatsink	Typ	0.1	°C/W

ELECTRICAL CHARACTERISTICS (T_j = 25 °C unless otherwise specified)

OFF

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V _{BR(CES)}	Collector-Emitter Breakdown Voltage	I _C = 250 μA V _{GE} = 0	600			V
I _{CES}	Collector cut-off (V _{GE} = 0)	V _{CE} = Max Rating T _j = 25 °C V _{CE} = Max Rating T _j = 125 °C			250 2000	μA μA
I _{GES}	Gate-Emitter Leakage Current (V _{CE} = 0)	V _{GE} = ± 20 V V _{CE} = 0			± 100	nA

ON (*)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
V _{GE(th)}	Gate Threshold Voltage	V _{CE} = V _{GE} I _C = 250 μA	3		5	V
V _{CE(SAT)}	Collector-Emitter Saturation Voltage	V _{GE} = 15 V I _C = 30 A V _{GE} = 15 V I _C = 30 A T _j = 125 °C		2.2 1.8	2.8	V V

DYNAMIC

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
g _{fs}	Forward Transconductance	V _{CE} = 25 V I _C = 30 A		20		S
C _{ies} C _{oes} C _{res}	Input Capacitance Output Capacitance Reverse Transfer Capacitance	V _{CE} = 25 V f = 1 MHz V _{GE} = 0		2300 250 60		pF pF pF
Q _G Q _{GE} Q _{GC}	Total Gate Charge Gate-Emitter Charge Gate-Collector Charge	V _{CE} = 480 V I _C = 30 A V _{GE} = 15 V		150 15 72		nC nC nC
I _{CL}	Latching Current	V _{clamp} = 480 V R _G = 10 Ω T _j = 150 °C	120			A

SWITCHING ON

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
t _{d(on)} t _r	Delay Time Rise Time	V _{CC} = 480 V I _C = 30 A V _{GE} = 15 V R _G = 10 Ω		15 35		ns ns
(di/dt) _{on}	Turn-on Current Slope	V _{CC} = 480 V I _C = 30 A R _G = 10 Ω V _{GE} = 15 V		1000		A/μs
E _{on}	Turn-on Switching Losses	T _j = 125 °C		1000		μJ

ELECTRICAL CHARACTERISTICS (continued)**SWITCHING OFF**

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
t_c	Cross-Over Time	$V_{CC} = 480\text{ V}$ $I_C = 30\text{ A}$		150		ns
$t_r(V_{off})$	Off Voltage Rise Time	$R_{GE} = 10\ \Omega$ $V_{GE} = 15\text{ V}$		40		ns
$t_d(off)$	Delay Time			210		ns
t_f	Fall Time			90		ns
$E_{off}(**)$	Turn-off Switching Loss			1.10		mJ
$E_{ts}(○)$	Total Switching Loss			2.0		mJ
t_c	Cross-Over Time	$V_{CC} = 480\text{ V}$ $I_C = 30\text{ A}$		250		ns
$t_r(V_{off})$	Off Voltage Rise Time	$R_{GE} = 10\ \Omega$ $V_{GE} = 15\text{ V}$		70		ns
$t_d(off)$	Delay Time	$T_j = 125\text{ }^\circ\text{C}$		250		ns
t_f	Fall Time			160		ns
$E_{off}(**)$	Turn-off Switching Loss			1.6		mJ
$E_{ts}(○)$	Total Switching Loss			2.65		mJ

COLLECTOR-EMITTER DIODE


Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
I_f	Forward Current				30	A
I_{fm}	Forward Current pulsed				240	A
V_f	Forward On-Voltage	$I_f = 30\text{ A}$		1.7	2.0	V
		$I_f = 30\text{ A}$ $T_j = 125\text{ }^\circ\text{C}$		1.55		V
t_{rr}	Reverse Recovery Time	$I_f = 30\text{ A}$ $V_R = 100\text{ V}$		116		nS
Q_{rr}	Reverse Recovery Charge	$dI/dt = 100\text{ A}/\mu\text{S}$ $T_j = 125\text{ }^\circ\text{C}$		406		nC
I_{rrm}	Reverse Recovery Current			7		A

(●) Pulse width limited by max. junction temperature


(○) Include recovery losses on the STTA2006 freewheeling diode

(*) Pulsed: Pulse duration = 300 μs , duty cycle 1.5 %


(**) Losses Include Also The Tail (Jedec Standardization)

Thermal Impedance


Output Characteristics




Transfer Characteristics




Transconductance




Collector-Emitter On Voltage vs Temperature




Collector-Emitter On Voltage vs Collector Current




Gate Threshold vs Temperature




Normalized Breakdown Voltage vs Temperature




Capacitance Variations




Gate Charge vs Gate-Emitter Voltage




Total Switching Losses vs Gate Resistance



Total Switching Losses vs Temperature




Total Switching Losses vs Collector Current



TO-247 MECHANICAL DATA

DIM.	mm			inch		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A	4.7		5.3	0.185		0.209
D	2.2		2.6	0.087		0.102
E	0.4		0.8	0.016		0.031
F	1		1.4	0.039		0.055
F3	2		2.4	0.079		0.094
F4	3		3.4	0.118		0.134
G		10.9			0.429	
H	15.3		15.9	0.602		0.626
L	19.7		20.3	0.776		0.779
L3	14.2		14.8	0.559		0.582
L4		34.6			1.362	
L5		5.5			0.217	
M	2		3	0.079		0.118



P025P

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a trademark of STMicroelectronics

© 1999 STMicroelectronics – Printed in Italy – All Rights Reserved
STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - China - Finland - France - Germany - Hong Kong - India - Italy - Japan - Malaysia - Malta - Morocco -
Singapore - Spain - Sweden - Switzerland - United Kingdom - U.S.A.