

4		3		2		1																																																																			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION																																																																					
APRIL ,2004.																																																																									
© COPYRIGHT 2004 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.																																																																									
NOTES:				LOC E																																																																					
1 SINGLE PACK IN ACCORDANCE WITH SPEC 107-3275				DIST B																																																																					
2 100 TRAY PACK IN ACCORDANCE WITH SPEC 107-3275				P LTR DESCRIPTION DATE DWN APVD																																																																					
3 0.08µm Au PLATING OVER 1.27µm Ni PLATING				A EBD0-0035-03 30JAN04 RS FWK																																																																					
4 0.08µm Au PLATING OVER 1.27µm Ni PLATING OVER 0.76µm Cu PLATING																																																																									
5 0.76µm Au PLATING OVER 1.27µm Ni PLATING OVER 0.76µm Cu PLATING																																																																									
6 FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE																																																																									
7 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED																																																																									
RECOMMENDED CABLE STRIPPING DIM'S																																																																									
				<table><tr><td></td><td></td><td></td><td></td><td>1</td><td>1</td><td>1</td><td>1</td><td>PTFE</td><td>INSULATOR</td><td>3</td></tr><tr><td></td><td></td><td></td><td></td><td>1</td><td>1</td><td>1</td><td>1</td><td>BERYLLIUM COPPER 5</td><td>SOCKET</td><td>2</td></tr><tr><td></td><td></td><td></td><td></td><td>1</td><td>1</td><td>-</td><td>-</td><td>BRASS 4</td><td>BODY</td><td>1</td></tr><tr><td></td><td></td><td></td><td></td><td>-</td><td>-</td><td>1</td><td>1</td><td>STAINLESS STEEL 3</td><td>BODY</td><td>1</td></tr><tr><td></td><td></td><td></td><td></td><td>3--1</td><td>3--0</td><td>1--1</td><td>1--0</td><td>MATERIAL</td><td>DESCRIPTION</td><td>ITEM</td></tr><tr><td></td><td></td><td></td><td></td><td>2</td><td>1</td><td>2</td><td>1</td><td colspan="3"></td></tr></table>								1	1	1	1	PTFE	INSULATOR	3					1	1	1	1	BERYLLIUM COPPER 5	SOCKET	2					1	1	-	-	BRASS 4	BODY	1					-	-	1	1	STAINLESS STEEL 3	BODY	1					3--1	3--0	1--1	1--0	MATERIAL	DESCRIPTION	ITEM					2	1	2	1			
				1	1	1	1	PTFE	INSULATOR	3																																																															
				1	1	1	1	BERYLLIUM COPPER 5	SOCKET	2																																																															
				1	1	-	-	BRASS 4	BODY	1																																																															
				-	-	1	1	STAINLESS STEEL 3	BODY	1																																																															
				3--1	3--0	1--1	1--0	MATERIAL	DESCRIPTION	ITEM																																																															
				2	1	2	1																																																																		
				QUANTITY PER ASSY PARTS LIST																																																																					
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R.SMITH 30JAN04																																																																					
DIMENSIONS: mm				CHK S.PARLOW 30JAN04																																																																					
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD F.WHEELER-KING 30JAN04																																																																					
0 PLC ± -				NAME																																																																					
1 PLC ± -				Tyco Electronics Corporation																																																																					
2 PLC ± -				Bideford, UK, EX39 4HE																																																																					
3 PLC ± -				108-3460																																																																					
4 PLC ± -				PRODUCT SPEC																																																																					
ANGLES ± -				APPLICATION SPEC																																																																					
FINISH				411-3276																																																																					
MATERIAL SEE TABLE				WEIGHT -																																																																					
				CUSTOMER DRAWING																																																																					
				SMA STRAIGHT JACK DIRECT SOLDER NON CAPTIVE CENTRE CONTACT RG405/U																																																																					
				SIZE A3 CAGE CODE 00779 DRAWING NO C-1478929 RESTRICTED TO -																																																																					
				SCALE 1:1 SHEET 1 OF 1 REV A																																																																					