

NC-445102-5-9 Product Details

 Share Print Email



NC-445102-5-9
TE Internal Number: A21141-000
 Active

Label ID Products
 Always EU RoHS/ELV Compliant (Statement of Compliance)
Product Highlights:

- Labels
- Region = Not Specified
- Printer Type = Thermal Transfer
- Label Height = 10.20 mm
- Label Width = 44.50 mm

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
Product Drawings: - None Available Catalog Pages/Data Sheets: Label ID Products (PDF, English) Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available	Additional Information: Product Line Information Related Products: Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Labels - Self-Laminating = No - Color = White Electrical Characteristics: - Printer Type = Thermal Transfer - Web Width (mm [in]) = 50.40 [1.986] Body Features: - Material = Nylon Cloth Configuration Features: - Number of Labels Across = 1 Industry Standards: - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Not relevant for lead free process - RoHS/ELV Compliance History = Always was RoHS compliant Printer/Label Features: - Label Height (mm [in]) = 10.20 [0.402] - Label Width (mm [in]) = 44.50 [1.750] - Tamper Evident = No - Label Type = Die-Cut - Adhesive Type = Permanent Acrylic - Vertical Repeat (mm [in]) = 12.70 [0.500] - Recommended Printer = T308S - Recommended Ribbon = 1330-0607-10	Identification Marking: - Energy Label Type = Pressure Sensitive Environmental: - Operating Temperature (°C [°F]) = -40 - +140 [-40 - +284] Conditions for Usage: - Energy Product = Yes Packaging Features: - Packaging Quantity = 5,000 Product Availability: - Region = Not Specified Other: - Series = NC - Brand = TE Connectivity