






LEAD FREE	71.12	[2.800]	28	5-641127-8	LEAD FREE	71.12	[2.800]	28	2-641127-8		SUPERSEDED BY 5-641127-8
	68.58	[2.700]	27	5-641127-7		68.58	[2.700]	27	2-641127-7		SUPERSEDED BY 5-641127-7
	66.04	[2.600]	26	5-641127-6		66.04	[2.600]	26	2-641127-6		SUPERSEDED BY 5-641127-6
	63.50	[2.500]	25	5-641127-5		63.50	[2.500]	25	2-641127-5		SUPERSEDED BY 5-641127-5
	60.96	[2.400]	24	5-641127-4		60.96	[2.400]	24	2-641127-4		SUPERSEDED BY 5-641127-4
	58.42	[2.300]	23	5-641127-3		58.42	[2.300]	23	2-641127-3		SUPERSEDED BY 5-641127-3
	55.88	[2.200]	22	5-641127-2		55.88	[2.200]	22	2-641127-2		SUPERSEDED BY 5-641127-2
	53.34	[2.100]	21	5-641127-1		53.34	[2.100]	21	2-641127-1		SUPERSEDED BY 5-641127-1
	50.80	[2.000]	20	5-641127-0		50.80	[2.000]	20	2-641127-0		SUPERSEDED BY 5-641127-0
	48.26	[1.900]	19	4-641127-9		48.26	[1.900]	19	1-641127-9		SUPERSEDED BY 4-641127-9
	45.72	[1.800]	18	4-641127-8		45.72	[1.800]	18	1-641127-8		SUPERSEDED BY 4-641127-8
	43.18	[1.700]	17	4-641127-7		43.18	[1.700]	17	1-641127-7		SUPERSEDED BY 4-641127-7
	40.64	[1.600]	16	4-641127-6		40.64	[1.600]	16	1-641127-6		
	38.10	[1.500]	15	4-641127-5		38.10	[1.500]	15	1-641127-5		SUPERSEDED BY 4-641127-5
	35.56	[1.400]	14	4-641127-4		35.56	[1.400]	14	1-641127-4		SUPERSEDED BY 4-641127-4
	33.02	[1.300]	13	4-641127-3		33.02	[1.300]	13	1-641127-3		SUPERSEDED BY 4-641127-3
	30.48	[1.200]	12	4-641127-2		30.48	[1.200]	12	1-641127-2		
	27.94	[1.100]	11	4-641127-1		27.94	[1.100]	11	1-641127-1		SUPERSEDED BY 4-641127-1
	25.40	[1.000]	10	4-641127-0		25.40	[1.000]	10	1-641127-0		SUPERSEDED BY 4-641127-0
	22.86	[.900]	9	3-641127-9		22.86	[.900]	9	-641127-9		
20.32	[.800]	8	3-641127-8	20.32	[.800]	8	-641127-8		SUPERSEDED BY 3-641127-8		
17.78	[.700]	7	3-641127-7	17.78	[.700]	7	-641127-7		SUPERSEDED BY 3-641127-7		
15.24	[.600]	6	3-641127-6	15.24	[.600]	6	-641127-6				
12.70	[.500]	5	3-641127-5	12.70	[.500]	5	-641127-5				
10.16	[.400]	4	3-641127-4	10.16	[.400]	4	-641127-4				
7.62	[.300]	3	3-641127-3	7.62	[.300]	3	-641127-3				
5.08	[.200]	2	3-641127-2	5.08	[.200]	2	-641127-2				
DIM (L)				NO.OF POSN	ASSEMBLY						

RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.60 [.063] THICK P.C. BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOPER 26-JAN-2005 CHK D. BOSSI 26-JAN-2005		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: APD D. BOSSI 26-JAN-2005		NAME MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 SQUARE RIGHT ANGLE POST, .000015 GOLD PLATED	
		PRODUCT SPEC 0 PLC ± 1 PLC ± 2 PLC ± 0.13 [.005] 3 PLC ± 4 PLC ±		APPLICATION SPEC	
MATERIAL 		WEIGHT 		SIZE A1	
ANGLE'S FINISH 		RESTRICTED TO		DRAWING NO 00779	
SCALE 8:1		SHEET 1 of 1		REV AC	