

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [76150-5020](#)
Status: **Active**
Overview: [Impact™ Backplane Connector and Cable Assembly System](#)
Description: [Impact™ 100 Ohm 6 Pair Right Angle Daughtercard Receptacle, Right Guided, 10 Columns, 180 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free](#)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-76060-999 \(PDF\)](#)
[Application Specification AS-76060-990 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
Series [76150](#)
Application Conventional, Coplanar, Daughtercard
Application Tooling Documents TM-622018799
Component Type PCB Receptacle
Electrical Model Yes
Overview [Impact™ Backplane Connector and Cable Assembly System](#)
Product Name Impact™
Style N/A
UPC 883906217068

Physical

Circuits (Loaded) 180
Circuits (maximum) 180
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part Yes
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 27.622/g
Number of Columns 10
Number of Pairs 6
Number of Rows 18
Orientation Right Angle
PC Tail Length 1.20mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.00mm
Packaging Type Tray
Pitch - Mating Interface 1.90mm
Pitch - Termination Interface 1.90mm
Plating min - Mating 0.762µm
Polarized to PCB Yes
Temperature Range - Operating -55°C to +85°C
Termination Interface: Style Through Hole - Compliant Pin



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[76150Series](#)

Mates With
[76145 Impact™ 100 Ohm Vertical Backplane Header](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Daughter Card	0622018661
Signal Module	
Assembly Press-In	
Tool for 6-Pair by 10-Column Assemblies	
Impact Daughter	0622024300
Card Extraction Tool	

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100#
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-76060-990
Electrical Model Document	EE-76150-001
Product Specification	PS-76060-999
Sales Drawing	RSD-76150-004, SD-76150-004

This document was generated on 12/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76150-5020](#)